

Fiber Optic Cable - Multimode Duplex 62.5/125 - LSZH - MTRJ/SC - 2 m

StarTech ID: FIBMTSC2



The FIBMTSC2, 2-meter (6.6ft) Multimode 62.5/125 Duplex Fiber Patch Cable is terminated with one MTRJ (male) connector and one SC (male) connector, to provide the necessary connection between fiber networking devices for high-speed, long distance networks.

This MTRJ-SC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

To ensure optimum performance, our multimode fiber duplex cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability.

Backed by Lifetime Warranty, our MTRJ-SC Multimode Fiber Patch cable is guaranteed to provide long-lasting dependability, and top quality performance.

Applications

- Used by long distance networks with mission critical data
- Telecommunication/Data communication
- Broadband systems
- Ideal solution for data applications requiring high speed data transmission

Features

- Attenuation loss meets or exceeds industry standards
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Immune to electrical interference

Technical Specifications

Warranty	Lifetime
Fiber Size	62.5/125
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Classification	OM1
Fiber Type	Multi Mode
Connector A	1 - Fiber Optic MT-RJ Male
Connector B	1 - Fiber Optic SC Duplex Male
Cable Length	6.6 ft [2 m]
Color	Orange
Product Length	6.6 ft [2 m]
Shipping (Package) Weight	0.1 lb [0 kg]
Included in Package	1 - 2m Multimode 62.5/125 Duplex Fiber Patch Cable MTRJ - SC

Certifications, Reports and Compatibility

