

# Product data sheet

Specifications



## Rack PDU, Basic, Zero U, 14.4kW, 208V, (24)C13, (4)C19, (2)L6-30R; 3' Cord

AP7569

### Overview

Presentation	Basic Rack PDU 14.4 kW solution for high density installations
Lead time	Usually in Stock

### Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	3 ft (0.9 m)
Number of cables	1
Provided Equipment	Cord retention bracket(s) Documentation CD Installation guide Rack Mounting brackets Toolless Mounting Kit

### Complementary

Input Voltage	208 V 3 phase
Height	70.0000000000 in (177.8 cm)
Width	2.2 in (5.6 cm)
Output Voltage	208 V 3 phase
Depth	3.7 in (9.5 cm)
Net Weight	16.14 lb(US) (7.32 kg)
mounting location	Side
Mounting preference	No preference
Mounting Mode	Rack-mounted
Rack units	0U
Mounting position	Vertical
Line Rated Current	40 A
Input current limits	50 A
Load Capacity	14400 VA
Input Frequency	50/60 Hz
Number of input connectors	1 CS8365

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Outlet type and quantity</b>	2 NEMA L6-30R 24 IEC 60320 C13 4 IEC 60320 C19
---------------------------------	--

## Environment

<b>Product Certifications</b>	cUL Listed CSA METI Denan UL Listed
<b>Standards</b>	UL 60950
<b>Ambient Air Temperature for Operation</b>	23.0000000000...113.0000000000 °F (-5...45 °C)
<b>Relative Humidity</b>	5...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13.0000000000...149.0000000000 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	5...95 %
<b>Storage altitude</b>	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

<b>GTIN</b>	731304240754
-------------	--------------

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	81.0 in (205.7 cm)
<b>Package 1 Width</b>	12.2 in (31.1 cm)
<b>Package 1 Length</b>	3.1 in (7.9 cm)
<b>Package 1 Weight</b>	24.87 lb(US) (11.28 kg)

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

## Resource performance

 Energy Efficient Product

 Take-Back Program Available

## Well-being performance

 Lead Free

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)