

Trodat GmbH
4600 Wels

Date printed 06.03.2014, Revision 05.03.2014

Version 01

Page 1 / 8

SECTION 1: Identification of the substance / preparation and of the company

1.1 Product identifier

7011 Trodat Stamp Ink

1.2 Relevant identified uses of the substance or mixture and uses advised against

1.2.1 Relevant uses

Paint

1.2.2 Uses advised against

None known.

1.3 Details of the supplier of the safety data sheet

Company	Trodat GmbH Linzerstr. 156 4600 Wels / AUSTRIA Phone +43 (0) 7242 239 - 0 Fax +43 (0) 7242 239 - 940 Homepage www.trodat.net E-mail trodat@trodat.net
----------------	--

Address enquiries to

Technical information	trodat@trodat.net
Safety Data Sheet	sdb@chemiebuero.de

1.4 Emergency phone

Advisory body	+43 (0) 1 406 43 43 (24h)
Company	+43 (0) 7242 239 - 0 Mo-Fr 8:00 - 16:00

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

2.1.1 Classification according to Regulation (EC) No 1272/2008 [CLP]

No classification.

2.1.2 Classification according to Regulation 67/548/EEC or 1999/45/EC

No classification.

2.2 Label elements

The product is required to be labelled in accordance with GHS/CLP-Directives.

Labelling according to Regulation (EC) 1272/2008

Hazard pictograms	not applicable
Hazard statements	none
Special labelling	EUH210 Safety data sheet available on request.

2.3 Other hazards

Environmental hazards	Does not contain any PBT or vPvB substances.
Other hazards	Further hazards were not determined with the current level of knowledge.

Trodat GmbH
4600 Wels

Date printed 06.03.2014, Revision 05.03.2014

Version 01

Page 2 / 8

SECTION 3: Composition / Information on ingredients

Product-type:

The product is a mixture.

Range [%]	Substance
1 - <25	2,2' -oxybisethanol
	CAS: 111-46-6, EINECS/ELINCS: 203-872-2, EU-INDEX: 603-140-00-6
	GHS/CLP: Acute Tox. 4: H302
	EEC: Xn, R 22

Comment on component parts

Substances of Very High Concern - SVHC: substances are not contained or are below 0,1%.
For full text of H-statements and R-phrases: see SECTION 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General information

Take off contaminated clothing and wash before reuse.

Inhalation

Ensure supply of fresh air.
In the event of symptoms seek for medical treatment.

Skin contact

When in contact with the skin, clean with soap and water.
Consult a doctor if skin irritation persists.

Eye contact

Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
If eye irritation persists: Get medical advice/attention.

Ingestion

Seek medical advice immediately.
Rinse out mouth and give plenty of water to drink.
Do not induce vomiting.

4.2 Most important symptoms and effects, both acute and delayed

Headache

4.3 Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Fire-fighting measures

5.1 Extinguishing media

Suitable extinguishing media

Extinguish blanket.
Carbon dioxide.
Foam.

Extinguishing media that must not be used

Full water jet.

5.2 Special hazards arising from the substance or mixture

Unknown risk of formation of toxic pyrolysis products.
Nitrogen oxides (NOx).
Carbon monoxide (CO)

5.3 Advice for firefighters

Use self-contained breathing apparatus.
Fire residues and contaminated firefighting water must be disposed of in accordance with the local regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

High risk of slipping due to leakage/spillage of product.
Ensure adequate ventilation.
Keep away from all sources of ignition.

Trodat GmbH
4600 Wels

Date printed 06.03.2014, Revision 05.03.2014

Version 01

Page 3 / 8

6.2 Environmental precautions

Prevent spread over a wide area (e.g. by containment or oil barriers).
Do not discharge into the drains/surface waters/groundwater.

6.3 Methods and material for containment and cleaning up

Pick up with absorbent material (e.g. sand, sawdust, universal absorbent, diatomaceous earth).
Dispose of absorbed material in accordance within the regulations.

6.4 Reference to other sections

See SECTION 8+13

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Use only in well-ventilated areas.

Take off contaminated clothing and wash before reuse.
Do not eat, drink, smoke or take drugs at work.
Wash face and/or hands before break and end of work.
Use barrier skin cream.

7.2 Conditions for safe storage, including any incompatibilities

Keep only in original container.
Prevent penetration into the ground.
Provide floor with bunding.
Do not store together with oxidizing agents.
Keep container in a well-ventilated place.
Keep container tightly closed.
Protect from heat/overheating.

7.3 Specific end use(s)

See product use, SECTION 1.2

SECTION 8: Exposure controls / personal protection

8.1 Control parameters

Ingredients with occupational exposure limits to be monitored (GB)

Range [%]	Substance
1 - <25	2,2' -oxybisethanol
	CAS: 111-46-6, EINECS/ELINCS: 203-872-2, EU-INDEX: 603-140-00-6
	Long-term exposure: 23 ppm, 101 mg/m ³

Trodat GmbH
4600 Wels

Date printed 06.03.2014, Revision 05.03.2014

Version 01

Page 4 / 8

8.2 Exposure controls

Additional advice on system design	Ensure adequate ventilation on workstation.
Eye protection	Safety glasses.
Hand protection	Butyl rubber, >480 min (EN 374). The details concerned are recommendations. Please contact the glove supplier for further information.
Skin protection	light protective clothing
Other	Avoid contact with eyes and skin. Personal protective equipment should be selected specifically for the working place, depending on concentration and quantity of the hazardous substances handled. The resistance of these equipments to chemicals should be ascertained with the respective supplier.
Respiratory protection	Breathing apparatus in the event of high concentrations. Short term: filter apparatus, combination filter A-P2.
Thermal hazards	not applicable
Delimitation and monitoring of the environmental exposition	Protect the environment by applying appropriate control measures to prevent or limit emissions.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Form	liquid
Color	various
Odor	characteristic
Odour threshold	not determined
pH-value	not determined
pH-value [1%]	not determined
Boiling point [°C]	not determined
Flash point [°C]	> 146
Flammability [°C]	225
Lower explosion limit	not applicable
Upper explosion limit	not applicable
Oxidizing properties	no
Vapour pressure/gas pressure [kPa]	0,01 (20 °C)
Density [g/ml]	not determined
Bulk density [kg/m³]	not applicable
Solubility in water	completely miscible
Partition coefficient [n-octanol/water]	not determined
Viscosity	not determined
Relative vapour density determined in air	not determined
Evaporation speed	not determined
Melting point [°C]	not determined
Autoignition temperature [°C]	not determined
Decomposition temperature [°C]	not determined

9.2 Other information

none

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reactions known if used as directed.

10.2 Chemical stability

The product is stable under standard conditions.

Trodat GmbH
4600 Wels

Date printed 06.03.2014, Revision 05.03.2014

Version 01

Page 5 / 8

10.3 Possibility of hazardous reactions

Reactions with oxidizing agents.

10.4 Conditions to avoid

See SECTION 7.2.

10.5 Incompatible materials

not determined

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Product
ATE-mix, oral, Rat: > 2000 mg/kg.

Range [%]	Substance
1 - <25	2,2' -oxybisethanol, CAS: 111-46-6
	LD50, dermal, Rabbit: 11890 mg/kg.
	LD50, oral, Rat: 12565 mg/kg.

Serious eye damage/irritation	not determined
Skin corrosion/irritation	not determined
Respiratory or skin sensitisation	not determined
Specific target organ toxicity — single exposure	not determined
Specific target organ toxicity — repeated exposure	not determined
Mutagenicity	not determined
Reproduction toxicity	not determined
Carcinogenicity	not determined
General remarks	

Toxicological data of complete product are not available.
No classification on the basis of the calculation procedure of the preparation directive.
The toxicity data listed pertaining to the ingredients are intended for those working in the medicinal professions, experts for occupational health and safety and toxicologists. The toxicity data pertaining to the ingredients were supplied by the manufacturers of raw materials.

SECTION 12: Ecological information

12.1 Toxicity

Range [%]	Substance
1 - <25	2,2' -oxybisethanol, CAS: 111-46-6
	LC50, (96h), fish: > 1000 mg/l.
	EC50, (24h), Daphnia magna: > 10000 mg/l.

12.2 Persistence and degradability

Behaviour in environment compartments	not determined
Behaviour in sewage plant	not determined
Biological degradability	not determined

Trodat GmbH
4600 Wels

Date printed 06.03.2014, Revision 05.03.2014

Version 01

Page 6 / 8

12.3 Bioaccumulative potential

not determined

12.4 Mobility in soil

not determined

12.5 Results of PBT and vPvB assessment

Based on all available information not to be classified as PBT or vPvB respectively.

12.6 Other adverse effects

No classification on the basis of the calculation procedure of the preparation directive.

Ecological data of complete product are not available.

The toxicity data pertaining to the ingredients were supplied by the manufacturers of raw materials.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Waste material must be disposed of in accordance with the Directive on waste 2008/98/EC as well as other national and local regulations. It is not possible to determine a waste code for this product in accordance with the European Waste Catalogue (EWC) since it is only possible to classify it according to how it is used by the customer. The waste code is to be determined within the EU in liaison with the waste-disposal operator.

Product

Coordinate disposal with the authorities if necessary.

Disposal in an incineration plant in accordance with the regulations of the local authorities.

Waste no. (recommended)

080112

Contaminated packaging

Packaging that cannot be cleaned should be disposed of as for product.

Uncontaminated packaging may be taken for recycling.

Waste no. (recommended)

150102

SECTION 14: Transport information

14.1 UN number

See SECTION 14.2 in accordance with UN shipping name

14.2 UN proper shipping name

Transport by land according to ADR/RID NO DANGEROUS GOODS

Inland navigation (ADN) NO DANGEROUS GOODS

Marine transport in accordance with IMDG NOT CLASSIFIED AS "DANGEROUS GOODS"

Air transport in accordance with IATA NOT CLASSIFIED AS "DANGEROUS GOODS"

14.3 Transport hazard class(es)

See SECTION 14.2 in accordance with UN shipping name

14.4 Packing group

See SECTION 14.2 in accordance with UN shipping name

14.5 Environmental hazards

See SECTION 14.2 in accordance with UN shipping name

Trodat GmbH
4600 Wels

Date printed 06.03.2014, Revision 05.03.2014

Version 01

Page 7 / 8

14.6 Special precautions for user

Relevant information under SECTION 6 to 8.

14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EEC-REGULATIONS 1967/548 (1999/45); 1991/689 (2001/118); 1999/13; 2004/42; 648/2004; 1907/2006 (Reach); 1272/2008; 75/324/EEC (2008/47/EC); 453/2010/EC

TRANSPORT-REGULATIONS DOT-Classification, ADR (2013); IMDG-Code (2013, 36. Amdt.); IATA-DGR (2013).

NATIONAL REGULATIONS (GB): EH40/2005 Workplace exposure limits (Second edition, published December 2011).
CHIP 3/ CHIP 4

- Observe employment restrictions for people no

- VOC (1999/13/CE) not determined

15.2 Chemical safety assessment

not applicable

SECTION 16: Other information

16.1 R-phrases (SECTION 3)

R 22: Harmful if swallowed.

16.2 Hazard statements (SECTION 3)

H302 Harmful if swallowed.

16.3 Abbreviations and acronyms:

ADR = Accord européen relatif au transport international des marchandises Dangereuses par Route
RID = Règlement concernant le transport international ferroviaire de marchandises dangereuses
ADN = Accord européen relatif au transport international des marchandises dangereuses par voie de navigation intérieure
CAS = Chemical Abstracts Service
CLP = Classification, Labelling and Packaging
DMEL = Derived Minimum Effect Level
DNEL = Derived No Effect Level
EC50 = Median effective concentration
ECB = European Chemicals Bureau
EEC = European Economic Community
EINECS = European Inventory of Existing Commercial Chemical Substances
ELINCS = European List of Notified Chemical Substances
GHS = Globally Harmonized System of Classification and Labelling of Chemicals
IATA = International Air Transport Association
IBC-Code = International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk
IC50 = Inhibition concentration, 50%
IMDG = International Maritime Code for Dangerous Goods
IUCLID = International Uniform Chemical Information Database
LC50 = Lethal concentration, 50%
LD50 = Median lethal dose
MARPOL = International Convention for the Prevention of Marine Pollution from Ships
PBT = Persistent, Bioaccumulative and Toxic substance
PNEC = Predicted No-Effect Concentration
REACH = Registration, Evaluation, Authorisation and Restriction of Chemicals
TLV@/TWA = Threshold limit value – time-weighted average
TLV@STEL = Threshold limit value – short-time exposure limit
VOC = Volatile Organic Compounds
vPvB = very Persistent and very Bioaccumulative

16.4 Other information

Modified position none

Trodat GmbH

4600 Wels

Date printed 06.03.2014, Revision 05.03.2014

Version 01

Page 8 / 8



Copyright: Chemiebüro®

