

Product data sheet

Specifications



APC Back-UPS, 500VA, Tower, 120V, 6 NEMA 5-15R Outlets , User Replaceable Battery

BK500BLK

Product availability: Stock - Normally stocked in distribution facility

Overview

Lead time Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	300 W
Rated power in VA	500 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA 5-15P
output connection type	3 NEMA 5-15R 3 NEMA 5-15R surge
Cable length	6 ft (1.8 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Cord management straps User Manual USB cable

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	8 h
RBC Quantity	1
Battery Charge Power (Watts)	13 W rated
Battery power in VAh	78 VAh runtime
Battery life	4...6 year(s)
Replacement battery	RBC2

Battery graph comments This graph is based on actual measured runtime data. All measurements were taken with new, fully charged batteries and a balanced resistive load (PF = 1.0). Actual runtimes may vary from the values of this graph. Actual runtimes are dependent on several variables including battery age, battery charge level, environmental conditions and characteristics of the connected load.

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Extendable Run Time	0
---------------------	---

General

Number of power module free slots	0
-----------------------------------	---

Number of power module filled slots	0
-------------------------------------	---

Redundant	No
-----------	----

Physical

color	Black
-------	-------

Height	6.5 in (16.5 cm)
--------	------------------

Width	3.6 in (9.1 cm)
-------	-----------------

Depth	11.2 in (28.4 cm)
-------	-------------------

Net Weight	13.82 lb(US) (6.27 kg)
------------	------------------------

mounting location	Front
-------------------	-------

Mounting preference	No preference
---------------------	---------------

Mounting Mode	Not rack-mountable
---------------	--------------------

Two post mountable	0
--------------------	---

USB compatible	Yes
----------------	-----

Input

Input Frequency	50/60 Hz +/- 3 Hz auto-sensing
-----------------	--------------------------------

Efficiency at full load	98...140 V
-------------------------	------------

Output

Max Configurable Power (Watts)	300 W
--------------------------------	-------

Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains
----------------------------------	---------------------------------

Topology	Standby
----------	---------

Waveform Type	Stepped approximation to a sinewave
---------------	-------------------------------------

Maximum configurable power in VA	500 VA
----------------------------------	--------

Transfer Time	8ms typical : 12ms maximum
---------------	----------------------------

Conformance

Product Certifications	cUL Listed California (CEC) Battery Charger ENERGY STAR V2.0 (USA) Industry Canada
------------------------	---

Equipment protection policy	Lifetime : \$25000
-----------------------------	--------------------

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
---------------------------------------	-------------------------

Relative Humidity	0...95 %
-------------------	----------

Operating altitude	0...10000 ft
--------------------	--------------

Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
-------------------------------------	--------------------------

Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
acoustic level	45 dBA
Online Thermal Dissipation	24 Btu/h

Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rating	480 J
Filtering	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : mee

Ordering and shipping details

Category	11309-APC RESALE PRODUCTS
Discount Schedule	APC1
GTIN	731304021360
Returnability	No
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.4 in (26.3 cm)
Package 1 Width	14.06 in (35.7 cm)
Package 1 Length	6.9 in (17.5 cm)
Package 1 Weight	15.32 lb(US) (6.95 kg)
SCC14	10731304021367

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH


Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Mercury Free

 Rohs Exemption Information Yes

Environmental Certifications

 Energy Star® ENERGY STAR UPS V2.0 (USA)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov