



# LYSOL® IC™ Quaternary Disinfectant Cleaner

Disinfects, cleans, and deodorizes healthcare facilities



## Product Information

Product	Units/Case	Unit Size	Reckitt Item #
Lysol® IC™ Quaternary Disinfectant Cleaner	4	1 gal	36241-74983

## Shipping Specifications

Reckitt Item #	36241-74983
Package Size	1 gal
Case Pack	4
Pallet Cases	36
Tie/High	12/3
Case Weight	36.75 lbs
Case Cube	1.12 cu. ft
Case L x W x H	12.50 x 12.50 x 12.38 in
Item D x W x H	5.81 x 5.81 x 11.25 in
Item Cube	0.220 cu. ft
Item Weight	8.70 lbs
Item UPC	036241749835
CSC Case GTIN	10036241749832

## Technical Specifications

Technical Data	LysoI® IC™ Quaternary Disinfectant Cleaner
Color/Form	Amber/Liquid
Fragrance	Lemon
Active Ingredient	Didecyl dimethyl ammonium chloride (10.14%); n-Alkyl (C14 50%, C12 40%, C16 10%) dimethyl benzyl ammonium chloride (6.76%)
Other Ingredients	83.10%
pH	7.2 to 8.2
EPA Registration	47371-129-675

### DIRECTIONS FOR USE<sup>1</sup>

Remove visible soil deposits from surface then visibly wet surface with a use-solution per the dilution table. The use-solution can be applied with a cloth, mop, sponge, or coarse spray, or soaking. Let solution remain visibly wet on surface for a minimum of 10 minutes. Rinse or allow to air dry. Rinsing of floors is not necessary unless they are to be waxed or polished.

USE AREAS <sup>1</sup>	SURFACE TYPES <sup>1</sup>	
<ul style="list-style-type: none"> <li>- Clinics</li> <li>- Dental offices</li> <li>- Health Care Facilities</li> <li>- Hospitals</li> <li>- Medical Offices</li> <li>- Nursing Homes</li> </ul>	<ul style="list-style-type: none"> <li>- Floors &amp; Walls</li> <li>- [Non-medical] metal surfaces</li> <li>- [Non-medical] stainless steel surfaces</li> <li>- Glazed porcelain,</li> <li>- Plastic surfaces [such as polypropylene, polystyrene, etc.]</li> <li>- Beds [Medical] [Hospital]</li> <li>- Bed frames, Bed rails</li> </ul>	<ul style="list-style-type: none"> <li>- Crutches</li> <li>- Defibrillators</li> <li>- Gurneys &amp; Stretchers</li> <li>- Non-critical [hospital] [medical] equipment surfaces</li> <li>- [Medical] Examining tables</li> <li>- Resuscitators</li> <li>- Stethoscopes</li> <li>- Walkers/Wheel chairs</li> </ul>

<sup>1</sup>On hard, non-porous surfaces

# GERMICIDAL EFFICACY

10 Minute Disinfection - Bacteria*
Pseudomonas aeruginosa <sup>3</sup>
Salmonella enterica
Staphylococcus aureus <sup>3</sup>
Acinetobacter baumannii
Acinetobacter calcoaceticus
Bordetella bronchiseptica
Chlamydia psittaci
Enterobacter cloacae
Enterobacter cloacae - NDM-1
Enterococcus faecalis - Vancomycin Resistant [VRE]
Escherichia coli <sup>3</sup>
Escherichia coli - NDM-1
Fusobacterium necrophorum
Klebsiella aerogenes
Klebsiella pneumoniae <sup>3</sup>
Klebsiella pneumoniae - NDM-1
Legionella pneumophila
Listeria monocytogenes
Pasteurella multocida
Proteus mirabilis
Proteus vulgaris
Salmonella enteritidis
Salmonella typhi
Serratia marcescens
Shigella flexneri
Shigella sonnei
Staphylococcus aureus - Community Associated Methicillin-Resistant [CA-MRSA] [NRS384] [USA300]
Staphylococcus aureus - Community Associated Methicillin-Resistant [CA-MRSA] [NRS123] [USA400]
Staphylococcus aureus - Methicillin resistant [MRSA]
Staphylococcus aureus - Vancomycin Intermediate Resistant [VISA]
Staphylococcus epidermidis <sup>4</sup>
Streptococcus faecalis <sup>3</sup>
Streptococcus pyogenes [Strep]
10 Minute Disinfection - Fungi*
Aspergillus niger
Candida albicans
Trichophyton interdigitale

10 Minute Disinfection - Viruses*
Adenovirus Type 4
Adenovirus Type 7 (at 2 oz. per gallon)
Hepatitis B Virus [HBV]
Hepatitis C Virus [HCV]
Herpes Simplex Virus Type 1
Herpes Simplex Virus Type 2
Human coronavirus
HIV-1 [AIDS virus]
Influenza A Virus
Respiratory Syncytial Virus [RSV]
Rotavirus [WA]
Rubella virus
SARS Associated Coronavirus [SARS]
SARS-CoV-2
Vaccinia virus
10 Minute Disinfection - Animal Viruses*
Avian Influenza virus (H5N1)
Avian polyomavirus
Canine distemper virus
Feline leukemia virus
Feline picornavirus
Infectious bovine rhinotracheitis virus
Infectious bronchitis virus [Avian IBV]
Newcastle Disease virus
Pseudorabies virus [PRV]
Rabies virus
Transmissible gastroenteritis virus [TGE]

\*When used as directed according to labeling and dilution instructions.

<sup>3</sup>ATCC & antibiotic-resistant strain

<sup>4</sup>Antibiotic-resistant strain only

**For additional product information and Safety Data Sheet,  
please visit [www.rbnainfo.com](http://www.rbnainfo.com)**

