

PERdiem® General Purpose Cleaner with Hydrogen Peroxide

Revision: 2020-09-06 Version: 02.0

1. IDENTIFICATION

PERdiem® Product name:

General Purpose Cleaner with Hydrogen Peroxide **Product Code:**

101100678, 94998832, 94998841, 94998859, 95019481, 95613252, 95614052, 95982816

SDS #: MS0800188

Recommended use: Industrial/Institutional Cleaning product

• This product is intended to be diluted prior to use Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier:

US Headquarters Diversey, Inc. 1300 Altura Rd., Suite 125 Fort Mill, SC 29708 Phone: 1-888-352-2249

SDS Internet Address: https://sds.diversey.com

Canadian Headquarters Diversey - Canada, Inc. 3755 Laird Road

Mississauga, Ontario L5L 0B3 Phone: 1-800-668-7171

Emergency telephone number: 1-800-851-7145 (U.S.); 1-651-917-6133 (Int'l);

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

Serious eye damage/eye irritation Category 2A



Signal word: Warning.

Hazard Statements CAUSES SERIOUS EYE IRRITATION.

Precautionary Statements

Avoid contact with eyes, skin and clothing. Wash affected areas thoroughly after handling. May cause irritation to mouth, throat and stomach. IF SWALLOWED: Rinse mouth. Drink a cupful of milk or water. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice or attention. Dispose of in accordance with all federal, state and local applicable regulations. SUPPLEMENTAL INFORMATION:. DO NOT MIX WITH AMMONIA, BLEACH OR OTHER CHLORINATED COMPOUNDS. Mix only with water. Can react to release hazardous gases. May vigorously react with strong alkaline products resulting in spattering and excessive heat.

Health hazards not otherwise classified (HHNOC) - Not applicable Physical hazards not otherwise classified (PHNOC) - Not applicable

Classification for the diluted product

This product, when diluted as stated on the label, is not classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and Canadian Hazardous Products Regulations (HPR) (WHMIS 2015-GHS).

Hazard and Precautionary Statements

None required.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

Ingredient(s)	CAS#	Weight %
Alcohol, C9-C11, ethoxylated	68439-46-3	7 - 13%
Hydrogen peroxide	7722-84-1	1 - 5%
Sodium xylene sulfonate	1300-72-7	1 - 5%
Dodecylbenzene sulfonic acid	68584-22-5	> 0.1 - < 1%

4. FIRST AID MEASURES

Undiluted Product:

Eyes: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice/attention.

Skin: No specific first aid measures are required.

Inhalation: No specific first aid measures are required.

Ingestion: IF SWALLOWED: Rinse mouth. Drink a cupful of milk or water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed Not applicable.

Aggravated Medical Conditions: None known.

Diluted Product:

Eyes: Rinse with plenty of water.

<u>Skin:</u> No specific first aid measures are required <u>Inhalation:</u> No specific first aid measures are required

Ingestion: IF SWALLOWED: Call a Poison Center (1-800-851-7145) or doctor/physician if you feel unwell.

5. FIRE-FIGHTING MEASURES

Specific methods: No special methods required

Suitable extinguishing media: The product is not flammable. Extinguish fire using agent suitable for surrounding fire.

Specific hazards: None known.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: Put on appropriate personal protective equipment (see Section 8.).

Environmental precautions

Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in

and clean-up methods: a chemical waste container. Use a water rinse for final clean-up.

7. HANDLING AND STORAGE

Handling: Can react to release hazardous gases. Do not mix with other products or chemicals except as directed on the label. Mix only with water. Avoid contact with skin, eyes and clothing. Wash thoroughly after handling. Do not taste or swallow. Product residue may remain on/in empty containers. All precautions for handling the product must be used in handling the empty container and residue. Remove and wash contaminated clothing and footwear before re-use. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: Keep tightly closed in a dry, cool and well-ventilated place.

Aerosol Level (if applicable): Not applicable.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines:

Ingredient(s)	CAS#	ACGIH	OSHA
Hydrogen peroxide	7722-84-1	1 ppm (TWA)	1 ppm (TWA)
			1.4 mg/m³ (TWA)

Undiluted Product:

Engineering measures to reduce exposure:

Good general ventilation should be sufficient to control airborne levels.

Personal Protective Equipment

It is the responsibility of the employer to determine the potential risk of exposure to hazardous chemicals for employees in the workplace in order to determine the necessity, selection, and use of personal protective equipment.

Eye protection: Chemical-splash goggles. **Hand protection:** Chemical-resistant gloves.

Skin and body protection:

Respiratory protection:

Hygiene measures:

If major exposure is possible, wear suitable protective clothing and footwear.

No personal protective equipment required under normal use conditions.

Handle in accordance with good industrial hygiene and safety practice.

Diluted Product:

Engineering measures to reduce exposure:

Good general ventilation should be sufficient to control airborne levels.

Personal Protective Equipment

Eye protection:

Hand protection:

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

No personal protective equipment required under normal use conditions.

Hygiene measures:

Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State:LiquidColor:Clear,ColorlessEvaporation Rate:No information availableOdor:No Odor/Odorless

Odor threshold: No information available. Boiling point/range: Not determined

Melting point/range: Not determined Decomposition temperature: Not determined

Autoignition temperature: No information available Solubility: Completely Soluble

Solubility in other solvents: No information available

Density: Specific gravity: 1.026 Kg/L

Bulk density: No information available

Relative Density (relative to water): 1.026

Vapor density: No information available

Vapor pressure: No information available.

Flash point (°F): > 200 °F > 93 °C Partition coefficient (n-octanol/water): No information available

Viscosity: 7 Elemental Phosphorus: 0 % by wt.

VOC: 0 % pH: < 2

Flammability (Solid or Gas): Not applicable Corrosion to metals: Not corrosive to metals

Sustained combustion: Not applicable

Explosion limits: - upper: Not determined - lower: Not determined

Dilution pH:

Dilution Flash Point (°F): > 200 °F > 93.4 °C

VOC % by wt. at use dilution: 0.0 %

* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

10. STABILITY AND REACTIVITY

Reactivity: Not Applicable Stability: The product is stable

Possibility of hazardous reactions: May vigorously react with strong alkaline products resulting in spattering and excessive heat.

Hazardous decomposition products: Oxygen.

Materials to avoid: Strong bases. Ammonia. Do not mix with chlorinated products (such as bleach). Do not mix with any

other product or chemical unless specified in the use directions.

Conditions to avoid: None known.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Skin contact, Inhalation, Eye contact

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: Unlikely to be irritant in normal use.

Eye contact: Causes serious eye irritation. Symptoms may include pain, redness, and watering.

Ingestion: Symptoms may include stomach pain and nausea. May be irritating to mouth, throat and stomach.

Inhalation: Symptoms may include coughing and difficulty breathing. May be irritating to nose, throat, and respiratory tract.

Sensitization: No known effects.

Target Organs (SE): None known

Target Organs (RE): None known

Numerical measures of toxicity

ATE - Oral (mg/kg): >5000
ATE - Dermal (mg/kg): >5000
ATE - Inhalatory, mists (mg/l): >20
ATE - Inhalatory, vapors (mg/l): >50

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products (undiluted product): This product, as sold, if discarded or disposed, is a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

Waste from residues / unused products (diluted product): This product, when diluted as stated on this SDS, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

RCRA Hazard Class (undiluted product): D002 Corrosive Waste

RCRA Hazard Class (diluted product): Not Regulated Contaminated Packaging: Do not re-use empty containers.

14. TRANSPORT INFORMATION

<u>DOT/TDG/IMDG:</u> The information provided below is the full transportation classification for this product. This description does not account for the package size(s) of this product, that may fall under a quantity exception, according to the applicable transportation regulations. When shipping dangerous goods, please consult with your internal, certified hazardous materials specialist to determine if any exceptions can be applied to your shipment.

DOT (Ground) Bill of Lading Description: NOT REGULATED

15. REGULATORY INFORMATION

International Inventories at CAS# Level

Ingredient(s)	CAS#	MARTK:	NJRTK:	PARTK:	RIRTK:
Water	7732-18-5	-	-	-	-
Alcohol, C9-C11, ethoxylated	68439-46-3	=	=	=	-
Hydrogen peroxide	7722-84-1	X	X	X	X
Sodium xylene sulfonate	1300-72-7	=	=	=	-
Dodecylbenzene sulfonic acid	68584-22-5	=	=	=	=

CERCLA/ SARA

Ingredient(s)	CAS#	Weight %	CERCLA/SARA RQ (lbs)	Section 302 TPQ (lbs)	Section 313
Hydrogen peroxide	7722-84-1	1 - 5%		1000	

16. OTHER INFORMATION

NFPA (National Fire Protection Association)

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 2 Flammability 0 Instability 0 Special Hazards -

Diluted Product:

Health 0 Flammability 0 Instability 0 Special Hazards -

Revision: 2020-09-06 **Version:** 02.0

Reason for revision: Not applicable

Prepared by:

Additional advice:

North American Regulatory Affairs

Does not contain an added fragrance

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.