



Floor Science® Cleaner & Restorer Spray Buff

Version Number: 2

Preparation date: 2017-01-27

1. IDENTIFICATION

Product name: Floor Science® Cleaner & Restorer Spray Buff
Product Code: CBD540458
SDS #: MS0801133
Recommended use:

- Floor care
- This product is intended to be used neat.

Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier:

US Headquarters Diversey, Inc. 2415 Cascade Pointe Blvd. Charlotte, NC 28208 Phone: 1-888-352-2249 SDS Internet Address: https://sds.diversey.com	Canadian Headquarters Diversey Canada, Inc. 3755 Laird Road Units 8-11 Mississauga, Ontario L5L 0B3 Phone: 1-800-668-7171
---	---

Emergency telephone number: 1-800-851-7145; 1-651-917-6133 (Int'l)

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

Serious eye damage/eye irritation Category 2A
 Skin sensitization Category 1



Signal Word: Warning.

Hazard and Precautionary Statements

CAUSES SERIOUS EYE IRRITATION. MAY CAUSE AN ALLERGIC SKIN REACTION.

If medical advice is needed, have product container or label at hand. Keep out of reach of children. Keep container tightly closed. Avoid breathing spray. Avoid contact with eyes, skin and clothing. Wash affected areas thoroughly after handling. May cause irritation to mouth, throat and stomach. Contaminated work clothing should not be allowed out of the workplace. Wear chemical-splash goggles and chemical-resistant gloves. IF SWALLOWED: Rinse mouth. Drink a cupful of milk or water. IF ON SKIN: Wash with plenty of soap and water. Wash contaminated clothing before reuse. IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice or attention. Dispose of in accordance with all federal, state and local applicable regulations.

Health hazards not otherwise classified (HHNOC) - Not applicable

Physical hazards not otherwise classified (PHNOC) - Not applicable

Classification for the diluted product @ RTU

Hazard and Precautionary Statements

See undiluted product information above.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

*Exact percentages are being withheld as trade secret information

4. FIRST AID MEASURES

Undiluted Product:

Eyes: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing for at least 15 minutes. If eye irritation persists: Get medical advice/attention.

Skin: IF ON SKIN: Wash with plenty of soap and water. IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water for at least 15 minutes.

Inhalation: No specific first aid measures are required.

Ingestion: IF SWALLOWED: Rinse mouth. Drink a cupful of milk or water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed: Not applicable.

Aggravated Medical Conditions: None known.

Diluted Product:

This product is intended to be used neat.

Eyes: See undiluted product information above.

Skin: See undiluted product information above.

Inhalation: See undiluted product information above.

Ingestion: See undiluted product information above.

5. FIRE-FIGHTING MEASURES

Specific methods: No special methods required

Suitable extinguishing media: The product is not flammable. Extinguish fire using agent suitable for surrounding fire.

Specific hazards: Not applicable.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: Put on appropriate personal protective equipment (see Section 8.).

Environmental precautions and clean-up methods: Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Use a water rinse for final clean-up.

7. HANDLING AND STORAGE

Handling: Avoid contact with skin, eyes and clothing. Do not taste or swallow. Wash thoroughly after handling. Remove and wash contaminated clothing and footwear before re-use. Handle in accordance with good industrial hygiene and safety practice. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: Protect from freezing. Keep tightly closed in a dry, cool and well-ventilated place. KEEP OUT OF REACH OF CHILDREN.

Aerosol Level (if applicable): Not applicable.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines:

Undiluted Product:

Engineering measures to reduce exposure:

No special ventilation requirements. General room ventilation is adequate.

Personal Protective Equipment

Eye protection: No special requirements under normal use conditions.
Hand protection: Chemical-resistant gloves.
Skin and body protection: If major exposure is possible, wear suitable protective clothing and footwear.
Respiratory protection: . No special requirements under normal use conditions.
Hygiene measures: Handle in accordance with good industrial hygiene and safety practice.

Diluted Product: This product is intended to be used neat.

Engineering measures to reduce exposure:
 No special ventilation requirements. General room ventilation is adequate.

Eye protection: No special requirements under normal use conditions.
Hand protection: Chemical-resistant gloves.
Skin and body protection: No personal protective equipment required under normal use conditions.
Respiratory protection: No special requirements under normal use conditions.
Hygiene measures: Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

<p>Physical State: Liquid Evaporation Rate: No information available Odor threshold: No information available. Melting point/range: Not determined Autoignition temperature: No information available Solubility in other solvents: No information available Density: 8.33 lbs/gal 0.999 Kg/L Bulk density: No information available Flash point (°F): > 200 °F > 93.4 °C Viscosity: No information available VOC: 0 % * Flammability (Solid or Gas): Not applicable Sustained combustion: Not applicable Explosion limits: - upper: Not determined - lower: Not determined @ RTU 7 > 200 °F > 93.4 °C</p>	<p>Color: Clear Straw Odor: Characteristic Boiling point/range: Not determined Decomposition temperature: Not determined Not applicable Solubility: Dispersible Relative Density (relative to water): 0.999 Vapor density: No information available Vapor pressure: No information available. Partition coefficient (n-octanol/water): No information available Elemental Phosphorus: 0.00 % by wt. pH: 7 Corrosion to metals: Not corrosive</p>
---	---

VOC % by wt. at use dilution 0

* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

10. STABILITY AND REACTIVITY

Reactivity: Not Applicable
Stability: The product is stable
Hazardous decomposition products: None reasonably foreseeable.
Materials to avoid: Do not mix with any other product or chemical unless specified in the use directions.
Conditions to avoid: No information available.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Eye contact, Skin contact, Inhalation

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: Unlikely to be irritant in normal use.
Eye contact: Causes serious eye irritation. Symptoms may include pain, redness, and watering.
Ingestion: May be irritating to mouth, throat and stomach. Symptoms may include stomach pain and nausea.
Inhalation: May be irritating to nose, throat, and respiratory tract. Symptoms may include coughing and difficulty breathing.
Sensitization: May cause an allergic skin reaction. Symptoms may include rash, hives, itching, bumps, redness, swelling, and/or discomfort.
Target Organs (SE): None known
Target Organs (RE): None known

Numerical measures of toxicity LD50 > 5000
ATE - Oral (mg/kg): >5000

ATE - Inhalatory, mists (mg/l): >20

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products (undiluted product): This product, as sold, if discarded or disposed, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Under RCRA, it is the responsibility of the user of the product to determine, at the time of disposal, whether the waste solution meets RCRA criteria for hazardous waste. Dispose in compliance with all Federal, state, provincial, and local laws and regulations.

Waste from residues / unused products (diluted product): Not applicable.

RCRA Hazard Class (undiluted product): Not Regulated

RCRA Hazard Class (diluted product): Not Regulated

Contaminated Packaging: Do not re-use empty containers.

14. TRANSPORT INFORMATION

DOT (Ground) Bill of Lading Description: NOT REGULATED

IMDG (Ocean) Bill of Lading Description: NOT REGULATED

15. REGULATORY INFORMATION

International Inventories at CAS# Level

All components of this product are listed on the following inventories: U.S.A. (TSCA), Canada (DSL/NDSL).

RIGHT TO KNOW (RTK)

CERCLA/ SARA

Canadian Regulations

16. OTHER INFORMATION

NFPA (National Fire Protection Association)

Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 2

Flammability 0

Instability 0

Diluted Product: This product is intended to be used neat.

Version Number: 2

Preparation date: 2017-01-27

Reason for revision: Not applicable

Prepared by: NAPRAC

Additional advice: • Does not contain an added fragrance

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.