

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

1 Identification

- **Product identifier** EAEDC408
- **Trade name:** Metered Spray Refill AIR-PRO Aerosol Green Apple
- **Manufacturer article number:** EAEDC408
- **Application of the substance / the mixture** Air Freshener
- **Details of the supplier of the safety data sheet** (826)(190)
- **Manufacturer/Supplier:**
Industrias Salcom, SA de CV
Calle 2 No. 10540
Parque Industrial El Salto
EL SALTO, JAL, ZP.45680
MEXICO
fredcominu@wiese.com.mx
- **Information department:** Product safety department
- **Emergency telephone number:** +52 33 3688 0850

2 Hazard(s) identification

- **Classification of the substance or mixture**



GHS02 Flame

Flam. Aerosol 1 H222 Extremely flammable aerosol.



GHS04 Gas cylinder

Press. Gas H280 Contains gas under pressure; may explode if heated.



GHS07

Eye Irrit. 2A H319 Causes serious eye irritation.

STOT SE 3 H336 May cause drowsiness or dizziness.

- **Label elements**

- **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

- **Hazard pictograms**



GHS02



GHS04



GHS07

- **Signal word** Danger

- **Hazard-determining components of labeling:**

acetone

- **Hazard statements**

Extremely flammable aerosol.

Contains gas under pressure; may explode if heated.

Causes serious eye irritation.

May cause drowsiness or dizziness.

(Contd. on page 2)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 1)

· **Precautionary statements**

- If medical advice is needed, have product container or label at hand.
 Keep out of reach of children.
 Read label before use.
 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
 Do not spray on an open flame or other ignition source.
 Pressurized container: Do not pierce or burn, even after use.
 Avoid breathing dust/fume/gas/mist/vapors/spray
 Wash thoroughly after handling.
 Use only outdoors or in a well-ventilated area.
 Wear eye protection / face protection.
 IF INHALED: Remove person to fresh air and keep comfortable for breathing.
 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.
 Continue rinsing.
 Call a poison center/doctor if you feel unwell.
 If eye irritation persists: Get medical advice/attention.
 Store in a well-ventilated place. Keep container tightly closed.
 Store locked up.
 Protect from sunlight. Store in a well-ventilated place.
 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
 Dispose of contents/container in accordance with local/regional/national/international regulations.

· **Classification system:**

· **NFPA ratings (scale 0 - 4)**



· **HMIS-ratings (scale 0 - 4)**



· **Other hazards**

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
 · **vPvB:** Not applicable.

3 Composition/information on ingredients

· **Chemical characterization: Mixtures**

· **Description:** Mixture of the substances listed below with nonhazardous additions.

· **Dangerous components:**

67-64-1	acetone	>50-≤100%
75-28-5	isobutane	>10-≤25%
74-98-6	propane	>2.5-≤10%
106-97-8	butane	≤2.5%
	Fragrance Trade secret (826)	≤2.5%

US

(Contd. on page 3)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 2)

4 First-aid measures

- **Description of first aid measures**
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:** Generally the product does not irritate the skin.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Information for doctor:**
- **Most important symptoms and effects, both acute and delayed** No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
Use fire-extinguishing media appropriate for surrounding materials. Foam. Dry powder. Carbon dioxide. Water spray. Sand.
- **Special hazards arising from the substance or mixture** No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures**
Wear protective equipment. Keep unprotected persons away.
- **Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.
- **Protective Action Criteria for Chemicals**

· PAC-1:

67-64-1	acetone	200 ppm
75-28-5	isobutane	5500* ppm
74-98-6	propane	5500* ppm
106-97-8	butane	5500* ppm
142-90-5	dodecyl methacrylate	6.9 ppm
110-91-8	morpholine	30 ppm

· PAC-2:

67-64-1	acetone	3200* ppm
75-28-5	isobutane	17000** ppm
74-98-6	propane	17000** ppm
106-97-8	butane	17000** ppm

(Contd. on page 4)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 3)

142-90-5	dodecyl methacrylate	76 ppm
110-91-8	morpholine	1,300 ppm
· PAC-3:		
67-64-1	acetone	5700* ppm
75-28-5	isobutane	53000*** ppm
74-98-6	propane	33000*** ppm
106-97-8	butane	53000*** ppm
142-90-5	dodecyl methacrylate	460 ppm
110-91-8	morpholine	8000** ppm

7 Handling and storage

- **Handling:**
- **Precautions for safe handling** Ensure good ventilation/exhaustion at the workplace.
- **Information about protection against explosions and fires:**
Do not spray on a naked flame or any incandescent material.
Keep ignition sources away - Do not smoke.
Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Observe official regulations on storing packagings with pressurized containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep receptacle tightly sealed.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.
- **Control parameters**
- **Components with limit values that require monitoring at the workplace:**
The following constituents are the only constituents of the product which have a PEL, TLV or other recommended exposure limit.
At this time, the remaining constituent has no known exposure limits.

67-64-1 acetone	
PEL	Long-term value: 2400 mg/m ³ , 1000 ppm
REL	Long-term value: 590 mg/m ³ , 250 ppm
TLV	Short-term value: 1187 mg/m ³ , 500 ppm
	Long-term value: 594 mg/m ³ , 250 ppm
	BEI
75-28-5 isobutane	
TLV	Short-term value: 2370 mg/m ³ , 1000 ppm
	(EX)
74-98-6 propane	
PEL	Long-term value: 1800 mg/m ³ , 1000 ppm

(Contd. on page 5)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 4)

REL	Long-term value: 1800 mg/m ³ , 1000 ppm
TLV	refer to Appendix F in TLVs & BEIs book; D, EX
106-97-8 butane	
REL	Long-term value: 1900 mg/m ³ , 800 ppm
TLV	Short-term value: 2370 mg/m ³ , 1000 ppm (EX)

· Ingredients with biological limit values:

67-64-1 acetone	
BEI	50 mg/L Medium: urine Time: end of shift Parameter: Acetone (nonspecific)

· **Additional information:** The lists that were valid during the creation were used as basis.

· **Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

- Keep away from foodstuffs, beverages and feed.
- Immediately remove all soiled and contaminated clothing.
- Wash hands before breaks and at the end of work.
- Avoid contact with the eyes.
- Avoid contact with the eyes and skin.

· **Breathing equipment:**

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use respiratory protective device that is independent of circulating air.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**

Safety glasses



Tightly sealed goggles

US

(Contd. on page 6)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 5)

9 Physical and chemical properties

· Information on basic physical and chemical properties

· General Information

· Appearance:

Form: Aerosol
Color: According to product specification

· **Odor:** Characteristic

· **Odor threshold:** Not determined.

· **pH-value:** Not determined.

· Change in condition

Melting point/Melting range: Undetermined.
Boiling point/Boiling range: -44 °C (-47.2 °F)

· **Flash point:** < 0 °C (<32 °F)

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:** 460 °C (860 °F)

· **Decomposition temperature:** Not determined.

· **Auto igniting:** Product is not selfigniting.

· **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapor mixtures are possible.

· Explosion limits:

Lower: 1.8 Vol %
Upper: 13 Vol %

· **Vapor pressure at 20 °C (68 °F):** 3,000 hPa (2,250.2 mm Hg)

· **Density:** Not determined.

· **Relative density** Not determined.

· **Vapor density** Not determined.

· **Evaporation rate** Not applicable.

· Solubility in / Miscibility with

Water: Not miscible or difficult to mix.

· **Partition coefficient (n-octanol/water):** Not determined.

· Viscosity:

Dynamic: Not determined.
Kinematic: Not determined.

· Solvent content:

Organic solvents: 83.8 %
VOC content: 26.05 %
 260.5 g/l / 2.17 lb/gal

Solids content: 0.9 %

· **Other information** No further relevant information available.

10 Stability and reactivity

· **Reactivity** No further relevant information available.

(Contd. on page 7)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 6)

- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

· Information on toxicological effects

· Acute toxicity:

· LD/LC50 values that are relevant for classification:

67-64-1 acetone

Oral	LD50	5,800 mg/kg (rat)
Dermal	LD50	20,000 mg/kg (rabbit)

· Primary irritant effect:

- **on the skin:** No irritant effect.
- **on the eye:** Irritating effect.
- **Sensitization:** No sensitizing effects known.

· Additional toxicological information:

The product shows the following dangers according to internally approved calculation methods for preparations:
Irritant

· Carcinogenic categories

· IARC (International Agency for Research on Cancer)

110-91-8	morpholine	3
----------	------------	---

· NTP (National Toxicology Program)

None of the ingredients is listed.

· OSHA-Ca (Occupational Safety & Health Administration)

None of the ingredients is listed.

12 Ecological information

· Toxicity

- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Behavior in environmental systems:**
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

US

(Contd. on page 8)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020



Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 7)

13 Disposal considerations

- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

· UN-Number	
· DOT, IMDG, IATA	UN1950
· UN proper shipping name	
· DOT	Aerosols, flammable
· IMDG	AEROSOLS
· IATA	AEROSOLS, flammable
· Transport hazard class(es)	
· DOT	
	
· Class	2.1
· Label	2.1
· IMDG, IATA	
	
· Class	2.1
· Label	2.1
· Packing group	
· DOT, IMDG, IATA	not regulated
· Environmental hazards:	Not applicable.
· Special precautions for user	Warning: Gases
· Danger code (Kemler):	-
· EMS Number:	F-D,S-U
· Stowage Code	SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.
· Segregation Code	SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.

(Contd. on page 9)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 8)

· **Transport/Additional information:**

· **DOT**

· **Quantity limitations**

On passenger aircraft/rail: 75 kg

On cargo aircraft only: 150 kg

· **IMDG**

· **Limited quantities (LQ)**

1L

· **Excepted quantities (EQ)**

Code: E0

Not permitted as Excepted Quantity

· **UN "Model Regulation":**

UN 1950 AEROSOLS, 2.1

15 Regulatory information

· **Safety, health and environmental regulations/legislation specific for the substance or mixture**

· **Sara**

· **Section 355 (extremely hazardous substances):**

None of the ingredients is listed.

· **Section 313 (Specific toxic chemical listings):**

None of the ingredients is listed.

· **TSCA (Toxic Substances Control Act):**

67-64-1 acetone

75-28-5 isobutane

74-98-6 propane

106-97-8 butane

25265-71-8 Dipropylene glycol (isomer unspecified)

142-90-5 dodecyl methacrylate

110-91-8 morpholine

106-22-9 dl-Citronellol

5392-40-5 Citral

127-51-5 alpha-iso-Methylionone

· **TSCA new (21st Century Act) (Substances not listed)**

Fragrance Trade secret (826)

· **Proposition 65**

· **Chemicals known to cause cancer:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients is listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients is listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients is listed.

(Contd. on page 10)

US

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 9)

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency)**

67-64-1	acetone	I
---------	---------	---

· **TLV (Threshold Limit Value established by ACGIH)**

67-64-1	acetone	A4
110-91-8	morpholine	A4

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **GHS label elements** The product is classified and labeled according to the Globally Harmonized System (GHS).

· **Hazard pictograms**



GHS02 GHS04 GHS07

· **Signal word** *Danger*

· **Hazard-determining components of labeling:**

acetone

· **Hazard statements**

*Extremely flammable aerosol.
Contains gas under pressure; may explode if heated.
Causes serious eye irritation.
May cause drowsiness or dizziness.*

· **Precautionary statements**

*If medical advice is needed, have product container or label at hand.
Keep out of reach of children.
Read label before use.
Keep away from heat/sparks/open flames/hot surfaces. - No smoking.
Do not spray on an open flame or other ignition source.
Pressurized container: Do not pierce or burn, even after use.
Avoid breathing dust/fume/gas/mist/vapors/spray
Wash thoroughly after handling.
Use only outdoors or in a well-ventilated area.
Wear eye protection / face protection.
IF INHALED: Remove person to fresh air and keep comfortable for breathing.
If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do.
Continue rinsing.
Call a poison center/doctor if you feel unwell.
If eye irritation persists: Get medical advice/attention.
Store in a well-ventilated place. Keep container tightly closed.
Store locked up.
Protect from sunlight. Store in a well-ventilated place.
Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.
Dispose of contents/container in accordance with local/regional/national/international regulations.*

· **Chemical safety assessment:** *A Chemical Safety Assessment has not been carried out.*

US

(Contd. on page 11)

Safety Data Sheet

acc. to OSHA HCS

Printing date 09/03/2020

Reviewed on 09/03/2020

Trade name: Metered Spray Refill AIR-PRO Aerosol Green Apple

(Contd. of page 10)

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Department issuing SDS:** Product Safety Department
- **Contact:** +52 33 3688 0850
- **Date of preparation / last revision** 09/03/2020 / 12
- **Abbreviations and acronyms:**
 - IMDG: International Maritime Code for Dangerous Goods
 - DOT: US Department of Transportation
 - IATA: International Air Transport Association
 - ACGIH: American Conference of Governmental Industrial Hygienists
 - EINECS: European Inventory of Existing Commercial Chemical Substances
 - ELINCS: European List of Notified Chemical Substances
 - CAS: Chemical Abstracts Service (division of the American Chemical Society)
 - NFPA: National Fire Protection Association (USA)
 - HMIS: Hazardous Materials Identification System (USA)
 - VOC: Volatile Organic Compounds (USA, EU)
 - LC50: Lethal concentration, 50 percent
 - LD50: Lethal dose, 50 percent
 - PBT: Persistent, Bioaccumulative and Toxic
 - vPvB: very Persistent and very Bioaccumulative
 - NIOSH: National Institute for Occupational Safety
 - OSHA: Occupational Safety & Health
 - TLV: Threshold Limit Value
 - PEL: Permissible Exposure Limit
 - REL: Recommended Exposure Limit
 - BEI: Biological Exposure Limit
 - Flam. Aerosol 1: Aerosols – Category 1
 - Press. Gas: Gases under pressure – Compressed gas
 - Eye Irrit. 2A: Serious eye damage/eye irritation – Category 2A
 - STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
- *** Data compared to the previous version altered.**

US