


1 Identification

- **Product identifier**
- **Trade name:** UHU stic
- **Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Application of the substance / the mixture** Adhesives
- **Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
UHU GmbH & Co.KG
Herrmannstraße 7
D-77815 Bühl (Baden)
Tel.: 0049-(0)7223-284-0
email: info@uhu.boltongroup.de
- Fax: 0049-(0)7223-284-245
- **Information department:** CRD
- **Emergency telephone number:** Tel.: +49 (0) 72 23/28 40

2 Hazard(s) identification

- **Classification of the substance or mixture**
 - **Classification according to Directive 67/548/EEC or Directive 1999/45/EC** Not applicable.
 - **Information concerning particular hazards for human and environment:**
The product does not have to be labeled due to the calculation procedure of international guidelines.
 - **Classification system:**
The classification was made according to the latest editions of international substances lists, and expanded upon from company and literature data.
 - **Label elements**
 - **Labelling according to EU guidelines:**
Observe the general safety regulations when handling chemicals.
The product is not subject to identification regulations according to directives on hazardous materials.
 - **Classification system:**
 - **NFPA ratings (scale 0 - 4)**
- 

Health = 0
Fire = 0
Reactivity = 0
- **HMIS-ratings (scale 0 - 4)**
- | | |
|------------|---|
| HEALTH | 0 |
| FIRE | 0 |
| REACTIVITY | 0 |

Health = 0
Fire = 0
Reactivity = 0
- **Other hazards**
 - **Results of PBT and vPvB assessment**
 - **PBT:** Not applicable.
 - **vPvB:** Not applicable.

3 Composition/information on ingredients

- **Chemical characterization:** Mixtures
- **Description:** Adhesive
- **Dangerous components:** Void

Trade name: UHU stic

(Contd. of page 1)

4 First-aid measures

- **Description of first aid measures**
- **General information:** No special measures required.
- **After inhalation:** No special measures required.
- **After skin contact:**
Immediately rinse with water.
Generally the product does not irritate the skin.
- **After eye contact:**
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:** If symptoms persist consult doctor.
- **Most important symptoms and effects, both acute and delayed**
No further relevant information available.
- **Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
CO₂, extinguishing powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **Special hazards arising from the substance or mixture**
No further relevant information available.
- **Advice for firefighters**
- **Protective equipment:** No special measures required.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures** Not required.
- **Environmental precautions:** No special measures required.
- **Methods and material for containment and cleaning up:**
Send for recovery or disposal in suitable receptacles.
- **Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

7 Handling and storage

- **Precautions for safe handling** No special measures required.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Protect from frost.
- **Specific end use(s)** No further relevant information available.

8 Exposure controls/personal protection

- **Additional information about design of technical systems:** No further data; see item 7.

(Contd. on page 3)

Trade name: UHU stic

(Contd. of page 2)

- **Control parameters**
- **Components with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists that were valid during the creation were used as basis.
- **Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures for handling chemicals should be followed.
Avoid direct contact with the chemical/ the product/ the preparation by organizational measures.
- **Breathing equipment:** Not required.
- **Protection of hands:** Not required.
- **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Not required.

9 Physical and chemical properties

- **Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

Form:	Solid
Color:	White
- **Odor:** Characteristic
- **pH-value at 20 °C:** 10.5
- **Change in condition**

Melting point/Melting range:	64-65 °C
Boiling point/Boiling range:	100 °C
- **Flash point:** Not applicable.
- **Ignition temperature:** 395 °C
- **Auto igniting:** Product is not selfigniting.
- **Danger of explosion:** Product does not present an explosion hazard.
- **Vapor pressure at 20 °C:** 23 hPa
- **Density at 20 °C:** 1.17 g/cm³
- **Solubility in / Miscibility with**

Water:	Soluble.
--------	----------
- **Viscosity:**

Dynamic:	Not applicable.
Kinematic:	Not applicable.
- **Solvent content:**

Organic solvents:	0.0 %
Water:	55.5 %

(Contd. on page 4)

Printing date 01/14/2014

Reviewed on 01/14/2014

Trade name: UHU stic

(Contd. of page 3)

· **Other information** No further relevant information available.

10 Stability and reactivity

- **Reactivity**
- **Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **Possibility of hazardous reactions** No dangerous reactions known.
- **Conditions to avoid** No further relevant information available.
- **Incompatible materials:** No further relevant information available.
- **Hazardous decomposition products:** No dangerous decomposition products known.

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **Primary irritant effect:**
- **on the skin:** No irritant effect.
- **on the eye:** No irritating effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**
The product is not subject to classification according to internally approved calculation methods for preparations:
When used and handled according to specifications, the product does not have any harmful effects according to our experience and the information provided to us.

- **Carcinogenic categories**

- **IARC (International Agency for Research on Cancer)**

9003-39-8 Polyvinylpyrrolidone

3

- **NTP (National Toxicology Program)**

None of the ingredients is listed.

12 Ecological information

- **Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **Persistence and degradability** No further relevant information available.
- **Bioaccumulative potential** No further relevant information available.
- **Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (Self-assessment): slightly hazardous for water
Do not allow product to reach ground water, water course or sewage system.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects** No further relevant information available.

CA

(Contd. on page 5)

Printing date 01/14/2014

Reviewed on 01/14/2014

Trade name: UHU stic

(Contd. of page 4)

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Smaller quantities can be disposed of with household waste.
Disposal must be made according to official regulations.
- **Uncleaned packagings:**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

· UN-Number	Void
· DOT, TDG, ADN, IMDG, IATA	Void
· UN proper shipping name	Void
· DOT, TDG, ADN, IMDG, IATA	Void
· Transport hazard class(es)	Void
· Class	Void
· Packing group	Void
· DOT, TDG, IMDG, IATA	Void
· Environmental hazards:	
· Marine pollutant:	No
· Special precautions for user	Not applicable.
· Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code	Not applicable.
· Transport/Additional information:	Not dangerous according to the above specifications.

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Sara**
- **Section 355 (extremely hazardous substances):**
None of the ingredient is listed.
- **Section 313 (Specific toxic chemical listings):**
None of the ingredients is listed.
- **TSCA (Toxic Substances Control Act):**
All ingredients are listed.
- **Proposition 65**
- **Chemicals known to cause cancer:**
None of the ingredients is listed.
- **Chemicals known to cause reproductive toxicity for females:**
None of the ingredients is listed.
- **Chemicals known to cause reproductive toxicity for males:**
None of the ingredients is listed.
- **Chemicals known to cause developmental toxicity:**
None of the ingredients is listed.

(Contd. on page 6)

Printing date 01/14/2014

Reviewed on 01/14/2014

Trade name: UHU stic

(Contd. of page 5)

· **Cancerogenity categories**

· **EPA (Environmental Protection Agency)**

None of the ingredients is listed.

· **TLV (Threshold Limit Value established by ACGIH)**

None of the ingredients is listed.

· **MAK (German Maximum Workplace Concentration)**

None of the ingredients is listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health)**

None of the ingredients is listed.

· **OSHA-Ca (Occupational Safety & Health Administration)**

None of the ingredients is listed.

· **Canadian substance listings:**

· **Canadian Domestic Substances List (DSL)**

All ingredients are listed.

· **Canadian Ingredient Disclosure list (limit 0.1%)**

None of the ingredients is listed.

· **Canadian Ingredient Disclosure list (limit 1%)**

57-11-4 stearic acid, pure

· **Product related hazard informations:**

Observe the general safety regulations when handling chemicals.

The product is not subject to identification regulations according to directives on hazardous materials.

· **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Department issuing MSDS:** CRD

· **Contact:**

Frau A. Liar,

Herr Dr. C. Hanf