

FlexPoint Modular Media Converters


**The flexible media converter solution
that grows with your network.**



FEATURES

- » More interface choices than any other media converter system.
- » Easy installation—no software required.
- » FlexPoint Media Converters work as standalone or hot-swappable chassis-based media converters.
- » The FlexPoint Power Chassis holds up to 14 media converters and features single or dual hot-swappable AC power supplies.

Link different media types together in one local area network.



OVERVIEW

FlexPoint™ Modular Media Converters from Black Box provide the ultimate in flexibility and reliability for your expanding multimedia LAN. These standalone converters are also chassis-based modules!

Plus, FlexPoint offers you more interface options than any other media converter system. Your choices include:

- Ethernet
- Gigabit Ethernet
- UTP
- Single-mode fiber
- Multimode fiber
- Coax
- 10/100 rate converters
- Single-mode to multimode fiber converters

FlexPoint Media Converters make it easy to expand your networks as your company grows. The incredible variety and versatility of this system make it ideal for networks that are subject to constant upgrades and changes.

LEDs on each FlexPoint Media Converter display status.

Tailor the system to your requirements. Get the media converters you need now and use them individually. Then, when your LAN grows, mount your media converters on the

wall, in the 5-Position Rackmounting Kit, as modules in the Power Chassis, or on a DIN rail. The Power Chassis holds 14 media converters and a Single or Dual AC or DC Power Supply.

10BASE-T to BNC

This media converter joins unshielded twisted-pair (UTP) and coax LANs together to form one network.

For UTP, the 10BASE-T/BNC converter supports Category 3, 4, and 5 wiring at distances of 328 feet (100 m). This model also corrects wiring-polarity reversals and eliminates crossed cables with a crossover switch.

For coax, this converter has a BNC connector that supports 50-ohm cable at up to 607 feet (185 m). And you don't need a T-connector—switch-selectable termination is built in.

10BASE-FL to BNC

The LMC211A-KIT 10BASE-FL to 10BASE2 media converter kit connects a ThinNet LAN to Multimode fiber to form one network. The kit consists of a LMC210A, a short RJ-45 to RJ-45 cable, and a LMC212A-MM-R3. The LMC210A converts 10BASE2 BNC to 10BASE-T and will be connected through a short RJ-45 to RJ-45 cable to the LMC212A-MM-R3 which converts 10BASE-T to 10BASE-FL. The fiber connection has 850 nm Multimode ST connectors rated for a fiber length of 1.2 miles (2 km).

On the coax side, the converters have BNC connectors and support 50-ohm cable at distances of up to 607 feet (185 m). You can connect up to 30 workstations to this segment per the 802.3 IEEE standard.

A switch-selectable terminator is built in.

10BASE-T to 10BASE-FL

These media converters join unshielded twisted-pair (UTP) and fiber LANs into one network. They support half- and full-duplex (10- and 20-Mbps) operation.

For fiber, these converters use SC or ST® connectors in 850-nm multimode, 1300-nm multimode, or 1300-nm single-mode.

For UTP, these media converters use an EIA/TIA modular 568 RJ-45 connector and support Category 3, 4, and 5 wiring, connecting at distances up to 328 feet (100 m).

10BASE-T to 10BASE-FL converters also correct wiring-polarity reversals and eliminate crossed cables with a crossover switch.

100BASE-TX to 100BASE-FX

This group of media converters connects Fast Ethernet 100BASE-FX fiber to 100BASE-TX UTP LANs. They use auto-negotiation for full- and half-duplex operation and can handle numerous fiber types.

These converters auto-adapt to the highest performance level supported by the device that is connected to the UTP port. When the device supports full-duplex, the converter adapts to full-duplex mode and creates a 200-Mbps bandwidth. When the connected device supports only half-duplex, the converter adapts to this mode and creates a 100-Mbps bandwidth. Full- and half-duplex operation can also be controlled by a manual override switch.

The fiber side of these converters operates at 1300 nm and uses ST or SC connectors. Multimode models can support distances of up to 1.2 miles (2 km).

The UTP port, which supports distances of up to 328 feet (100 m), has a modular 568 RJ-45 connector for Category 5 wiring.

A crossover switch eliminates the need for crossed cables.

Gigabit UTP to Fiber

Use FlexPoint Gigabit UTP to Fiber Media Converters to convert Gigabit Ethernet 1000BASE-T unshielded twisted-pair (UTP) cable to 1000BASE-SX single- or 1000BASE-LX multimode fiber. The converters comply with the IEEE 802.3 standard.

The converters auto-adapt to the full-/half-duplex and flow-control services supported by the device connected to its UTP port. User-selectable override options set the desired mode.

The converters operate in full-duplex to provide an effective 2-Gbps data rate or in half-duplex mode to provide a 1-Gbps rate. This maximizes the throughput when connecting to high-bandwidth full-duplex services such as servers or switches.

Network flow control is supported via an auto-selected or user-selected "Pause" function that helps relieve network congestion by providing "backpressure" to the sending device.

The converter supports 850-nm (SX) or 1300-nm (LX) and uses SC or LC connectors. The Multimode SX supports distances of up to 722 feet (220 m); the single-mode models support distances of up to 6.2 miles (10 km).

User-selectable Link Propagation is available for Spanning-Tree redundant network architectures as well as for connecting to SNMP or other network-managed devices that monitor link availability. A user-selectable override is provided to isolate the link detection to a per-segment basis.

The converter's UTP port uses a modular EIA/TIA 568 RJ-45 connector and supports Category 5 or higher wiring with distances of up to 328 feet (100 m). Automatic polarity detection and correction assists in network installation and maintenance.

100-Mbps Fiber-to-Fiber Mode Converters

Multimode-to-Single-Mode converters connect to the network over multimode fiber. But between Media Converters, they connect with single-mode fiber to give you distances up to 17.4 miles (28 km).

Multimode-to-Multimode versions extend your network up to 3.1 miles (5 km).

100-Mbps Fiber-to-Fiber Mode Converters support Ethernet and Fast Ethernet.

1000-Mbps Multimode-to-Single-Mode

1000-Mbps Multimode-to-Single-Mode converters connect to the network over multimode fiber and extend the network with single-mode fiber. The converters comply with IEEE 802.3 and 1000BASE-LX/SX standards.


10/100 Rate Converters

This group of rate converters connects Fast Ethernet 100BASE-FX fiber to 10BASE-T or 100BASE-TX UTP LANs. They use autonegotiation for full- and half-duplex operation and can handle numerous fiber types. An override switch provides total manual control over the 10/100 operation of the UTP port and the half-/full-duplex operation of both the fiber and UTP port.

The fiber port operates at 1300 nm and features SC or ST connectors. Multimode models support distances of 1.2 miles (1.9 km), and single-mode models support up to 16.8 miles (27 km).

These converters also feature a 1 MB store-and-forward buffer and MAC address learning.





LMC206-WALL



LMC200:
shown with modules



LMC205:
shown with modules

T1/E1 Copper to Fiber Line Drivers

FlexPoint T1/E1 Copper to Fiber Line Drivers convert coax and twisted pair to multimode or single-mode fiber—and they extend T1/E1 over fiber.

T1/E1 Copper to Fiber Line Drivers feature a crossover switch on the RJ-45/RJ-48 port for easy connections to equipment. Dry relay contacts on Pins 3 and 6 of the RJ-45 connector provide connection to alarm equipment. The contact closes when the signal is lost on the copper or fiber connection.

LEDs display the T1/E1 link status, diagnostic modes of operation, and line segment errors.

The line drivers support AMI, B8ZS, and HDB3 line codes.

To install any of the converters on a DIN rail, select the DIN Rail Mounting Kit (LMC207-DRM).

TECH SPECS

Power Chassis:

Indicators — LED: (1) Power

Power — LMC200: 115-230-VAC, 50-60-Hz, autosensing single power supply;

LMC200-2PS: 115-230-VAC, 50-60-Hz, autosensing dual power supply

Size — 3"H x 19"W x 10"D (7.6 x 48.3 x 25.4 cm)

Weight — 7 lb. (3.2 kg)

5-Position Rackmounting Kit:

Size — 1.75" (1U) H x 19"W x 5"D (4.4 x 48.3 x 12.7 cm)

Weight — 2 lb. (0.9 kg)

Modules:

CE Approval — Yes

Power — 110-VAC, 60-Hz, external power supply (230-VAC, 50-Hz version on request) or from Power Chassis

Size — 1"H x 3"W x 4"D (2.5 x 7.6 x 10.2 cm)

Weight — 0.4 lb. (0.2 kg)

What's included

Media Converter Chassis (LMC200 and LMC200-2PS):

- Chassis
- Power cord
- User's manual

Media Converter Modules:

- Converter
- Power supply
- User's manual

Item


Code

FlexPoint 14-Slot Power Chassis	
Single Power Supply	LMC200
115-230 VAC	
Dual Power Supply	LMC200-2PS
115-230 VAC	
5-Position Rackmounting Kit—Nonpowered Rack	
Holds up to Five FlexPoint Media Converters	LMC205
Wallmounting Hardware for Single FlexPoint Media Converter	LMC206-WALL
FlexPoint Media Converter Modules	
ThinNet	
10BASE-T/BNC	LMC210A
10BASE-FL/BNC	LMC211A-KIT
850-nm, Multimode, 2 km	
ST functionality through LMC210A, a short RJ-45 to RJ-45 cable, and LMC212A-MM-R3	
10BASE-T to 10BASE-FL	
850-nm, Multimode, 2 km	
ST	LMC212A-MM-R3
SC	LMC212A-MM-SC-R2
1300-nm, Multimode, 5 km	
ST	LMC212A-13MM-R3
1300-nm, Multimode, 15 km	
ST	LMC212A-SM-R3
100-Mbps UTP to Fiber	
100BASE-TX to 100BASE-FX	
1310-nm, Multimode, 2 km Full Duplex, 412 m Half-Duplex	
ST	LMC213A-MMST-R2
SC	LMC213A-MMSC-R2
1310-nm, Single-Mode, 25 km	
ST	LMC213A-SMST-R2
SC	LMC213A-SMSC-R2
Gigabit UTP to Fiber	
1000BASE-T to 1000BASE-SX (UTP to Fiber)	
850-nm, Multimode, 220 m	
SC	LMC1003A-R3
1000BASE-T to 1000BASE-LX	
1300-nm, Single-Mode, 10 km	
SC	LMC1004A-R3
100-Mbps Fiber-to-Fiber Mode Converters	
1300-nm Multimode to 1300-nm Single-Mode, 5 km-28 km	
ST to ST	LMC250A-ST
SC to SC	LMC250A
1300-nm Multimode to 100BASE-FX 1300-nm SC to SC	LMC250A-LH
1300-nm Multimode to 1300-nm Multimode, 5 km to 5 km Full Duplex, 412 m to 412 m Half-Duplex	
ST to ST	LMC253A-ST





LMC100A-R3



MT660A-MM

Item

Code

FlexPoint Media Converter Modules (Continued)

1000-Mbps Multimode to Single-Mode Fiber-to-Fiber Mode Converters

850-nm Multimode to 1300-nm Single-Mode,
220 m Multimode to 5 km Single-Mode

SC to SC **LMC1001A**

10/100 Rate Converters

1300-nm, Multimode, 2 km

ST **LMC100A-R3**

SC **LMC100A-SC-R3**

LC **LMC100A-LC-R2**

1300-nm, Single-Mode, 28 km

ST **LMC100A-SM-R3**

1300-nm, Single-Mode, 58 km

SC **LMC100A-SMSC-LH-R2**

T1/E1 Copper to Fiber Line Drivers

1310-nm, Multimode, 5 km

ST **MT660A-MM**

FlexPoint Accessories and Replacement Parts

Power Supply for Power Chassis

115-230 VAC **PSFP200**

DC Power Converter, 18-to-72 VDC

Standalone **LMC204A**

DC Power Converter

Wallmounting Kit **LMC206A-WALL-DC**

International Power Supply for all

FlexPoint Models (9 V, 1 A) **LMC203A**

To install the converter on DIN rails, order...

FlexPoint DIN Rail Mounting Kit **LMC207-DRM**

You may also need...

Cat5e cable 4 pair straight-pinned, PVC **EVNSL85**

Duplex Fiber Optic Cable, PVC, ST-ST **EFN110**

Single-Mode Duplex Fiber Optic Cable, PVC,

ST-ST **EFN310**

T1 Cable, RJ-48/RJ-48, Straight-Pinned **ETNMSR01**

