

## **41U Rack Enclosure Server Cabinet - 32.3 in. Deep - Built-in Fans**

Product ID: 7236CABINET



This 41U 36in Black Server Rack Cabinet offers a lockable, dust-reduced environment for rackmount servers and network equipment. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

With exterior dimensions of H 75.5in x W22in x D35.5in (cabinet only), this sturdy space-saving unit is made from extruded aluminum for an appealing appearance. A standard lockable smoked plexiglass (see-through) front door and solid aluminum rear door provide quick access to installed equipment.

The internal front and rear mounting rails are spaced to accept standard 19in rackmount devices and are completely depth adjustable as to be able to fit virtually any piece of equipment that is less than 33in deep. A standard roof-mounted triple motor AC fan unit and high-flow air filter below the rear door provide up to 300 CFM of bottom to top air flow through the cabinet, removing the heat produced by the enclosed equipment.

In addition to the standard equipment that are options on most other cabinets, the StarRack Cabinet also has a full complement of optional accessories like fixed shelving, storage drawers, keyboard drawers, front panel spacer plates, and slide-out shelves.

### Certifications, Reports and Compatibility



### Features

- Extruded aluminum construction provides rounded corners and edges for an attractive appearance
- Fully forward/back adjustable mounting rails inside cabinet
- TAA compliant for GSA Schedule purchases
- Front and back doors are removable and can be switched to open left or right
- Rolling casters provide full mobility
- Three (3) roof-mounted fans exhaust up to 300 CFM of air
- Many accessory options available like mounting shelves, keyboard drawers, storage drawers, sliding shelves, front blanking plates, etc.
- Comes fully assembled
- Includes (3) 5" ball bearing AC fans moving up to 300 CFM of air, air filter and adjustable levelers at each corner
- Also comes with front flip-up stabilizers, removable smoked acrylic front door with 2 keys, removable rear door and 50 Philips-head mounting screws

	Warranty	Lifetime
<b>Hardware</b>	Additional Required Tools	Phillips Screwdriver
	Adjustable Mounting Rails	Yes
	Back Door Construction	Solid Steel
	Back Door Key Lock	Yes
	Back Door Reversible and/or Removable	Removable
		Reversible
	Cable Management	Yes C-Hooks
	Casters	Included
	Fan(s)	Yes
	Fans	3 - 120 mm
	Frame Type	Enclosed Cabinet
	Front Door Construction	Steel w/ Window
	Front Door Key Lock	Yes
	Front Door Reversible and/or Removable	Removable
		Reversible
	Industry Standards	EIA-310-D
		EIA RS310-C
	Ladder Type	L-Shape
	Mounting Holes	Square
	Number and Type of Included Cage Nuts	92 - M5
	Rack Type	4-Post
	Side Panel Construction	Solid Steel
	Tools Included	No
	U Height	41U
	U Markings	No
	Wallmountable	No
<b>Performance</b>	Noise Level	39 dBA
	Weight Capacity (Stationary)	2210 lb [1000 kg]

<b>Special Notes / Requirements</b>	<b>Note</b>	Includes 2 locking front casters, and 2 rear swivel casters
<b>Power</b>	Input Current	0.13/0.14 A
	Input Voltage	115V AC
<b>Physical Characteristics</b>	Color	Black
	Enclosure Type	Steel and Aluminum
	Height with Casters	78.8 in [200.2 cm]
	Internal Depth	35 in [89 cm]
	Internal Height	71.8 in [1824 mm]
	Internal Width	21.8 in [554 mm]
	Maximum Mounting Depth	32.3 in [820 mm]
	Minimum Mounting Depth	14.2 in [360 mm]
	Product Height	75.4 in [1914 mm]
	Product Length	35.4 in [900 mm]
	Product Weight	200.5 lb [90.7 kg]
	Product Width	22 in [560 mm]
	Rail Thickness	0.1 in [2 mm]
<b>Packaging Information</b>	Flat Pack (Assembly Required)	No
	Shipping (Package) Weight	218.5 lb [98.9 kg]
<b>What's in the Box</b>	Included in Package	1 - H72"xW19"xD36" 41U Cabinet Equipment Rack 1 - Bag of screws, fasteners and keys

Product appearance and specifications are subject to change without notice.