

WorkCentre®
3210 / 3220

Letter-size
Black-and-white
Multifunction Printer



Xerox WorkCentre® 3210 / 3220
Multifunction Laser Printer
Maximized efficiency,
tailored to your desktop

xerox 

WorkCentre® 3210/3220 Multifunction Laser Printer

True office productivity on your desktop. The WorkCentre 3210/3220 is a highly compact device complete with extensive features to increase performance and manage costs. This value-packed and reliable all-in-one print/copy/scan/fax device has been designed with individuals and small workteams in mind.

Performance-tuned for busy professionals

The WorkCentre 3210/3220 puts a premium on efficiency, giving you the power and functions you need to stay on top of heavy workloads.

30
ppm

- **Fast output keeps pace with high demand.** Print speeds up to 30 ppm, and a rapid first-page-out time of less than 8.5 seconds, deliver documents fast.
- **Concurrent operation** means you can quickly scan a file when you need it, even while other jobs are printing.
- **Flexible paper handling.** Reliably feed a wide variety of media, including cardstocks, transparencies, envelopes and papers ranging from 16 to 43 lb. (60 – 163 gsm).
- **Sharp, clear images and text,** with up to 1200 x 1200 enhanced image quality plus PCL® 6 and PCL 5e printer languages. The WorkCentre 3220 includes Adobe® PostScript® 3™ compatibility.
- **Find your most-needed functions fast** on the user-friendly front panel with large, easy-to-read buttons and a two-line LCD display.
- **Set-up is a snap,** thanks to an installation video, and simplified network and driver installation.
- **No-hassle maintenance.** An all-in-one user-replaceable print cartridge keeps intervention to a minimum, and a robust monthly duty cycle of up to 30,000 pages (3210) and 50,000 pages (3220) ensures reliable operation day after day.

Outstanding overall value

The WorkCentre 3210/3220 delivers more for your money and helps small offices gain efficiency while keeping costs down.

- **Affordable price** lets you add superior office capabilities without breaking your budget.
- **Combines critical functions.** One device that does the work of four reduces operating costs and service calls.
- **High productivity right out of the box,** with built-in networking and everything you need to start using this multifunction printer within a few minutes of setup.
- **Choose long-lasting high-capacity print cartridges** to lower your cost per print and minimize printer intervention.
- **An array of security features** such as Secure Fax Receive, which holds a fax until an authorized user logs in to retrieve it, along with SNMPv3 and IPv6, ensure that private data stays secure.
- **Xerox quality, reliability and performance** are backed by Xerox Service and Support, a standard one-year warranty and the unmatched Xerox Total Satisfaction Guarantee.
- **Front panel USB port** offers convenient scanning to and printing from a USB memory drive.

Conserve resources and stay green.

- **Energy Star** qualified to save on power consumption.
- **Reduce paper use** with automatic two-sided printing on the WorkCentre 3220.
- **Adjustable power save mode** puts you in control of your multifunction printer's power bill.
- **Increase toner yield** by using Toner Saver mode on draft documents.
- **One set of consumables** saves money and storage space. No more purchasing supplies for separate print, fax and copy machines.
- **Save paper with digital workflows,** letting you distribute documents electronically instead of on paper.

WorkCentre® 3210 / 3220 Quick Facts

- Up to 24 ppm and 30 ppm
- 250-sheet paper capacity, expandable to 500 sheets
- 600 x 600 dpi (1200 x 1200 enhanced image quality)
- 360 MHz processor
- 128 MB memory (384 MB maximum)
- Color scanning



Print / Copy / Scan / Fax



Letter / Legal



ppm

WxDxH:

17.5 x 16.2 x 15.6 in.
445.2 x 410.5 x 395.3 mm
3210: 30.45 lbs./13.8 kg
3220: 30.73 lbs./13.9 kg





Small-office friendly

All the office-ready features you need, sized to fit your workspace.

- **Compact, quiet and lightweight.** The WorkCentre 3210/3220 fits perfectly in tight, busy spaces.
- **Color scanning** quickly converts paper into electronic documents on your network, ready to be saved to a network or desktop folder, inserted into an application, sent to an email inbox (WorkCentre 3220) or stored on a USB memory drive.
- **Included scan software** provides helpful tools for editing and document manipulation, and for organizing and distributing your scanned files.
- **Edit and organize** scanned files with Optical Character Recognition scanning tools.
- **Advanced fax features** such as broadcast (multisend) faxing, fax forwarding and fax speed dials let you replace less cost-effective standalone fax machines with a single, well-integrated device.
- **PC/LAN Fax** allows paperless faxing right from your desktop (Windows only).
- **Manage from your desktop** using CentreWare® Internet Services, which lets you configure, update, view status and receive event alerts remotely.
- **Expand paper capacity** as your requirements expand. An optional 250-sheet paper tray gives you 500-sheet total capacity to reduce paper-changing trips.
- **Work team-ready**, this multifunction printer supports a diverse office environment with Microsoft® Windows®, Linux and Apple® Macintosh® systems.

- 1 Automatic Document Feeder holds 50 sheets.
- 2 Automatic two-sided printing on the WorkCentre 3220 saves paper and money.
- 3 Single-sheet multipurpose tray can handle envelopes, labels, postcards and transparencies.
- 4 250-sheet tray provides plenty of paper capacity for workgroup printing, copying and faxing.
- 5 Optional 250-sheet tray brings total capacity to 500 sheets.
- 6 USB memory port lets you save to, or print directly from, a USB drive — no computer needed.
- 7 Paper level indicator shows the sheets remaining in the tray.
- 8 Find frequently used fax numbers and email addresses in address book. You can also print an address list.
- 9 Four-way directional pad eases menu navigation.
- 10 Copy both sides of an ID card to a single side of paper with ID Card Copy feature.



WorkCentre® 3210 / 3220



		WorkCentre 3210	WorkCentre 3220
Speed		Up to 24 ppm (Letter/A4)	
Duty Cycle		Up to 30,000 pages / month	
Paper Handling Paper input	Standard	Automatic Document Feeder: 50 sheets; Custom Sizes: 5.6 x 5.8 in. to 8.5 x 14 in. / 142 x 148 mm to 216 x 356 mm Multipurpose Tray: 1 sheet; Sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm Main Tray 1: 250 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm Tray 2: 250 sheets; Custom sizes: 3 x 5 in. to 8.5 x 14 in. / 76 x 127 mm to 216 x 356 mm	
	Optional		
Automatic two-sided printing		NA	Standard
Paper output		150 sheets	
Print First-page-out-time		As fast as 9.5 seconds	As fast as 8.5 seconds
Print resolution		600 x 600 dpi (1200 x 1200 enhanced image quality)	
Processor		360 MHz	
Memory (std / max)		128 MB / 384 MB	
Connectivity		10/100 Base-TX Ethernet, USB 2.0	
Page description languages	PCL® 6 and PCL®5e emulations (host-based for Mac and Linux)		PCL® 6 and PCL®5e emulations, PDF 1.4, PostScript® 3™ compatibility
Print features	Custom-size pages, Watermarks, Poster printing, N-Up, Fit to Page, Scaling, Overlays, Reduce/Enlarge, Toner Saver, Print from USB memory drive, Booklet printing		
Copy First-page-out-time		As fast as 10 seconds	
Copy resolution		Up to 600 x 600 dpi (1200 x 1200 interpolated)	
Copy features		Reduce/Enlarge (25 – 400 %), Auto background suppression, 3 level darkness control, Collation (ADF only), ID Card Copy, N-Up (2-up, 4-up), Clone (platen only), Poster Copying (platen only)	
		NA	Two-sided (1:2 duplex copy), Manual 2:2 copying (no collation)
Fax		Embedded fax (33.6 Kbps with MH/MR/MMR/JBIG/JPEG compression)	
Fax features	Secure fax receive, PC/LAN Fax (send only)*, Fax forward to fax, Junk fax barrier, Searchable address book, Auto reduction, Battery backup, Distinctive ring, Broadcast (multisend) fax, Up to 200 group dial/broadcast locations, 200 speed dial locations, Delayed fax, Memory receive, Color fax send, Fax reports, Up to 300 x 300 dpi, 4 MB (225 pages)		
	NA	Fax forward to email, Two-sided fax receive	
Scan Scan destinations		Scan to application, Network Scan to PC, Scan to USB memory drive	
			Scan to application, Network Scan to PC, Scan to USB memory drive, Scan to email
Scan features	Scan to PC Desktop® SE Personal Edition; PDF; JPEG; TIFF; Multi-page TIFF; BMP; Color Scanning; USB, TWAIN, WIA drivers, Up to 4800 x 4800 enhanced dpi		
Security		IP Filtering, SNMPv3, Port Control, IPv6, Secure IPP, Scan-to-email with user authentication, Secure fax receive	
Warranty	One-year return to depot, Xerox Total Satisfaction Guarantee		

*Windows only

Device Management

CentreWare® Internet Services, CentreWare Web, WebJet Admin Interface

Print Drivers

Windows® 2000/XP (32/64 bit)/Vista/2003 Server/2008 Server, Mac OS® X version 10.3 and above; Various Linux® OS (via USB interface only) including Red Hat® 8-9, Fedora™ Core 1-4, Mandrake® 9.2-10.1, SUSE® 8.2-9.2, Mandriva 2005/2006/2007 (32/64 bit), Ubuntu 6.06-7.04, Debian 3.1-4.0, UNIX AT&T system V (4.2) BSD4.3, HP-UX (Rel 9x & 10x), SCO 5.x, SUN OS 5.5, Sparc or Solaris 2.5; Xerox Global Print Driver™, Xerox Mobile Express Driver™ (WorkCentre 3220)

Media Handling

Main Tray 1 and optional Tray 2: 16 – 28 lb. / 60 – 105 gsm; Multipurpose Tray: 16 – 43 lb. bond / 60 – 163 gsm; ADF: 16 – 28 lb. / 60 – 105 gsm; Plain paper, envelopes, labels, card stock, transparencies

Operating Environment

Operating: 50° to 90° F / 10° to 32° C; Storage: 14° to 104° F / -20° to 40° C; Relative humidity: 20 to 80%; Sound pressure levels: Printing: **3210:** 49 dB(A), **3220:** 50 dB(A); Standby: 26 dB(A); Warm-up time (from Power Save): Less than 2 seconds; Warm-up time (from power on): Less than 54 seconds

Electrical

Power: 110–127 VAC, 50/60 Hz or 220–240 VAC, 50/60 Hz; Power consumption: Standby: 60 W; Printing: 450 W; Power save: 12 W; ENERGY STAR® qualified

Dimensions (WxDxH)

17.5 x 16.2 x 15.6 in. / 445.2 x 410.5 x 395.3 mm; Weight: **3210:** 30.45 lbs / 13.8 kg, **3220:** 30.73 lbs / 13.9 kg; Package Dimensions (WxDxH): 23 x 21.7 x 20.7 in. / 584 x 551 x 526 mm; Weight: 39.24 lbs / 17.8 kg

Certifications

Listed UL 60950-1/CSA 609501-1-03, CE Mark applicable to Directives 2006/95/EC, 2004/108/EC, and 99/5/EC, FCC Part 15 Class B, FCC Part 68

What Comes In The Box

- WorkCentre 3210/3220
- Print Cartridge (2,000 pages)*
- Software (Scan to PC Desktop SE Personal Edition with Single license for support for OmniPage and PaperPort)
- Documentation CD (with User Manual, Quick Installation Guide and Warranty Statement)
- Fax cord, power cord, USB cable



Supplies

Standard-capacity print cartridge:¹

2,000 pages

106R01485

High-capacity print cartridge:¹

4,100 pages

106R01486

¹ Average standard pages. Declared Yield in accordance with ISO/IEC 19752.

Yield will vary based on image, area coverage and print mode.

Options

256 MB Memory

098N02189

Additional Paper Tray

098N02204

Wireless Network Adapter

097S03740

– N. America Power Converter

097S03741

– European Power Converter

097S03742

– UK Power Converter

097S03743

Supplies Recycling Program

Consumables for the WorkCentre 3210/3220 are part of the Xerox Green World Alliance Supplies Recycling Program. For more information, please visit the Green World Alliance website at www.xerox.com/gwa

For more information, call **1-877-362-6567** or visit us at www.xerox.com/office