

SHERPA Motion Letter Size

Article number	553937	Sales unit quantity	1 Set
Colour	Graphite	Sales unit EAN	616528501686
Base EAN	616528501686	Packing weight (gross)	3304.3 G
		Country of origin	DE



Product description

- Easy-rotating display panel system with 10 SHERPA® display panels in A4 format
- The galvanised ball allows rotation by 360° and adjustment of the reading angle from 25° to 70°
- Polypropylene display panels with coloured profile frame and low-reflection film suitable for scanners
- Incl. tabs with blank insert sheets for labelling the display panels
- Practical pivot mechanism for simple replacement of the displays
- Ideal for information in offices or representative environments in hotel and hospitality sectors
- 5-year warranty

Product features

Filling quantity / Filling quantity for	10 Display panel(s)
Format / Format for	Letter Size
Orientation Format	Portrait
Brand	DURABLE
Set includes display panels	Yes
Rotate / Swivel amounts	360°
Opening for documents	Top

SHERPA Motion Letter Size

Tabs with blank labels included	Yes
Non-slip / Stable	Non-slip / stable
Warranty	5 years
Product features relating to documents	Can be scanned, anti-glare
Base / mount type	Table stand