

**Fiber Optic Cable - Multimode Duplex 50/125 - LSZH - LC/LC - 5 m**

*StarTech ID: 50FIBLCLC5*



The 50FIBLCLC5 5m LSZH LC to LC Fiber Cable features 50/125 micron fiber for high-speed, high bandwidth data transmissions over Gigabit Ethernet and Fiber Channel networks, with support for duplex multimode applications.

This LC-LC patch cable is housed in a LSZH (Low-Smoke, Zero-Halogen) flame retardant jacket, to ensure minimal smoke, toxicity and corrosion when exposed to high sources of heat, in the event of a fire. Making it ideal for use in industrial settings, central offices and schools, as well as residential settings where building codes are a consideration.

Each Duplex 50/125 (OM2) Multimode Fiber Patch Cable is individually tested and certified to be within acceptable optical insertion loss limits for guaranteed compatibility and 100% reliability and is backed by our lifetime warranty.

**Anwendungen**

- Ideal solution for data applications requiring high speed data transmission
- Broadband systems
- Telecommunication / Data communication
- Used by long distance networks with mission critical data

## Merkmale

- Immune to electrical interference
- OM2 (50/125) 500MHz multimode fiber
- LSZH (Low-Smoke, Zero-Halogen) cable jacket
- Attenuation loss meets or exceeds industry standards

## Technische Spezifikationen

Warranty	Lifetime
Fiber Size	50/125
Fire Rating	LSZH Rated (Low Smoke Zero Halogen)
Fiber Classification	OM2
Fiber Type	Multi Mode
Connector A	1 - Fiber Optic LC Duplex Male
Connector B	1 - Fiber Optic LC Duplex Male
Cable Length	5 m [16.4 ft]
Color	Orange
Product Length	5 m [16.4 ft]
Shipping (Package) Weight	0.1 kg [0.1 lb]
Included in Package	1 - 5m Multimode 50/125 Duplex Fiber Patch Cable LC – LC

## Zertifikate Berichte und Kompatibilität

