

Vario Display System pro 10 Letter Size

Article number	551500	Sales unit quantity	1 Set
Colour	Assorted colours	Sales unit EAN	616528501846
Base EAN	616528501846	Packing weight (gross)	2431.35 G
		Country of origin	DE



Product description

- Multi-purpose display panel system made of powder-coated steel sheet
- For wall or table application, can be used in portrait or landscape format through 90° rotation
- L-shaped table stand for extra stability, simple mounting for wall application
- With 10 SHERPA® display panels in A4 format, 2 units each in black, red, yellow, green, dark blue
- Polypropylene display panels with coloured profile frame and low-reflection film suitable for scanners
- Incl. tabs with blank insert sheets for labelling the display panels
- Practical pivot mechanism for simple replacement of the displays
- 5-year warranty

Product features

Filling quantity / Filling quantity for	10 Display panel(s)
Format / Format for	Letter Size
Orientation Format	Portrait / landscape
Brand	DURABLE
Set includes display panels	Yes
Rotate / Swivel amounts	90°
Adjustable reading angle	No

Vario Display System pro 10 Letter Size

Opening for documents	Top
Tabs with blank labels included	Yes
Non-slip / Stable	Non-slip / stable
Warranty	5 years
Product features relating to documents	Can be scanned, anti-glare
Base / mount type	Table stand