

6 ft Coax High Resolution Monitor VGA Video Cable - HD15 to HD15 M/M

StarTech ID: MXT101MMHQ



The MXT101MMHQ High Resolution VGA Cable (6ft) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Applications

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)

Features

- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief

Technical Specifications

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Type	PVC - Polyvinyl Chloride
Cable Shield Type	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)
Number of Ferrites	1
Regulatory Approvals	UL2919
Connector A	1 - VGA (15 pin; High Density D-Sub) Male
Connector B	1 - VGA (15 pin; High Density D-Sub) Male
Impedance	75 Ohm
Product Length	1.8 m [6 ft]
Color	Black
Wire Gauge	28 AWG
Max Connector Dimension	34 mm [1.3 in]
Cable Length	1.8 m [6 ft]
Cable OD	9 mm [0.4 in]
Product Weight	280 g [9.9 oz]
Operating Temperature	0 to 60 °C
Storage Temperature	-20 to 80 °C
Humidity	0 - 80 %RH
Shipping (Package) Weight	0.3 kg [0.6 lb]
Included in Package	2 - Nuts
Included in Package	1 - 6 ft Coax High Resolution Monitor VGA Cable - HD15 M/M

Certifications, Reports and Compatibility

