



# SPECIFICATION SHEET

## Heavy Duty Bathroom Cleaner

# Professional Lysol® Heavy Duty Bathroom Cleaner – 1 gal.

Versatile, concentrated solution that delivers powerful restroom cleaning and kills 99.9% of viruses and bacteria.\* Penetrates tough soils and soap scum to help deliver a confident clean.



### Product Information

Product	Units/Case	Unit Size	Reckitt Item #
Professional Lysol® Heavy Duty Bathroom Cleaner	4	1 gal.	36241-94201

### Shipping Specifications

Reckitt Item #	36241-94201
Package Size	1 gal.
Case Pack	4
Pallet Cases	36
Tie/High	12/3
Case Weight	36.75
Case Cube	1.12
Case L x W x H	12.50 x 12.50 x 12.38
Item D x W x H	5.81 x 5.81 x 11.25
Item Cube	0.220
Item Weight	8.70
Item UPC	036241942014
SCS Case GTIN	10036241942011

### Technical Specifications

Technical Data	Professional Lysol® Heavy Duty Bathroom Cleaner
Color/Form	Blue, Green / Liquid
Fragrance	Citrus Floral
Active Ingredient	Alkyl (50% C <sub>14</sub> , 40% C <sub>14-2</sub> , 10% C <sub>16</sub> ) dimethyl benzyl ammonium chloride
Other Ingredients	96.56%
pH	12.6 to 13.1
EPA Registration #	675-54

USE AREAS	SURFACE TYPES <sup>2</sup>
<ul style="list-style-type: none"> <li>- Toilets</li> <li>- Urinals</li> <li>- Sinks</li> <li>- Faucets</li> <li>- Dispenser Covers</li> <li>- Baby Changing Tables<sup>1</sup></li> <li>- Waste Receptacles</li> <li>- Showers</li> </ul>	<ul style="list-style-type: none"> <li>- Bathtubs</li> <li>- Door Handles</li> <li>- Handrails</li> <li>- Stall Partitions</li> <li>- Stall Locks</li> <li>- Walls</li> <li>- Floors</li> <li>- Hard, non-porous surfaces</li> </ul>
	<ul style="list-style-type: none"> <li>- Acrylic</li> <li>- Plastic</li> <li>- Chrome</li> <li>- Glazed Ceramic</li> <li>- Glazed Porcelain</li> <li>- Stainless Steel</li> <li>- Formica</li> <li>- Concrete</li> </ul>
	<ul style="list-style-type: none"> <li>- Quartz</li> <li>- Laminated Wood</li> <li>- Aluminum</li> <li>- Fiberglass</li> <li>- Polypropylene</li> </ul>

\*When used as directed

<sup>1</sup>Rinse baby changing table with potable water after use.

<sup>2</sup>Do not use on polished marble, rubber flooring, copper, bronze, brass, rubber, bare wood surfaces, and black/dark natural stone (unfinished/unsealed).

For other surfaces, test on a small hidden area before use.

# GERMICIDAL EFFICACY

10 Minute Disinfection - Bacteria	ATCC No.
Acinetobacter baumannii [MDR] (Multi-Drug Resistant)	(19606)
Acinetobacter calcoaceticus	(17902)
Bordetella pertussis	(12743)
Burkholderia cepacia	(25416)
Corynebacterium ammoniagenes	(6872)
Corynebacterium diphtheriae	(11913)
Enterobacter aerogenes [MDR] (Multi-Drug Resistant)	(29751)
Enterococcus faecalis	(828)
Enterococcus faecium [MDR] (Multi-Drug Resistant)	(51559)
Escherichia coli ESBL (Extended-Spectrum beta-lactamase)	(BAA-196)
Escherichia coli O157:H7	(43888)
Haemophilus influenzae	(33930)
Klebsiella pneumoniae	(9997)
Klebsiella pneumoniae NDM-1 (New Delhi metallo-beta-lactamase 1 positive)	(CDC1000527)
Legionella pneumophila	(33153)
Listeria monocytogenes	(19117)
Neisseria elongate	(25295)
Proteus mirabilis	(25933)
Proteus vulgaris	(9920)
Pseudomonas aeruginosa	(15442)
Salmonella (choleraesuis) enterica	(10708)
Salmonella enterica serovar Paratyphi B	(8759)
Salmonella enterica serovar Paratyphi B (formely schottmuelleri)	(10719)
Salmonella typhi	(6539)
Serratia marcescens	(8195)
Shigella dysenteriae	(11835)
Staphylococcus aureus	(6538)
Staphylococcus aureus [MRSA] (Methicillin Resistant)	(33592)
Staphylococcus epidermidis	(12228)
Streptococcus pneumoniae [PRSP]	(700677)
Streptococcus pyogenes	(12384)
Streptococcus salivarius	(7073)

5 Minute Disinfection - Viruses	ATCC No.
Adenovirus Type 2	(VR-846)
Cytomegalovirus	(VR-538)
Hepatitis B Virus (HBV)	
Hepatitis C Virus (HCV)	
Herpes Simplex Virus Type 1	(VR-733)
Herpes Simplex Virus Type 2	(VR-734)
Human Coronavirus	(VR-740)
Human Immunodeficiency Virus Type 1	
Influenza A Virus [Hong Kong]	(VR-544)
2009-H1N1 Influenza A Virus (Novel H1N1, Strain A/Mexico/4108/2009)	(CDC 2009712192)
Pseudorabies Virus	(VR-135)
Rabies Virus	(VR-139)
Respiratory Syncytial Virus [RSV]	(VR-26)
Rotavirus WA	(VR-2018)
SARS-Associated Coronavirus	(CDC 200300592)
10 Minute Disinfection - Fungi	ATCC No.
Aspergillus niger	(6275)
Candida albicans	(10231)
Trichophyton mentagrophytes	(9533)

# DIRECTIONS FOR USE

## Professional Lysol® Heavy Duty Bathroom Cleaner

This product is a concentrate. Always dilute in accordance with label instructions.

Prepare a fresh solution daily and change solution frequently if heavily soiled or diluted. Proper dilution provides maximum cleaning benefits and product economy.

DILUTION CHART		
To prepare proper dilutions, add this product full strength to water as below.		
DILUTION RATIO	This product	Water
1:32	1 fl. oz.	1 Quart (32 fl. oz.)
	4 fl. oz.	1 Gallon (128 fl. oz.)
1:16	2 fl. oz.	1 Quart (32 fl. oz.)
	8 fl. oz.	1 Gallon (128 fl. oz.)
1:8** , ^^	4 fl. oz.	1 Quart (32 fl. oz.)
	16 fl. oz.	1 Gallon (128 fl. oz.)
1:4	8 fl. oz.	1 Quart (32 fl. oz.)
	32 fl. oz.	1 Gallon (128 fl. oz.)

\*\* For Pseudomonacidal activity in Hospitals and other Health Care Facilities, dilute 1:8.

^^ For Burkholderia cepacia, Rotavirus, Aspergillus niger, and Trichophyton mentagrophytes, dilute 1:8

**For General Cleaning:** Pre-clean surfaces.

**For General Disinfection:** Pre-clean surfaces. Remove heavy soils and gross filth prior to disinfection, as per General Cleaning instructions. Dilute in 1:32 in water (1/2 cup per gallon), apply with cloth or sponge and thoroughly wet surface for 10 minutes, then remove excess. ^^For Burkholderia cepacia, Rotavirus, Aspergillus niger, and Trichophyton mentagrophytes, dilute at 1:8.

**For Cleaning and Disinfecting Toilet Bowls:** Pre-clean surfaces. Prior to disinfection, remove all heavy soil and flush toilet. Add 4 fl. oz. of this product full strength into the bowl water (1:25 dilution). Thoroughly brush all bowl surfaces and under the rim. Let stand 10 minutes and then flush.

**For additional product information and Safety Data Sheet,  
please visit [www.rbnainfo.com](http://www.rbnainfo.com)**

