Product data sheet

Specifications





APC Smart-UPS 5000VA 208V Rackmount/Tower

SUA5000RMT5U

Overview	
Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually Ships within 3 Weeks
Main	
Main Input Voltage	208 V
Main Output Voltage	208 V
Kw Rating	4000 W
Rated power in VA	5000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA L6-30P
output connection type	2 NEMA L6-20R 2 NEMA L6-30R
Number of rack unit	5U
Cable length	8 ft (2.4 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Rack Mounting support rails Smart UPS signalling RS-232 cable User Manual Web/SNMP Management Card
Range of Product	Smart-UPS

Batteries & Runtime

Run Time	View Runtime Graph □
Efficiency	View Efficiency Graph □
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	2
Battery life	35 year(s)
Replacement battery	RBC55 🗗

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

Battery Charge Power (Watts) 542 W rated

General

Number of power module filled slots	0
Number of power module free slots	0
Redundant	No

Physical

color	Black
Height	8.7 in (22.2 cm)
Width	19.02 in (48.3 cm)
Depth	26.0 in (66 cm)
Net Weight	215.46 lb(US) (97.73 kg)
mounting location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	No

Input

Efficiency at full load	131268 V adjustable 141255 V
Input Frequency	50/60 Hz +/- 5 Hz manual switch

Output

Harmonic distortion	Less than 5 % at full load
Maximum configurable power in VA	5000 VA
Max Configurable Power (Watts)	4000 W
Transfer Time	2ms typical : 4ms maximum
Тороlоду	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	4753 Hz for 50 Hz nominal sync to mains 5763 Hz for 60 Hz nominal sync to mains

Conformance

Product Certifications	CSA
Equipment protection policy	Lifetime : \$150000

Environmental

Acoustic level	53 dBA
Online Thermal Dissipation	344 Btu/h
Operating altitude	010000 ft
Ambient Air Temperature for Operation	32.000000000113.000000000 °F (045 °C)

Ambient Air Temperature for Storage	23.00000000131.000000000 °F (-555 °C)
Storage altitude	050000 ft (0.00000000015240.000000000 m)
Relative Humidity	095 %
Storage Relative Humidity	095 %

Communications & Management

Control panel	LED status display with load and battery bar-graphs and On Line : On Battery : Replace Battery : and Overload Indicators
Emergency Power Off (EPO)	Optional
Free slots	0
Pre-Installed SmartSlot™ Cards	Network management card
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	480 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304255338
Returnability	No
Country of origin	IN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	25.000000000 in (63.5 cm)
Package 1 Width	30.000000000 in (76.2 cm)
Package 1 Length	24.02 in (61 cm)
Package 1 Weight	235.50 lb(US) (106.82 kg)

Contractual warranty

Warranty

2 years repair or replace

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Energy Efficient Take-back Transparency RoHS/REACh

Resource performance

Energy Efficient Product

Take-Back Program Available

Well-being performance

Mercury Free

Rohs Exemption Information

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Yes