19-Inch 5-WIRE Resistive Touch Monitor














P19BH-AB-459G

GVision's P19BH is a 19" industrial grade resistive touch monitor designed for use in the professional industry. It's the perfect 5-wire resistive touch screen solution for harsh enviornment.

DIMENSIONS





FEATURES

- 19-Inch Screen Size
- 1280 x 1024 Resolution
- 5-Wire Resistive Touch Panel
- Supporting Inputs: DVI-D / VGA / USB / RS232 / Audio
- 350 nits High Brightness
- LED-Diriect Backlight Unit
- Integrated Stereo Speakers
- Designed for 24/7/365 Operation
- TAA Compliant
- 3-Year Warranty

SPECIFICATIONS

or cell learnois	
MODEL	P19BH-AB-459G
Screen Size	19 In
Resolution	1280 x 1024
Backlight	LED Direct Backlight
Aspect Ratio	5:4
Viewing Angle	170° / 160°
Response Time	5ms
Brightness	350cd/m²
Contrast Ratio	1000 : 1
Display Area	376.4 (H) x 301.1 (V)
INTERFACE	
DVI In	1
VGA In	1
Audio	1
USB Type-A / RS232	1 / 1
AUDIO	
Speaker	2 (1W Per Channel)
TOUCH	
Туре	Resistive
Panel	5-Wire Resistive
Interface	RS-232 or USB Type-A
POWER	
Input Voltage	DC12V / 5A (100~240V,50~60Hz)
Consumption	TBD
Saving Mode	< 0.5W
TEMPERATURE	
Operating	32° F ~ 104° F (0° C ~ 40° C)
Storage	-4° F ~ 140° F (-20° C ~ 60° C)
Humidity	10% ~ 80%
DIMENSIONS (WXHXD)	
Inch (in)	17.2 x 16.4 x 7
Millimeter (mm)	438 x 417.5 x 180
WEIGHT	
Net Weight	17.6 lbs (8 kg)
COMPLIANT	
Certification	FCC / UL / cUL
VESA™	
Mount Size (mm)	100 x 100
	Specifications subject to change without any notice