

Specifications

Eaton TPC2105-1-119



Eaton Basic rack PDU, 1U, L6-30P input, 4.99 kW max, 208-240V, 24A, 15 ft cord, Single-phase, TAA compliant, Outlets: (16) C13

General specifications

PRODUCT NAME	Eaton basic PDU
CATALOG NUMBER	TPC2105-1-119
UPC	786685358185
PRODUCT LENGTH/DEPTH	19 in
PRODUCT HEIGHT	1.7 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.0001 lb
WARRANTY	3 year
COMPLIANCES	Contact Manufacturer TAA Compliant
CERTIFICATIONS	UL Listed

Product specifications

FORM FACTOR	1U
OUTLET CONTROL	No
PHASE	Single-phase
WATTAGE	4.99 kW max
AMPERAGE RATING	24A
INPUT VOLTAGE	208-240V
INPUT CONNECTION	L6-30P
OUTLETS	(16) C13
CORD LENGTH	15 ft
FREQUENCY RATING	50-60 Hz
OPERATING TEMPERATURE	0° to 60°C (32° to 140°F)

Resources

	Eaton RoHS declaration of conformity: ePDU G3
CERTIFICATION REPORTS	Eaton RoHS Declaration of Conformity: ePDU G3
DRAWINGS	Eaton PDU TPC2105-1-119 technical drawing
INSTALLATION INSTRUCTIONS	Eaton ePDU G3 troubleshooting guide
MANUALS AND USER GUIDES	Eaton ePDU G3 1U and 2U installation addendum Eaton ePDU G3 installation and connectivity quick start Eaton ePDU G3 operations manual Eaton ePDU G3 replace and configure eNMC module
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - TPC2105-1-119

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

