

Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

DVI over Cat5/6 Passive Extender, Remote Receiver for Video, DVI-D Single Link, Up to 100 ft. (30 m), TAA

MODEL NUMBER: B140-1P0



Transmit a DVI-D Single-Link signal up to 100 ft. away using a single Cat5e/6 patch cable

Description

The B140-1P0 is a receiver unit that is used with the B140-002 and B140-004 extender/splitter transmitter units, and it transmits a DVI-D Single-Link signal up to 100-ft. (30.5 m) away using a single Cat5e/6 patch cable. To achieve maximum distance and resolution, use 24AWG Solid Wire Cat5e/6 cable (Tripp Lite's N202-Series). The B140-1P0 is compatible with all operating systems, and is plug and play, with no external power, software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Installation is simple. Connect a B140-002 or B140-004 transmitter (not included) to a DVI source using a Tripp Lite P561-Series DVI cable (not included). Connect the B140-1P0's built-in DVI connector to a display. Finally, the receiver unit is connected to an RJ45 port on the transmitter unit using a single Cat5e/6 cable. A 1920 x 1080 @ 60Hz signal can be extended up to 50-ft. (15.24 m) from the source, or a 1024 x 768 @ 60Hz signal up to 100-ft. (30.5 m)

Features

- Transmit a DVI-D Single-Link signal up to 100-ft. (30.5 m) away using a single Cat5e/6 patch cable
- For use with B140-002 or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 50-ft. (15.24 m), or a 1024 x 768 @ 60Hz signal up to 100-ft. (30.5 m)
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- HDCP compatible

Highlights

- For use with B140-002 or B140-004 extender/splitter transmitter units
- Supports DVI-D Single-Link video resolutions up to 1920 x 1080 @ 60Hz
- Extends a 1920 x 1080 @ 60Hz signal up to 50-ft. (15.24 m), or a 1024 x 768 @ 60Hz signal up to 100-ft. (30.5 m)
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Compatible with all operating systems
- Plug and play, no external power, software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- B140-1P0 DVI Over Cat5
 Passive Extender Remote Unit
- Owner's manual



- Compatible with all operating systems
- Plug and play; no external power, software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW		
UPC Code	037332156655	
Product Type	Receiver	
Technology	DVI; Cat5/5e; Cat6	
VIDEO		
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)	
Max 720P Range (ft)	100	
Max 1080P Range (ft)	50	
Max 1280 x 720 (720p) Range (ft)	50	
Max 1920 x 1080 (1080p) Range (ft)	50	
Receiver/Transceiver Video Output	DVI-D (Single Link)	
Receiver - Number of Video Outputs	1	
Signal Range (ft)	100ft @ 1024 x 768 XGA 50ft @ 1920 x 1080 UXGA	
Signal Range (m)	30.5m @ 1024 x 768 XGA 15.2m @ 1920 x 1080 UXGA	
Range Extension using other Tripp Lite product	175ft @ 1024 x 768 XGA 125ft @ 1920 x 1080 UXGA	
Recommended Cabling	N202-Series Cat6 Patch Cable	
Other Tripp Lite product used to extend range	B140-110	
3D Video Supported	Yes	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	Power (Green); Activity (Orange)	
PHYSICAL		
Color	Black	
Number of Displays	1	
Form Factor/Mounting Options	Pigtail	
Shipping Dimensions (hwd / cm)	5.08 x 16.00 x 18.29	
Shipping Dimensions (hwd / in.)	2.00 x 6.30 x 7.20	





Shipping Weight (kg)	0.27	
Shipping Weight (lbs.)	0.60	
Unit Dimensions (hwd / in.)	1.36 x 0.94 x 14.16	
Unit Packaging Type	Вох	
Unit Weight (kg)	0.06	
Unit Weight (lbs.)	0.14	
Housing	Plastic	
ENVIRONMENTAL		
Operating Temperature Range	32 to 104 °F (0 to 40 °C)	
Storage Temperature Range	5 to 122 °F (-15 to 50 °C)	
Relative Humidity	0% to 85%, Non-Condensing	
COMMUNICATIONS		
Max 1024 x 768 Range (ft)	100	
Max 480P Range (ft)	100	
Max 1440 x 900 Range (ft)	100	
Max 1080i Range (ft)	50	
Max 480i Range (ft)	100	
Max 640 x 480 Range (ft)	100	
Max 800 x 600 Range (ft)	100	
Max 1600 x 1200 Range (ft)	100	
EDID Compatible	Yes	
Consumer Electronics Control (CEC) Supported	Yes	
USB Extension Support	No	
CONNECTIONS		
Ports	1	
Side A - Connector 1	RJ45 (FEMALE)	
Side B - Connector 1	DVI-D SINGLE LINK (MALE)	
FEATURES & SPECIFICATIONS		
Driver Required	No	
Built-In Equalizer	No	
STANDARDS & COMPLIANCE		
Certifications	Tested to CE, FCC, RoHS, REACH	



Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234

WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies