

## HDMI over Dual Cat5/6 Extender Kit, In-Line Transmitter/Receiver for Video/Audio, Up to 150 ft. (45 m)

MODEL NUMBER: **B125-150**



Transmit a HDMI signal up to 150ft, 1080p @ 24Hz using two Cat6 patch cables.

### Description

Tripp Lite's HDMI Over Dual Cat5 Extender Kit is the perfect solution for those who need to extend a HDMI signal over a long distance over two Cat5/6 cables.

- When using 24Awg, Solid Wire Cat6 cable, a 1080p @ 24Hz (or 1920 x 1200) signal can be extended up to 150-ft. (45.72 m) from the source.
  - When using 24Awg, Solid Wire Cat6 cable, a 3D signal can be extended up to 125-ft. (38.1 m)
  - When using 24Awg, Solid Wire Cat5 cable, a 1080p @ 24Hz (or 1920 x 1200) signal can be extended up to 100-ft. (30.5 m) from the source.
  - When using 24Awg, Solid Wire Cat5 cable, a 3D signal can be extended up to 75-ft. (22.86 m)
- Simply run two Cat5/6 cables between the local transmitter and remote receiver units, and plug in standard Tripp Lite HDMI cables to the HDMI source and the display.
- The B125-150 comes with both local transmitter and remote receiver units. DTS-HD, Dolby True HD and 7.1 Channel Surround Sound audio are supported, and it is compliant with HDCP, EDID and DDC. 24-bit True Color (8-bits per channel) is supported.

### Features

- Extends a 1080p @ 24Hz (or 1920 x 1200) signal up to 150-ft. (45.72 m) using 24Awg, Solid Wire Cat6 cabling (Tripp Lite N202-Series)
- Extends a 1080p @ 24Hz (or 1920 x 1200) signal up to 100-ft. (30.5 m) using 24Awg, Solid Wire Cat5 cabling
- Extends a 3D signal up to 125-ft. (38.1 m) using 24Awg, Solid Wire Cat6 cabling, or up to 75-ft. (22.86 m) using 24Awg, Solid Wire Cat5 cabling
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC

### Highlights

- Extends a 1080p @ 24Hz (or 1920 x 1200) signal up to 150-ft. (45.72 m) using 24Awg, Solid Wire Cat6\* cabling (Tripp Lite N202-Series)
- Extends a 3D signal up to 125-ft. (38.1 m) using 24Awg, Solid Wire Cat6\* cabling (Tripp Lite N202-Series)
- Supports 24-bit True Color (8-bits per channel)
- Supports DTS-HD, Dolby True HD and 7.1 Channel Surround Sound Audio
- Supports HDCP, EDID and DDC

### Package Includes

- HDMI Extender Local Transmitter Unit
- HDMI Extender Remote Receiver Unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.4A; Output: 9V, 1.5A, 4.5-ft. (1.37 m))
- Owner's Manual



- Supports 24-bit True Color (8-bits per channel)
- Use Tripp Lite P568-Series HDMI cables to connect to HDMI source and monitor
- Supports Lip-Sync Pass Through, and CEC pass through
- Green LED on the remote unit will illuminate to indicate that power is being received
- The Red LED on the remote unit will illuminate only if a working signal is NOT being received. The unit is functioning properly when the Red LED is not illuminated

## Specifications

OVERVIEW	
UPC Code	037332143723
Product Type	Extender Kit
AC Adapter	Input: 100-240V, 50/60Hz, 0.4A; Output: 9V, 1.5A, 4.5 ft.
Technology	HDMI; Cat5/5e; Cat6
VIDEO	
Max Supported Video Resolution	1920x1080 (1080p @ 60Hz)
Max 720P Range (ft)	150
Max 1080P Range (ft)	150
Max 1280 x 720 (720p) Range (ft)	195
Max 1920 x 1080 (1080p) Range (ft)	115
Transmitter Video Input	HDMI
Transmitter - Number of Video Outputs	1
Receiver/Transceiver Video Output	HDMI
Receiver - Number of Video Outputs	1
Signal Range (ft)	230ft via Cat6 @ 480p 197ft via Cat6 @ 720p 115ft via Cat6 @ 1080p
Signal Range (m)	70m via Cat6 @ 480p 60m via Cat6 @ 720p 35m via Cat6 @ 1080p
Recommended Cabling	N202-Series Cat6 Patch Cable
Max Supported Color Depth	24-bit True Color
3D Video Supported	Yes
Chroma Sub Sampling	4:4:4
AUDIO	
Audio Input	HDMI
Audio Output	HDMI



Audio Specification	Pass-through audio
<b>POWER</b>	
Power Source	Receiver end only (Included)
Power Source Type	AC Adapter
AC Plug Type	NEMA 1-15P
External Power Supply Input Specs (V / Hz / A)	100-240V / 50-60Hz / 0.5A
External Power Supply Output Specs (V / A)	5V/2A
External Power Supply Cord Length (ft.)	4.5
External Power Supply Cord Length (m.)	1.38
External Power Supply DC Barrel Connector Specs	OD: 5.5 x 2.1 x 7.5mm, Positive Pin, Negative Sleeve
External Power Supply Certifications	FCC; PSE; TUV; UL; cUL
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	Power (Green), Signal (Red)
<b>PHYSICAL</b>	
Color	Black
Number of Displays	1
Form Factor/Mounting Options	Box
Receiver Unit Dimensions (hwd / in.)	2.45 x 1.85 x 0.85
Receiver Unit Weight (lbs.)	0.06
Shipping Dimensions (hwd / cm)	18.29 x 16.26 x 5.59
Shipping Dimensions (hwd / in.)	7.20 x 6.40 x 2.20
Shipping Weight (kg)	0.36
Shipping Weight (lbs.)	0.80
Transmitter Unit Dimensions (hwd / in.)	2.45 x 1.85 x 0.85
Transmitter Unit Weight (lbs.)	0.06
Unit Dimensions (hwd / cm)	Source Unit: 2.375"W x 1.75"D x 0.75"H
Unit Packaging Type	Box
Housing	Plastic
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 104 °F (0 to 40 °C)



Storage Temperature Range	5 to 122 °F (-15 to 50 °C)
Relative Humidity	0% to 85% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Max 1024 x 768 Range (ft)	150
Max 480P Range (ft)	150
Max 1440 x 900 Range (ft)	150
Max 1080i Range (ft)	150
Max 480i Range (ft)	150
Max 640 x 480 Range (ft)	150
Max 800 x 600 Range (ft)	150
Max 1600 x 1200 Range (ft)	150
EDID Compatible	Yes
Consumer Electronics Control (CEC) Supported	Yes
USB Extension Support	No
<b>CONNECTIONS</b>	
Ports	1
Side A - Connector 1	HDMI (FEMALE)
Side A - Connector 2	(2) RJ45 (FEMALE)
Side B - Connector 1	HDMI (FEMALE)
Side B - Connector 2	(2) RJ45 (FEMALE)
<b>FEATURES &amp; SPECIFICATIONS</b>	
HDCP Specification	1.4
Driver Required	No
Built-In Equalizer	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>