

## 5.5kW Single-Phase Metered PDU, 208/230V Outlets (16 C13 & 2 C19), L6-30P, 12 ft. (3.66 m) Cord, 2U Rack-Mount, TAA

MODEL NUMBER: PDUMH30HV



### Highlights

- Metered single phase 24A 208/230V 2U horizontal rackmount PDU
- Two built-in meters report output current in amps for each load bank
- Attached 12-ft. (3.66 m) cord with NEMA L6-30P input plug
- 18 total outlets (16 C13, 2 C19)
- Reversible housing, 2U 208/230V rackmount metered PDU
- TAA Compliant

### Package Includes

- 2U rack PDU
- Mounting brackets
- Plug retention plates
- User manual

### Features

- 30A single phase 208/230V Metered Power Distribution Unit / PDU (Agency derated to 24A continuous)
- Set of two lighted meters report PDU output current in amps for each 9 outlet load bank
- Attached NEMA L6-30P 30A 208/230V input plug and 12-ft. (3.66 m) cord
- 2U horizontal rackmount format installs in two rack spaces
- 18 output receptacles (16 C13, 2 C19)
- Outlets are arranged in two 9 outlet load banks, each with separate 20A breaker and current metering
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Cord retention brackets keep vital equipment plugs connected
- Grounding lug
- Compliant with the Federal Trade Agreements Act(TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
UPC Code	037332159021
PDU Type	Metered
INPUT	
PDU Input Voltage	208/230V
Recommended Electrical Service	Single-phase 30A 208/230V service



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Maximum Input Amps	24
Maximum Input Amps Details	Agency de-rated to 24A continuous
PDU Plug Type	NEMA L6-30P
Input Phase	Single-Phase
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
<b>OUTPUT</b>	
Output Capacity Details	5.5kW (230V), 5kW (208V) total capacity / 30A max (Agency de-rated to 24A), 20A max per breakered outlet bank; 16A max per C19 outlet; 12A max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(16) C13; (2) C19
Output Nominal Voltage	208/230V
Overload Protection	Two 20A breakers protect 9 outlets each
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Front Panel LCD Display	Set of 2 digital meters continuously report output current for breakered load banks 1 & 2 (Bank 1: upper row of 9 outlets / Bank 2: lower row of 9 outlets)
<b>PHYSICAL</b>	
Material of Construction	Metal
Form Factors Supported	2U rackmount; mounting accessories included
Minimum Required Rack Depth (cm)	40.64
Minimum Required Rack Depth (inches)	16
PDU Form Factor	Horizontal (2U)
Shipping Dimensions (hwd / cm)	19.81 x 42.42 x 50.29
Shipping Dimensions (hwd / in.)	7.80 x 16.70 x 19.80
Shipping Weight (kg)	7.17
Shipping Weight (lbs.)	15.80
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 12.5
Unit Dimensions (hwd / cm)	8.8 x 44.4 x 31.8
Unit Weight (lbs.)	13.7
Unit Weight (kg)	6.21
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	0C ~ 40C (32F ~ 104F)
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Relative Humidity	5-95% non-condensing
<b>FEATURES &amp; SPECIFICATIONS</b>	
TVSS Grounding	Grounding lug
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL62368-1 (USA, Canada), NOM (Mexico), Class A (Emissions), RoHS compliant, TAA Compliant
Certification Details	Series Number(s) AGPD7986
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>