

Lenovo recommends Windows Vista® Business.

LENOVO THINKPAD® T400 AND T500 NOTEBOOK

GREAT IDEAS THAT BREAK BARRIERS WITH CUTTING-EDGE TECHNOLOGY.



UNCOMPROMISED PERFORMANCE

- Combines the highest performing Intel® Core™2 Duo processor with Active Management Technology (iAMT), for enhanced notebook management and security



BEST WIRELESS SOLUTIONS

- Faster data transfer rates
- Bluetooth capability



CUTTING-EDGE TECHNOLOGIES

- Switchable graphics (integrated and discrete)
- Solid State Drives for improved performance and reliability
- High performing DDR3 memory
- LED-Backlight displays (Available on selected models of T400)
- DisplayPort - for the next generation VESA interface incorporating HD video (available on T500)



ENVIRONMENTALLY RESPONSIBLE

- Most energy-efficient ThinkPad
- An EPEAT Gold qualified notebook (LED Backlight systems) (Available on selected models of T400)
- Industry's first PC with a GREENGUARD Air Quality certification
- Energy efficient 25 watt processors
- New Power Management utility and enhanced BatteryStretch feature for lower power consumption and improved battery life



NEW NAMING CONVENTION: The latest ThinkPad T Series marks the introduction of a new naming convention. The new ThinkPad T400 (14.1") widescreen display and the ThinkPad T500 (15.4" widescreen display) will replace the ThinkPad T61.

lenovo

Lenovo recommends Windows Vista® Business.

THE NEW THINKPAD® T SERIES

ENGINEERED TO REACH NEW HEIGHTS IN CONNECTIVITY, PRODUCTIVITY, POWER MANAGEMENT, ENVIRONMENTAL RESPONSIBILITY AND COMFORT.

The ThinkPad T Series notebooks are designed to enhance productivity and change the way you work. To begin with, they feature 14.1" and 15.4" LED-backlight widescreen displays that help to lower power consumption and offer brighter colors. In addition, the notebooks come equipped with a range of technology that includes Solid State Drives (SSDs), an integrated camera, DDR3 memory modules, new DisplayPort technology and a wider Touchpad for improved ergonomics. ThinkVantage Client Security Solution with an Integrated Fingerprint Reader and SmartCard support are other innovative features that give these notebooks extra protection by securing data against potential intruders.

ThinkPad notebooks are also environmentally responsible and can meet EPEAT Gold qualification. Equally reassuring is the fact that T Series models enjoy worldwide, round-the-clock service and support and come with an industry-leading warranty - as well as optional services like ThinkPad Protection which provides repair and replacement services to further protect assets.



OUTSTANDING BATTERY LIFE

New Power Management feature enables extended battery life. The Enhanced BatteryStretch feature allows users to select the most efficient power management on demand.



SWITCHABLE GRAPHICS

Provision for an easy switch between Discrete and Integrated graphics processing unit which enables maximized battery life and performance.



COOL AND QUIET DESIGN

Best engineered fan technology for focused air flow which provides for cooler systems and balanced temperatures across the system. The new fan design guarantees superquiet computing.

THINKPAD® T400 / T500 SPECIFICATIONS

THINKPAD T SERIES

Processor (Speed, L2 Cache, FSB)

Intel® Core™2 Duo processor P8400
(2.26GHz, 3MB L2, 1066MHz FSB, 25 watt)
Intel® Core™2 Duo processor P8600
(2.4GHz, 3MB L2, 1066MHz FSB, 25 watt)
Intel® Core™2 Duo processor P9500
(2.53GHz, 3MB L2, 1066MHz FSB, 25 watt)
Intel® Core™2 Duo processor T9400
(2.53GHz, 6MB L2, 1066MHz FSB, 35 watt)
Intel® Core™2 Duo processor T9600
(2.8GHz, 6MB L2, 1066MHz FSB, 35 watt)

Preloaded Operating System

Genuine Windows Vista® Ultimate 32
Genuine Windows Vista® Business 32
Genuine Windows Vista® Business 64
Genuine Windows Vista® Home Premium 32
Genuine Windows Vista® Home Basic 32
Genuine Windows® XP Professional

Serial ATA Hard Drives

80, 160, 250, 320GB / 5400 rpm
160GB / 7200 rpm
200GB / 7200 rpm with Full Disk Encryption (FDE)
64GB Solid State Drive

Memory

Up to 4GB of PC2-8500 1066MHz DDR3

Optical Drive

DVD-ROM, CD-RW/DVD-ROM, DVD Burner, Blu-ray

Keyboard

Ergonomic keyboard with palm rest, ThinkPad UltraNav® multipointing system, including TrackPoint® pointing device with "Press-to-Select", Internet Scroll Bar, intuitive volume, ThinkVantage button and Windows key

Graphics

Integrated Intel® GMA 4500 MHD
ATI Switchable business graphics with 256MB

Available Integrated Communication

Gigabit Ethernet
Bluetooth 2.1

Supported WLAN cards:

Intel® Wireless WiFi Link 5100 1x2
Intel® Wireless WiFi Link 5300 2x3
ThinkPad 11b/g Wireless LAN Mini PCI Express Adapter III

Security

Standard: ThinkVantage Client Security with Password Manager, Integrated Trusted Platform Module (TPM v1.2), Bios disable of all ports
Optional: Integrated Fingerprint Reader, SmartCard Reader, Full Disk Encryption HDD, Softex OmniPass, Utimaco® SGE

Other features

Optional integrated camera, white ThinkLight®

ThinkPad Shock-Mounted Hard Drive

Standard

Limited warranty

1yr, 3yr system/ 4 yr system by special bid only/1yr battery

Included software (preloaded)¹²

Adobe Acrobat Reader; Microsoft® Office Ready 2007; Microsoft® Windows Live™ Toolbar & Search; Roxio Creator; Intervideo WinDVD (DVD models only); Intervideo WinDVD Creator (DVD models only); McAfee VirusScan® Plus with 30 days of virus definition updates; Creator Business Edition (combo models); Creator Business Edition + MYDVD (Rambo); PC-Doctor diagnostics; Sun JRE; ThinkPad Utilities (Power Manager and Presentation Director); ThinkVantage® Access Connections™; ThinkVantage Fingerprint Software; ThinkVantage Productivity Center; ThinkVantage Rescue and Recovery™; ThinkVantage System Update; ThinkVantage Client Security Solution

THINKPAD T400

Li-ion Battery Life (Windows Vista®)¹³

4-cell: starting at 4.3 hrs
6-cell: starting at 6.5 hrs
9-cell: starting at 9.8 hrs
9-cell + bay battery: starting at 13.0 hrs

Dimensions

335.3x238x27.6x31.9mm (4/6-cell battery)
13.2x9.4x1.1 - 1.3"

Weight

4-cell battery models starting at 2.13 kg/4.7 lbs

Display

WXGA (1280x800, 98dpi, 185+ nit)
WXGA+ (1440x900, 129dpi, 200+ nit)
WXGA+ W/LED Backlight (1680x1050, 129dpi, 200+ nit)

Ports and Slots

Ports: 3 USB, IEEE 1394a, VGA, Microphone/line-in, Headphone/line-out
Slots: Standard Express Card 34/54 mm and optional choice of either PC Card, or 7-1 Media Card Reader

THINKPAD T500

Li-ion Battery Life

6-cell: starting at 4.3 hrs
9-cell: starting at 6.4 hrs
9-cell + bay battery: starting at 8.5 hrs

Dimensions

357.5x255 x 29.7x 33.5mm (6-cell battery)
14.1x10.0x1.2 - 1.3"

Weight

6-cell battery models starting at 2.63 kg/5.8 lbs

Display

WXGA (1280x800, 98dpi, 185+ nit)
WSXGA+ resolution (1440x900, 129dpi, 200+ nit)
WXGA+ W/LED Backlight (1680x1050, 129dpi, 200+ nit)

Ports and Slots

Ports: 3 USB, IEEE 1394a, VGA, Microphone/line-in, Headphone/line-out, DisplayPort and optional DVI-D monitor cable
Slots: Standard Express Card 34/54 mm, 7-1 Media Card Reader and optional choice of either PC Card or SmartCard

THINKPAD® T SERIES GOES GREEN



The ThinkPad T400 and T500 can both meet EPEAT Gold qualification (LED Backlight Display systems). They consume 25% less power when compared to previous generation notebooks and also have Energy Star 4.0 and Climate Savers certifications.

What else makes the ThinkPad T Series so "green"?

- Industry's first PC with GREENGUARD Air Quality certification
- Less power consumption with LED-Backlight displays compared to a standard LCD display
- Increased power efficiency with BatteryStretch feature
- Less power consumption with Solid State Storage Drives compared to standard hard drives
- Greater use of recycled plastics
- Mercury free displays (LED Backlight displays)



Lenovo recommends Windows Vista® Business.

DESIGNED TO DO THE UNEXPECTED

MAKE AN AMAZING PC EVEN BETTER.

THINKPAD T400/T500 ACCESSORIES:



LENOVO 2GB PC3-8500 1066MHz DDR3 SODIMM MEMORY (43R1988)
Lowest-cost method to boost system performance. Recommended for Microsoft® Vista



THINKPAD ADVANCED MINI DOCK (39T4595)
Rear ports offers enhanced cable management and connectivity; Quick and easy access to peripherals



THINKPAD T/R 14W 9-CELL HIGH CAPACITY BATTERY (43R2499)
Carry battery spares, or replace system batteries when charge capacity diminishes with time



THINKPAD AND IDEAPAD™ 90W SLIM AC/DC COMBO ADAPTER (41N8488)
Allows you to power your notebook everywhere you go - in the office, at home, on the road, and in the air; optional dual charging cable also can simultaneously charge cell phones or PDA devices



800 938 838
lenovo.com/hk

lenovo

©2008 Lenovo. All rights reserved. All offers subject to availability. Lenovo reserves the right to alter product offerings and specifications at any time without notice. Lenovo is not responsible for photographic or typographic errors. For a copy of applicable product warranties, visit lenovo.com/hk/warranty. Lenovo makes no representation or warranty regarding third-party products or services. Lenovo may not offer the products, services or features discussed in this document in all countries. Information is subject to change without notice. Consult your local Lenovo representative for information on offerings available in your area. IBM, Lenovo logos and trademarks are used under license. Contact Lenovo for details. Certain IBM and ThinkCentre logo products are not manufactured, warranted or supported by IBM or Lenovo. Lenovo makes no representation or warranty regarding third-party products or services.

Lenovo, the Lenovo logo, Rescue and Recovery, Access Connections, TrackPoint, ThinkCentre and ThinkVantage are trademarks of Lenovo. Lenovo's marks may not be used in connection with any product or service that is not Lenovo's in any manner that is likely to cause confusion, or in any manner that disparages or discredits Lenovo. IBM, the IBM logo, Lotus, Lotus Notes and Lotus SmartSuite are trademarks of International Business Machines Corporation in the United States, other countries, or both and are used under license. Celeron, Celeron Inside, Centrino, Centrino Inside, Centrino Logo, Core Inside, Intel, Intel Logo, Intel Core, Intel Inside, Intel Inside Logo, Intel Viiv, Intel vPro, Itanium, Itanium Inside, Pentium, Pentium Inside, Viiv Inside, vPro Inside, Xeon and Xeon Inside are trademarks of Intel Corporation in the U.S. and other countries. Java, JRE, Sun and all Java-based trademarks are trademarks of Sun Microsystems, Inc. in the U.S., other countries, or both. Linux is a trademark of Linus Torvalds in the U.S., other countries, or both. Microsoft, Windows and Vista are registered trademarks of Microsoft Corporation in the U.S., other countries, or both. Other company, product and service names may be trademarks or service marks of others.

Footnotes: [1] **Weight:** Includes battery and optional travel bezel instead of standard optical drive in Ultrabay drive, if applicable. Weight may vary due to vendor components, manufacturing process and options. [2] **WWAN service providers:** Coverage not available in all areas. Service available via select service providers and is available in select metropolitan markets. Service agreement required. Special credit and tenure restrictions and additional charges may apply to international roaming. A network connection, third-party software, additional hardware, and/or subscription to a third-party service may be required for certain solutions/applications. Additional restrictions apply. Service is subject to the applicable service agreement/terms from the respective service providers, the corresponding rate plan brochure and coverage maps. Offer subject to change. [3] **International warranty service:** is available for most models in any country in which this product is sold and serviced. Service delivery methods and parts availability vary by country, may be different from those in the country of purchase, and are subject to change without notice. Fees and restrictions may apply in some countries. [4] **Mobile processors:** Power management reduces processor speed when in battery mode. [5] **Operating system:** Level of support varies by operating system. Operating systems not preloaded on the system may not provide full feature functionality. Refer to lenovo.com/pc/support and enter your machine type and model number for more information. [6] **Hard disk drive:** GB=1,000,000,000 bytes. Accessible capacity is less; up to 4GB is service partition. [7] **Models with 4GB memory:** Total accessible memory will be less and will vary depending on the system configuration. Maximum capacity may require purchase of optional component. Subject to availability of new 4GB DIMMs. [8] **11a, 11b, and 11g wireless:** are based on IEEE 802.11a, 802.11b, and 802.11g respectively. The IEEE 802.11n specification has not been finalized and is currently in draft release. The Lenovo and ThinkPad 11a/b/g/n Wireless Lan Mini-PCI Express Adapters are based on the Draft Release, Version 1.0, of the IEEE 802.11n specification. An adapter with 11a/b, 11a/b/g, or 11a/b/g/n can communicate on any of its supported formats; the actual connection will be based on the access point to which it connects. [9] **The Bluetooth word mark and logos:** are owned by Bluetooth SIG, Inc. and any use of such marks by Lenovo is under license. [10] **Battery:** These model numbers achieved Battery Rundown Time of at least the time shown during testing. A description of the testing is available at lenovo.com/pc/www/thinkpad/batterylife. [11] **Limited warranty:** Support unrelated to a warranty issue may be subject to additional charges. [12] **Included software:** may differ from its retail version (if available) and may not include user manuals or all program functionality. [13] **Battery Life:** Battery life based on MobileMark 2007 Benchmark on Windows Vista 32 bit.

Visit lenovo.com/safecomputing periodically for the latest information on safe and effective computing.