

# VPC221

**22" (21.5" VIEWABLE)  
ALL-IN-ONE PC**

## Green, work horse.

The ViewSonic® VPC221 All-in-One PC is the perfect combination for saving energy, space and resource. This total green solution is powered by the Core i3 processor delivering all the performance needed for smart multitasking. Plus efficiency of the Core i3 processor combined with the low power LED panel saves up to 60% on energy costs over traditional PC's and provide fantastic TCO. The six high-speed USB 2.0 ports allow connection of multiple peripherals, and the advanced ergonomics provides the flexibility needed for working long hours with minimum strain. Whether surfing the web or connecting to the corporate network, the VPC221 has both LAN and Wireless capability. The VPC221 is your new smarter, greener PC solution.



- > Windows 7 Professional offers enhanced security and easy integration with your company network
- > Intel Core i3 CPU and NVIDIA® discrete graphics provide uncompromised performance
- > Work on productivity applications and watch full HD video in crisp detail on the huge 21.5" screen
- > Six high-speed USB 2.0 ports provide easy connections for peripherals
- > 4-in-1 card reader allows for easy file transfers
- > Stay networked through 802.11 b/g/n Wi-Fi or Ethernet LAN connectivity
- > Integrated 1.3 megapixel webcam and two 3-watt speakers allow productive video conferencing
- > Easy to mount to a wall for space savings



**ViewSonic®**  
See the difference® 

# VPC221 22" (21.5" VIEWABLE) ALL-IN-ONE PC



|                               |   |   |
|-------------------------------|---|---|
| <b>MODEL NUMBER</b>           | VPC221B-7PUS-M1   |   |
| <b>LCD</b>                    | Type  | 21.5" Color TFT Active Matrix LED   |
|                               | Resolution  | 1920x1080 Full High-Definition  |
|                               | Contrast Ratio  | 1000:1 static (typ)   |
|                               | Viewing Angles  | 170° horizontal, 160° vertical  |
|                               | Response Time   | 5ms   |
|                               | Light Source  | Long life, 30,000 hrs. (min)  |
|                               | Brightness  | 250 cd/m2 (typ)   |
| <b>CORE</b>                   | CPU Processor Type  | Intel® Core i3  |
|                               | CPU Processor Speed   | 3.08GHz Dual Core, FSB 667MHz   |
|                               | Chipset   | Intel® H55  |
| <b>VIDEO</b>                  | NVIDIA GeForce 310M graphics with 512MB VRAM  |   |
| <b>MEMORY</b>                 | 4GB DDR3 SDRAM 1066MHz (Upgradeable to 8GB)   |   |
| <b>SOFTWARE</b>               | Operating System  | Windows® 7 Professional   |
| <b>HARD DRIVE</b>             | Capacity  | 3.5", 500GB SATA 5400rpm  |
| <b>OPTICAL DRIVE</b>          | Super Multi Drive   | 12.7MM slim tray-in, DVD and CD R/W   |
| <b>COMMUNICATION</b>          | Ethernet LAN  | 10/100/1000 Gigabit Ethernet  |
|                               | Wireless LAN  | 802.11 b/g/n  |
| <b>WEBCAM</b>                 | 1.3 megapixel   |   |
| <b>INPUT/OUTPUT</b>           | USB 2.0 (x6)  |   |
|                               | RJ45 Gigabit Ethernet LAN   |   |
|                               | Microphone jack   |   |
|                               | Earphone jack   |   |
|                               | 4-in-1 card reader (SD, MMC, MS, MS Pro)  |   |
| <b>AUDIO OUTPUT</b>           | Speakers  | 3-watt (x2)   |
| <b>OTHER</b>                  | Wireless keyboard and mouse   |   |
| <b>POWER</b>                  | Voltage   | AC 100-240V (universal), +/-10% Wide Range  |
|                               | Power Cord  | 3-pin AC plug   |
| <b>OPERATING CONDITIONS</b>   | Temperature   | 32-104°F (0-40°C)   |
|                               | Humidity  | 15-90% (non-condensing)   |
|                               | Altitude  | 0-6,000 ft. (1800m), operational up to 10,000 ft. (3048 m) at reduced reliability and performance |
| <b>DIMENSIONS (W x H x D)</b> | Physical  | 20.8" x 18.3"-22.6" x 9.8" (528mm x 465-574mm x 250mm)  |
|                               | Physical Without Stand  | 20.8" x 15.2" x 2.4" (528mm x 385mm x 60mm)   |
|                               | Packaging   | 24.8" x 21.5" x 8.7" (630mm x 545mm x 220mm)  |
| <b>WEIGHT</b>                 | Net   | 20.6 lb. (10.7 kg)  |
|                               | Net Without Stand   | 16.52 lb. (7.5 kg)  |
|                               | Gross   | 30.73 lb. (13.0 kg)   |
| <b>ERGONOMICS</b>             | Height, tilt, swivel, pivot   |   |
| <b>WALL MOUNT</b>             | VESA 100mm x 100mm  |   |
| <b>REGULATIONS</b>            | FCC, RoHS   |   |
| <b>RECYCLE/DISPOSAL</b>       | Please dispose of in accordance with local, state or federal laws.                  |   |
| <b>PACKAGE CONTENTS</b>       | VPC221, power cord, keyboard, mouse, Quick Start Guide, Driver Disk with User Guide |   |
| <b>WARRANTY</b>               | 1-year limited warranty on parts, labor and backlight.                              |   |

- 1 – 21.5" LCD Screen
- 2 – Webcam
- 3 – Tilt/Swivel/Pivot Display
- 4 – Menu Controls
- 5 – RJ45 Port

- 6 – Audio Input
- 7 – Headphone
- 8 – Microphone
- 9 – 4 USB 2.0 Ports
- 10 – Power

- 11 – VESA mountable
- 12 – Height Adjust Stand
- 13 – DVD/CD RW
- 14 – 2 USB 2.0 Ports
- 15 – 4-in-1 Card Reader



ViewSonic Corporation's OMS & EMS have been registered to ISO 9001 & ISO 14001, respectively, by TUV NORD.

Sales: (888) 881-8781 • SalesInfo@ViewSonic.com • ViewSonic.com

Microsoft, Windows, and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries. Specifications subject to change without notice. Selection, offers and programs may vary by country; see your ViewSonic representative for complete details. Corporate names, trademarks stated herein are the property of their respective companies. Copyright © 2011 ViewSonic Corporation. All rights reserved. [15475-00B-02/11] VPC221

**ViewSonic®**  
See the difference®

**Smarter Greener Computing**  
For more product information, visit us on the web at [ViewSonic.com](http://ViewSonic.com)