

2U 19in Hinged Wall Mount Bracket for Patch Panels

StarTech ID: WALLMOUNTH2



The WALLMOUNTH2 2U 19in Hinged Wall Mounting Bracket for Patch Panels is 6in deep and sturdily designed to provide a dependable solution for mounting a patch panel, or other slim 19in networking equipment to a wall.

The patch panel wall mount features a hinged design for easy access to configuration buttons, ports and cables.

Backed by a StarTech.com 2-year warranty.

Applications

- Wall mount patch panels and other slim 19" rackmount equipment

Features

- Sturdy cold rolled steel construction
- 2U rack height
- Hinged side panel for easy equipment access
- 10 kg (22 lbs) weight capacity
- Wall mounting holes are 16" center to center for greater stability, and mounting to standard wall studs

Technical Specifications

Warranty	2 Years
Fan(s)	No
Frame Type	Open Frame
Front Door Type	Open
Rack Type	2-Post
U Height	2U
Wallmountable	Yes
Weight Capacity	10 kg [22.1 lb]
Color	Black
External Depth	152 mm [6 in]
External Height	89 mm [3.5 in]
External Width	483 mm [19 in]
Flat Pack	No
Shipping (Package) Weight	0.8 kg [1.8 lb]
Included in Package	1 - 2U Hinged 19" Wallmount Panel Bracket
Included in Package	4 - Cab Screws and Cage Nuts
Included in Package	1 - Allen Key

Certifications, Reports and Compatibility

