



DT-1000

STAINLESS STEEL KEYBOARD

The DT-1000 is a full-size desktop keyboard, featuring a stainless steel case and a sealed industrial silicone rubber keypad. Its 24 function keys and 10-key number pad allow for user versatility. The DT-1000 is designed to meet NEMA 4X specifications, making it resistant to dust, dirt, water and corrosive liquids. Features: 10-Key Numeric Pad 114-Key Functionality 24 Function Keys USB, PS/2 and AT Configurations Available

Product Code DT-1000

CERTIFICATIONS	NEMA 4X, UL60950, FCC Part 15 Class B
SHOCK	3x11 ms pulses of 50g on each of 3 axes
CABLE	LENGTH: 10 FEET (3 meters) DESIGN: PS/2, AT or Single-Cable USB
KEY SWITCH	MATERIAL: Industrial silicone rubber LIFE: 10 million cycles TRAVEL: 0.055 in. (1.4 mm) ACTUATION FORCE: 7.05 oz. +/- 1.06 oz. (200g +/- 20g) FEEDBACK: Tactile with mechanical snap
VIBRATION	POWER SPECTRAL DENSITY: 0.04g/Hz FREQUENCY RANGE: 20Hz - 2 kHz DURATION OF TEST PER AXIS: 3 hours
POWER	PS/2 or AT: 50mA@5V (from Keyboard port) USB: 50mA@5V (from CPU port)
COMPATABILITY	PS/2: All Windows Operating Systems USB: All Windows and Macintosh OS
TEMPERATURE RANGE	STORAGE: -40C to +90C (-40F to +194F) OPERATING: -40C to +70C (-40F to +158F)
WEIGHT	5.25 lbs +/- 0.10 lbs (2.38 kg +/- 0.05 kg)
WARRANTY	1 year limited warranty
HUMIDITY	100% Humidity Resistant
DIMENSIONS	16.25" x 7.88" x 1.80" (w-h-d) 412.8mm x 200.2mm x 45.7mm
MODEL NUMBERS	DT-1000-PS2: With PS/2 cable DT-1000-USB: With USB cable DT-1000-STD: With AT cable