

Product data sheet

Specifications



Power Cord, Locking C19 to 5-15P, 3.0m



AP8750

Product availability: Stock - Normally stocked in distribution facility

Overview

Presentation Free up space and secure power cords between rack-mount PDUs and attached IT equipment with this exclusive easy-to-use cord retention method. While these cords will fit into any standard IEC receptacle or power inlet; the "locking" feature is enabled only when used with APC AP8000 series Rack PDUs or IT equipment with built-in locking receptacles. These locking connectors reduce the probability of accidentally disconnecting cords and dropping loads.

Lead time Usually in Stock

Main

| | |
|----------------------------------|------------------|
| Product or Component Type | Power cord |
| Main Output Voltage | 120 V |
| Input Connection Type | NEMA 5-15P |
| Cable length | 9.84 ft (3.00 m) |
| Number of cables | 1 |

Physical

| | |
|----------------------------|-----------------------|
| Color | Black |
| Height | 9.06 in (23 cm) |
| Width | 9.06 in (23 cm) |
| Depth | 1.8 in (4.5 cm) |
| Net Weight | 1.12 lb(US) (0.51 kg) |
| Mounting preference | No preference |
| Mounting Mode | Not rack-mountable |

Input

| | |
|-----------------------------|------|
| Max line current | 15 A |
| Input current limits | 15 A |

Output

| | |
|---|-----------------|
| Maximum Total Current Draw per Phase | 15 A |
| Number of power socket outlets | 1 IEC 60320 C19 |
| Cord Length | 10 ft (3.05 m) |

Conformance

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

| | |
|-------------------------------|-------------------------|
| Product Certifications | CSA PSE UL Listed |
|-------------------------------|-------------------------|

Environmental

| | |
|--|--|
| Ambient Air Temperature for Operation | 32...221 °F (0...105 °C) |
| Relative Humidity | 20...80 % |
| Operating altitude | 0...10000 ft |
| Ambient Air Temperature for Storage | -13...221 °F (-25...105 °C) |
| Storage Relative Humidity | 20...80 % |
| Storage altitude | 0...50000 ft (0.0000000000...15240.0000000000 m) |

Ordering and shipping details

| | |
|--------------------------|---------------------------|
| Category | 11309-APC RESALE PRODUCTS |
| Discount Schedule | APC1 |
| GTIN | 731304279730 |
| Returnability | No |
| Country of origin | CN |

Packing Units

| | |
|-------------------------------------|-----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 9.06 in (23 cm) |
| Package 1 Width | 1.8 in (4.5 cm) |
| Package 1 Length | 9.06 in (23 cm) |
| Package 1 Weight | 1.12 lb(US) (0.51 kg) |
| SCC14 | 10731304279737 |

Contractual warranty

| | |
|-----------------|---------------------------|
| Warranty | 2 years repair or replace |
|-----------------|---------------------------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Lead Free

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Circularity Profile

[End of Life Information](#)

California Proposition 65

WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov