


CEILING LOUDSPEAKER

Quam C5/BU/SW

C5/BU/SW consists of an 8" O.D., dual cone loudspeaker with a 5 oz. magnet, a 5W, 25/70V transformer, and a square, screw-mount baffle with a white, powder coat finish. It is designed for paging/intercom applications that require a high efficiency speaker and clear, accurate sound.



APPLICATION	Intended Use: Program Material:	Indoor environment Signal tones, voice and music
AUDIO PERFORMANCE	Average Sensitivity: Loudspeaker Power Rating: Maximum Power Rating: Calculated Output: Magnet Type & Weight: Frequency Response: Nominal Coverage Angle: Audio Connection:	92 dB SPL, 1W/1M 12W RMS, EIA 426A Standard 15W @ 8 Ohms 98dB SPL, 4W/1M BeFe Ceramic, 5 oz. Nominal 65Hz - 17kHz, EIA 426A Standard 100° Included Angle, -6dB/2kHz, Half Space 7", Color-coded, Pre-tinned Leads
COMPONENT	Dimensions: Combined Weight: Loudspeaker Model: Loudspeaker Specs: Transformer: Baffle: Finish:	11 1/2" (H) x 11 1/2" (W) x 2 1/2" (D) 3.5 lbs. 8C5PAX 8" O.D. loudspeaker, 5 oz. magnet TBLU: 5W, 25/70V, with 5 taps (0.31W, 0.63W, 1.25W, 2.5W, 5.0W) BS8W: square, steel, screw-mount White powder coat finish
RECOMMENDED QUAM COMPONENTS	Enclosures: Mounting Supports:	ES-8, ES-8S, ES8-6, SE1WVP, SE1WVPS, SE2WVP SSB-2, SSB-3, SSB-7

