

Product data sheet

Specifications



Rack PDU 2G, Switched, ZeroU, 20A, 208V, (7) C13 & (1) C19, L620 Cord

AP8958NA3

Overview

Presentation	APC Switched Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and active monitoring. Remote outlet level controls allow power on/off functionality for power recycling to remotely reboot equipment and restrict unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, locking IEC receptacles, and low profile circuit breakers. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched Rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager.
---------------------	---

Lead time	Usually in Stock
------------------	------------------

Main

Color	Black
Product or Component Type	PDU
PDU Type	Switched
Cord length	9.84 ft (3.00 m)
Number of cables	1
Provided Equipment	Installation guide Locking input power cord Rack Mounting brackets Serial configuration cable Safety guide

Complementary

Input Voltage	200 V 208 V 230 V
Height	38.9 in (98.8 cm)
Width	2.2 in (5.6 cm)
Output Voltage	200 V 208 V 230 V 240 V
Depth	1.8 in (4.6 cm)
Net Weight	7.12 lb(US) (3.23 kg)
Mounting Location	Side
Mounting preference	No preference

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Input Plug Type	NEMA L6-20P
Mounting Mode	Not rack-mountable
Rack units	0U
USB compatible	No
Mounting position	Vertical
Line Rated Current	16 A
Acceptable Input Voltage	200...240 V
Input current limits	20 A
Load Capacity	3300 VA
Input Frequency	50/60 Hz
Outlet type and quantity	7 IEC 60320 C13 1 IEC 60320 C19

Environment

Product Certifications	cUL Listed PSE UL Listed VCCI Class A VDE
Standards	EN 55022 Class A EN 55024 EN 61000-3-2 EN 61000-3-3 FCC Part 15 class A ICES-003
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)

Ordering and shipping details

GTIN	731304277125
-------------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	44.3 in (112.5 cm)
Package 1 Width	4.5 in (11.4 cm)
Package 1 Length	6.5 in (16.5 cm)
Package 1 Weight	12.1 lb(US) (5.5 kg)

Contractual warranty

Warranty	2 years repair or replace
-----------------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH


Resource performance


 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Lead Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)
