

Specifications

Eaton PC3368-3511



Eaton REPO rack PDU, 2U, 8.64 kW max, 120/208V WYE, 24A, 15 ft cord, Three-phase WYE

General specifications

PRODUCT NAME	Eaton REPO Rack PDU
CATALOG NUMBER	PC3368-3511
PRODUCT LENGTH/DEPTH	0.01 in
PRODUCT HEIGHT	0.01 in
PRODUCT WIDTH	0.01 in
PRODUCT WEIGHT	0.01 lb
COMPLIANCES	Contact Manufacturer
CERTIFICATIONS	Contact Manufacturer

Physical

MOUNTING DIRECTION Horizontal

COLOR Black

FORM FACTOR 2U

Electrical input

CORD LENGTH 15 ft

WATTAGE 8.64 kW max

AMPERAGE RATING 24A

INPUT VOLTAGE 120/208V WYE

PHASE Three-phase WYE

FREQUENCY RATING 50-60 Hz

Electrical output

CIRCUIT BREAKER 3P 30A, 1P 20A, 2P 15A, (2)
2P 20A

OUTLET CONTROL No

Additional specifications

OPERATING TEMPERATURE 0° to 60°C (32° to 140°F)

SERIES RE

Resources

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - PC3368-3511](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.