



DisplayPort Monitor Cable

DisplayPort Male / DisplayPort Male, 1 m (3.3 ft.), Black

Part No.: **306935**

High-definition performance for personal computing.

Manhattan DisplayPort Cables provide a single-cable solution that delivers both high-definition digital audio and video signals between desktop and notebook computers and an output device. With 17.28 Gbps bandwidth (HBR2), DeepColor and 24-bit, 8-channel uncompressed audio capability, the 20-pin connector is small, compact and ideal for use with DisplayPort-equipped computers, flat-panel displays, slim-profile devices and many consumer electronics including Blu-ray players and game consoles. Full foil and braided shielding, molded boots with strain relief, protective PVC jackets and gold-plated connections help Manhattan DisplayPort Cables provide maximum conductivity and clear, crisp signal transmissions with reduced EMI interference and distortion.

Features:

- DisplayPort 20-pin male to DisplayPort 20-pin male latching connections
- Delivers high-bandwidth, digital audio/visual signals from PC to display and other DisplayPort-enabled devices — up to 4K@60hz resolution
- Supports HDMI and DVI signal passthrough
- Fully shielded to reduce EMI and other interference sources
- Plug and play for box-to-box applications
- Molded PVC boot
- Lifetime Warranty

Specifications:

Standards and Certifications

- UL 20276
- DisplayPort v1.2

Connectors

- DisplayPort 20-pin male with latches (2)
- Nickel plated
- Molded PVC boot

Cable

- 28 AWG connectors
- Shielding: aluminum and Mylar braid
- Withstanding voltage: 300 VDC

- Insulation resistance: 5 MOhm
- Contact resistance: 10 Ohm
- PVC jacket

Package Contents

- DisplayPort Monitor Cable

