

Xerox® DocuMate® 4799

Versatile High-Speed Scanner Provides Extra Performance for Heavy Scanning Demands

- 100 ppm / 200 ipm*
- A3 (11" x 17") paper size
- ADF holds 250 pages†
- Stapled Document Detection
- 3 Ultrasonic Double Feed Detection Sensors
- Color Space Compatibility with Xerox® iGen™ Digital Press
- Pre- & Post-Scan Imprinter (*sold separately*)
- Intelligent Feed Control
- Multi Color Dropout
- Easy Maintenance

* Landscape US letter and A4, b&w, gray & color.
† 20 lb., 75-80 g/m² paper

Overcome Your Fear of Difficult Documents

Versatility, high-speed and superior reliability make the Xerox® DocuMate 4799 a powerful scanner for demanding environments. With up to a 40,000 page per day duty cycle, this innovative workhorse scans up to 100 pages per minute and employs three advanced sensor systems: ultrasonic double feed detection, stapled document detection and intelligent feed control to ensure that your scan job will not get interrupted.

Documents of various sizes can be stacked together in the automatic feed tray without worry because the Xerox® DocuMate 4799 employs not one, but three ultrasonic double feed detection sensors to cover the entire width of a document. The scanner has another set of sensors designed to detect staples anywhere in a document. As soon as a staple is detected, the scanning process is halted — minimizing damage to the optical glass and your documents. A third set of sensors constantly monitors the thickness of documents being fed into the scanner and

automatically adjusts the roller pressure to ensure that all pages are accurately fed. This combination of sensors creates one of the most reliable feed mechanisms available today.

Up to 250 mix-sized documents can be stacked in the center of the automatic feeder. There is no need to organize documents according to their size, so scanning is fast, easy and efficient. A pre- and post-scan imprinter is also available for the Xerox® DocuMate 4799 and is supported through the included TWAIN™ and ISIS® drivers.

Advanced Image Processing Technology

The Xerox® DocuMate 4799 provides both high quality image enhancement and increased productivity with Kofax® VRS™ Professional AIPE-EBC for auto-everything scanning, including Auto Rotation, Blank Page Deletion and Auto Color Detect. VRS Professional improves your workflow and reduces the total time needed to scan even the largest volumes of mixed batch documents. Taken together, the Xerox® DocuMate 4799 and the Kofax VRS Professional bundle translate into real and measurable savings — fewer manual steps, reduced storage requirements and less operator intervention.

The DocuMate 4799 also employs a device-independent color space that is compatible with the Xerox® iGen™ digital press so that you can be assured that the color fidelity of your original translates to the output of your real time digital press.

When the occasional paper jam happens, the Xerox® DocuMate 4799 is very easy to maintain. Its unique “clamshell” design allows full access to the entire paper path, so you can clear paper jams or clean the unit without calling a service technician. The rollers are easy to replace, improving the unit’s cost effectiveness, and have a long service life.



Xerox® DocuMate 4799 Product Specifications

SKU Number (US)	XDM47995D-WU
SKU Number (Euro/UK)	XDM47995E-WU
Scan Speed	100 ppm / 200 ipm (black & white, grayscale, or color @ 150, 200, or 300 dpi, landscape A4 and US letter)
Scan Method	Dual Color Contact Image Sensor (CCFL light source), switchable black or white background
Optical Resolution	600 dpi
Output Bit Depth	24-bit color, 8-bit grayscale, 1-bit black & white
Interface	Hi-speed USB 2.0 (1.1 compatible)
Dimensions	18.7"(w) x 23"(d) x 13"(h) (474 x 585 x 329 mm)
Weight	55 lbs (25 kg)
ADF Minimum Document Size	1.9" x 2.8" (48 mm x 70 mm)
ADF Maximum Document Size	11.7" x 17" (297 x 432 mm); custom lengths up to 100" (2,540 mm)
ADF Capacity	250 sheets (20 lb., 75-80 g/m ² paper)
Duty Cycle	40,000 pages/day

Box Contents

- DocuMate 4799 Scanner
- Quick Installation Guide
- Technical Support Card
- Blower w/Brush
- Roller Cleaning Paper, Cleaning Paper Card
- Shading Sheet, Shading Caution Leaflet
- DFP Roller Pad
- Hopper Cushion
- Stacker Pad
- AC Power Cord US (1), Euro/UK (2)
- USB Cable
- DVD-ROM including:
 - User's Manual
 - Kofax® VRS™ Professional AIPE-EBC
 - Nuance® OmniPage® Pro
 - Visioneer OneTouch® with Kofax VRS technology
 - Scanner Drivers: TWAIN™, EMC Captiva ISIS®, Microsoft® Windows® Image Acquisition (WIA) Driver

PC Minimum System Requirements

- Intel® Pentium® 4 or equivalent processor
- Windows 7 / Windows Vista® / Windows XP®
- 1 GB RAM (512 MB for Windows XP)
- 350 MB available hard disk space
- CD/DVD-ROM drive
- USB port

For more information about the Xerox line of scanners, visit www.xeroxscanners.com



© 2011 Xerox Corporation. All rights reserved. XEROX®, XEROX and Design®, DocuMate® and DocuShare® are trademarks of, or licensed to Xerox Corporation in the United States and/or other countries. Visioneer and OneTouch® are trademarks of Visioneer, Inc. Kofax®, VirtualReScan® and VRS™ are trademarks of Kofax, Inc. Nuance® and OmniPage® are trademarks of Nuance Communications, Inc. or its affiliates in the United States and/or other countries. Microsoft®, SharePoint®, Windows Vista®, Windows®, the Windows logo and XP® are trademarks of Microsoft Corporation in the United States and/or other countries. Intel® and Pentium® are trademarks of Intel Corporation in the U.S. and/or other countries. Universal Serial Bus is a trademark of USB Implementers Forum, Inc. (USB-IF). TWAIN™ is a trademark of TWAIN Working Group. EMC®, Captiva®, ISIS® and QuickScan™ are trademarks of EMC Corporation. All other trademarks are the property of their respective owners and are hereby acknowledged. Prices, features, specifications, capabilities, appearance and availability of Xerox products and services are subject to change without notice. 04/11

