

155 Mbps 1310nm Multi Mode LC Fiber SFP Transceiver w/ DDM - 2km

StarTech ID: SFPF1302C



The SFPF1302C Fiber Optic Transceiver w/ DDM (2km) offers a cost-effective way to add, replace or upgrade a Multimode LC port on your 100 Mbps fiber networking equipment or fiber media converter.

Featuring data rates of up to 155 Mbps and support for Digital Diagnostics Monitoring (DDM), this LC SFP module can be installed into any networking device with an SFP Multi-Sourcing Agreement (MSA) compliant, or Cisco compliant port.

Delivering convenience and scalability, this fiber transceiver is fully hot-pluggable, enabling you to install the module without interrupting network traffic or requiring a device reboot.

Backed by a StarTech.com 3-year warranty and free lifetime technical support.

Applications

- Replacing defective or damaged SFPs in MSA compliant or Cisco equipment
- Expand your network to remote segments

Features

- Supports data transfer rates up to 155 Mbps
- Supports distances up to 2 km (1.2 miles)
- Complies with SFP Multi-Source Agreements standards (MSA)
- Compatible with Cisco® equipment
- LC Fiber connector
- Fully Hot Pluggable

Technical Specifications

| | |
|-------------------------------|---|
| Warranty | 3 Years |
| WDM | No |
| Industry Standards | IEEE 802.3u 100BASE-FX |
| Local Unit Connectors | 1 - Fiber Optic LC Female |
| Maximum Data Transfer Rate | 155 Mbps |
| Max Transfer Distance | 2 km (1.2 mi) |
| Fiber Type | Multi Mode |
| Wavelength | 1310nm |
| Fiber Operating Mode | Half/Full-Duplex |
| Note | For use in 100 Mbps fiber networking equipment and media converters |
| Product Length | 2.6 in [65 mm] |
| Product Width | 0.4 in [9 mm] |
| Product Height | 0.6 in [14 mm] |
| Product Weight | 0.9 oz [25 g] |
| Operating Temperature | 0°C to 70°C (32°F to 158°F) |
| Storage Temperature | -40°C to 85°C (-40°F to 85°F) |
| Humidity | 30~70% RH |
| System and Cable Requirements | MSA or Cisco compliant SFP port |
| Shipping (Package) Weight | 0.1 lb [0 kg] |
| Included in Package | 1 - 155 Mbps Multi Mode LC SFP |

Certifications, Reports and Compatibility

