

Product data sheet

Specifications



APC Smart-UPS X, Line Interactive, 3kVA, Rack/tower convertible 2U, 208V-230V, 8x C13+1x C19 IEC, Network card, Extended runtime

SMX3000RMHV2UNC

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead time	Usually in Stock


Main

Main Input Voltage	208 V 230 V
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	208 V 220 V 240 V
Kw Rating	2700 W
Rated power in VA	3000 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	BS1363A British IEC 320 C20 Schuko CEE 7 / EU1-16P
output connection type	8 IEC 320 C13 2 IEC Jumpers 1 IEC 320 C19
number of rack unit	2U
Cable length	8 ft (2.4 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Rack Mounting support rails Smart UPS signalling RS-232 cable Temperature Probe User Manual Web/SNMP Management Card
Range of Product	Smart-UPS

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Extendable Run Time	1
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Replacement battery	APCRBC117 
Battery Charge Power (Watts)	245 W rated

General

Number of power module	2400
Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	Network card pre-installed
Redundant	No

Physical

color	Black
Height	3.3 in (8.5 cm)
Width	17.008 in (43.2 cm)
Depth	26.3 in (66.7 cm)
Net Weight	82.28 lb(US) (37.32 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	140...280 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	3000 VA
Max Configurable Power (Watts)	2700 W
Transfer Time	2-4 ms 6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	C-tick CE EAC GOST IRAM VDE UK PSTI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic level	55 dBA
Online Thermal Dissipation	184 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control panel	Multi-function LCD status and control console
Emergency Power Off (EPO)	Yes
Free slots	0
Pre-Installed SmartSlot™ Cards	Network management card 3 with environmental monitoring
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rating	645 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

Category	11309 - APC RESALE PRODUCTS
GTIN	731304272694
Returnability	No
Country of origin	PH

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.6 in (24.3 cm)
Package 1 Width	23.5 in (59.6 cm)

Package 1 Length	34.2 in (86.9 cm)
Package 1 Weight	100.002 lb(US) (45.36 kg)
Unit Type of Package 2	PAL
Number of Units in Package 2	8
Package 2 Height	46.9 in (119 cm)
Package 2 Width	39.4 in (100 cm)
Package 2 Length	47.2 in (120 cm)
Package 2 Weight	843.05 lb(US) (382.4 kg)
Pallet unit layers	2
Pallet layers	4

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery, optional extended warranties available, optional on-site warranties available
-----------------	--

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH


Resource performance

 Energy Efficient Product

 Take-Back Program Available

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov