

2 Port PCI Express / PCI-e Parallel Adapter Card – IEEE 1284 with Low Profile Bracket

StarTech ID: PEX2PECP2



The PEX2PECP2 2 Port PCI Express Parallel Adapter Card - EPP/ECP/SPP/PS2 parallel card adds two IEEE 1284 parallel ports to your PC, with support for parallel data communication at speeds of up to 1.5 Mbps.

This high performance 2 Port PCI Express parallel card adds 2 DB25 parallel ports, perfect for connecting printers, scanners, memory card readers, bar code scanners and more. With the added convenience of plug-and-play capability, installing the parallel adapter card is hassle-free. The PCIe Parallel card also includes both standard and half-height/low profile mounting brackets for compatibility with almost any system form factor.

Backed by a StarTech.com Lifetime Warranty and free lifetime technical support.

Applications

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers

Features

- Supports Standard Parallel Port(SPP), Enhanced Parallel Port(EPP), Enhanced Capability Port(ECP) and PS/2
- Data transfer rate up to 1.5 Mbps
- Standard and low-profile brackets included

Technical Specifications

Warranty	Lifetime
Ports	2
Bus Type	PCI Express
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Chipset ID	ASIX/MosChip - MCS9865
Connector Type(s)	1 - PCI Express x1 Male
External Ports	2 - DB-25 (25 pin; D-Sub) Female
Maximum Data Transfer Rate	1.5 Mbps
OS Compatibility	Windows® 8 (32/64), 7 (32/64), Vista(32/64), XP(32/64), 2000 Windows® Sever 2008 R2, 2003 (32/64) Linux
Product Length	4.8 in [121 mm]
Product Width	0.7 in [19 mm]
Product Height	3.4 in [86 mm]
Product Weight	1.8 oz [51 g]
Humidity	5~85% RH, Non-condensing
Operating Temperature	0°C to 40°C (32°F to 122°F)
Storage Temperature	-20°C to 60°C (-4°F to 140°F)
Shipping (Package) Weight	0.4 lb [0.2 kg]
Included in Package	1 - 2 Port PCIe Parallel Card
Included in Package	2 - Low Profile Brackets
Included in Package	1 - Driver CD
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

