

DC2 Desktop Charger for 9d24 and i75

Features

- Tilted design for stable operation of handset
- Allows loud speaking function
- Confirmation beep indicates start of charging
- Charging status indicated in handset display
- Headset can be connected during charging
- Handset can automatically send absent indication in charger



Technical Specifications

Physical

Dimensions (l × w × h):	143 × 92 × 46 mm
Weight:	135 g
Material:	Case: PC/ABS High friction polyurethane footing
Colour:	Dark grey Light grey (Medic)

Functional

Supply voltage:	100-240 V AC 50-60 Hz 150 mA
Output voltage:	5 V DC 1 A (Only use the provided power supply)

Charging

Charging time for 9d24:	1 h
Charging time for 9d24 MkII:	2 h
Charging time for i75:	2-4 h

Environmental

Operation temperature:	0°C – +40°C
Storage temperature:	-20°C – +70°C
Relative humidity:	30 – 85% (non condensing)
Enclosure protection:	IP30, EN 60529

Compliance to European regulations and standards

EU directives:	73/23/EEC(LVD), 89/336/EEC(EMC)
Product marking:	CE
EMC:	EN 55022 (class B), EN 55024
LVD:	IEC 60950-1:2001 and EN 60950-1:2001, A11:2004 First Edition

Compliance to other regulations and standards

Product marking (AUS):	C
Safety (AUS):	IEC 60950 3Ed.
Safety (USA and Canada)	IEC 60950-1CB Bulletin No. 107A, May 2004

Specifications are subject to change without notice.