


HSM® SECURIO

B22 office shredder

Compact for use at home or a small office



- Energy Management Control System EcoSmart: particularly low power consumption of 0.1 watt in standby mode
- Automatic start/stop function with integrated reverse
- Shred bin level indicator
- Removable waste container for effortless emptying
- Folding safety element
- Cutting rollers are V-TEK by HSM with specially hardened steel rollers. This optimum design of all cutting unit components saves valuable energy.
- Continuous motor operation
- Quiet Operation feature shreds documents with a pleasantly, quiet operating sound
- 11 gallon waste bag capacity; Part #HSM1310



HSM part#	HSM1830	HSM1831	HSM1833	HSM1832
Cutting type	Strip cut	Strip cut	Cross cut	Micro cut
Cutting size	1/8"	1/4"	1/8" x 1 1/8"	1/16" x 9/16"
Security level DIN 32757-1	2	2	3	4
Security level DIN 66399	P-2 / T-2 / E-2	P-2 / O-2 / T-2 / E-2	P-4 / T-4 / E-3 / F-1	P-5 / T-5 / E-4 / F-2
Cutting capacity per run in sheets	16 - 18	22 - 24	12 - 14	9 - 11
Cutting speed	16 ft / min	16 ft / min	16 ft / min	16 ft / min
Throat opening	9.4"	9.4"	9.4"	9.4"
Motor at max. no. of sheets	440W	440W	440W	440W
Motor power (horsepower)	0.59	0.59	0.59	0.59
Voltage	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz
Dimensions (H x W x D)	23.1" x 14.8" x 11.3"	23.1" x 14.8" x 11.3"	23.1" x 14.8" x 11.3"	23.1" x 14.8" x 11.3"
Weight	26.5 lbs	26.5 lbs	28.6 lbs	28.6 lbs
Shred-bin volume	8.7 gallons	8.7 gallons	8.7 gallons	8.7 gallons
Cutting capabilities				

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM®