



Part Number SPAN104-1025TL
 Basic, Surge
 Power Configuration 20A, 120V, 1.9kW
 Physical Configuration 19 in / 483 mm Horizontal



| | |
|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description | SPAN104-1025TL is ideal for smaller environments that don't have protective surge suppression at the facility level, or just when additional protection is needed. Parallel circuitry keeps the SPAN104-1025TL working as a power strip, even if a surge or spike disables surge suppression. |
| Product Summary | SPAN104-1025TL - Surge, 20A, 120V, Horizontal, (10) NEMA 5-20R, breakered, 10 ft power cord with L5-20P, Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input , Aggregate - Total Unit Monitoring |
| Monitoring | Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input |
| Plug Form |  L5-20P |
| Receptacle |  NEMA 5-20R (Quantity: 10) |



SPAN104-1025TL - Product Specification and Options

| | |
|-----------------------------------------|---------------------------------------------------------------------------------------------------|
| Monitoring | Current - Local Digital RMS Current Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input |
| Monitoring Level 1 | Aggregate - Total Unit Monitoring |
| Quantity Of Inputs | 1 |
| Voltage | 120V |
| Current | 20A |
| VA per Input (Load Capacity) | 1.9kW |
| Frequency | 50/60 Hz |
| Over Current Protection | 20A Thermal Breaker |
| Switch | No |
| Indicators - LED(s) | 1 - Power ON Green LED |
| Power Cable Wire Gauge | 12/3 |
| Power Cable Length | 10ft |
| Plug Type | NEMA L5-20P Twistlock |
| Receptacle/Socket Type #1 | NEMA 5-20R |
| Quantity on Rear #1 | 10 |
| Quantity per Breaker #1 | 10 |
| Style #1 | Duplex |
| Maximum Output per Receptacle/Socket #1 | 20A |
| Voltage per Receptacle/Socket #1 | 120V |
| Joule Rating | 720 |
| UL 1449 Rating (500A) | 330V |
| Clamping Level | < 315V |
| Response Time | < 5 nanoseconds |
| Technology Used | Super MOVs |
| Surge Indicator Red LED | Yes |
| Heavy Steel -Black Powder Coat | Yes |
| Configuration | 19in / 435mm Horizontal Rackmount |
| Flush Mount | Yes |
| Made in the USA | Yes |
| Product Warranty | Three Year |
| Connected Equipment Warranty | Three Year - \$5000 |
| Certification/Agency Approvals | RoHS Compliant |
| Certification/Agency Approvals | UL & c-UL Listed 60950 |
| Chassis Dimensions (HxWxD) | 1.72in x 17in x 4.50in |
| Shipped Weight | 8lbs (3.63kg) |

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,

Geist Asia

Hong Kong
Tel: +852 90361927

Email: salesasia@geistglobal.com

www.geistglobal.com

+44 (0) 1823 275100
www.geisteurope.com

Guangdong Province, China.
Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com