

## Composite and S-Video to VGA Video Scan Converter

StarTech ID: VID2VGATV2



The VID2VGATV2 Composite and S-Video to VGA Video Scan Converter (with Scaler) provides a simple way to convert Composite or S-Video signals to VGA (or Component RCA) output, for use with computer monitors, projectors or HDTV sets.

Equipped with an On-Screen Display (OSD) menu and dip switches for simple configuration and selection of your video output settings, this compact video scaler installs quickly and easily for a true plug-and-play experience. An integrated scaler circuit dynamically converts the S-Video or Composite video input signal, giving you multiple output resolutions to choose from, to ensure compatibility with your display or projector.

Plus, the Component/S-Video-VGA Converter includes a VGA to Component (RCA) breakout cable, which enables you to connect to TV sets that are not equipped with a VGA port.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

### Applications

- Perfect for displaying video from DVD players, VCRs or legacy Game Consoles on VGA projectors and HDTV sets
- Display camcorder output on televisions or monitors equipped with VGA input
- Monitor security cameras with S-Video or composite signaling using VGA monitors or televisions
- Adapt VHS video in the classroom to newer televisions
- Convert legacy Medical Imaging equipment for display on computer monitors
- Use in boardrooms for adapting legacy video equipment to work with new projectors

## Features

- Convert and scale Composite/S-Video input to VGA/Component output
- Accepts NTSC and PAL input
- On-Screen Display for simple output setting selection
- VGA to Component (YPbPr) RCA Adapter included
- 50 Hz to 60 Hz frame rate conversion
- Plug & Play installation - no drivers or software required

## Technical Specifications

Warranty	2 Years
Converter Type	Scaler
Audio	No
Connector A	1 - Composite Video (1 x RCA) Female
Connector A	1 - S-Video (4 pin; Mini-DIN) Female
Connector B	1 - VGA (15 pin; High Density D-Sub) Female
Supported Resolutions	PC: 1600x1200, 1280x1024, 1024x768 HDTV: 480p (50/60Hz), 576p (50Hz), 720p (50/60Hz), 1080p (50/60Hz)
Color	Black
Enclosure Type	Plastic
Product Length	4.4 in [112 mm]
Product Width	2.5 in [64 mm]
Product Height	1 in [26 mm]
Product Weight	3.2 oz [90 g]
LED Indicators	1 - Composite (Yellow) / S-Video (Red) input indicator
Power Adapter Included	Yes
Output Voltage	5 DC
Output Current	1A
Power Consumption	2.5W
Operating Temperature	0°C to 40°C (32°F to 104°F)
Storage Temperature	0°C to 60°C (32°F to 140°F)
Humidity	0~60% RH
Shipping (Package) Weight	1 lb [0.5 kg]
Included in Package	1 - Video Converter/Scaler
Included in Package	1 - VGA to Component (RCA) breakout cable
Included in Package	1 - Universal Power Adapter
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

