



Panasonic recommends Windows® 7.

THE TOUGHBOOK H2

- Intel® Core™ i5 vPro™ Processor
- Sealed Fanless All-weather Design
- Sunlight-viewable Up to 6000 Nit in Direct Sunlight
- USB, Serial and Ethernet Ports
- Long-life Hot-swappable Twin Batteries Provide Limitless Hours of Use
- Available Built-in Camera, RFID and SmartCard and Barcode Readers
- Choice of 3G Gobi™ or 4G LTE Mobile Broadband

IP65

6-FOOT
DROP RATING

MIL-STD-
810G

THE INDUSTRY'S MOST RUGGED HANDHELD TABLET PC.

The rugged Panasonic Toughbook® H2 handheld tablet PC is the ultimate productivity tool for mobile workers. With superior ergonomics, a brilliant 10.1" sunlight-viewable LED screen capable of up to 6000 nit in direct sun and sealed all-weather design, the Toughbook H2 lets you work virtually anywhere. Designed with a magnesium alloy chassis encased in polycarbonate, the IP65 and MIL-STD-810G certified¹ Toughbook H2 delivers a complete range of integrated wireless features including Wi-Fi, Bluetooth® and optional embedded 4G LTE or 3G Gobi™ mobile broadband. Add to that fast charging hot-swappable twin batteries for maximum uptime, optional integrated GPS and SmartCard reader, and you've got a handheld tablet PC that is unmatched in the field.



1.800.662.3537

panasonic.com/toughbook/H2

SOLUTIONS

IS OUR MIDDLE NAME

DURABILITY

- MIL-STD-810G certified (6' drop, shock, vibration, rain, dust, sand, altitude, freeze/thaw, high/low temperature, temperature shock, humidity, explosive atmosphere)¹
- IP65 certified¹ sealed all-weather design
- Hard drive heater
- Magnesium alloy chassis encased with polycarbonate
- Shock-mounted flex-connect hard drive
- Integrated handle and ergonomic rubber hand strap
- Reinforced locking port covers

SOFTWARE

- Genuine Windows® 7 Professional 32-bit² or Genuine Windows® 7 Professional 64-bit²
- Panasonic Utilities (including Dashboard and Cleaning Reminder Tool), Recovery DVD

CPU

- Intel® Core™ i5-2557M vPro™ Processor
 - 1.7GHz with Turbo Boost up to 2.7GHz
 - Intel® Smart Cache 3MB

STORAGE & MEMORY

- 4GB SDRAM (DDR3-1333MHz), expandable to 8GB^{3,4}
- 320GB 7200rpm hard drive (shock-mounted and flex-connect)⁴
 - Optional 128GB reinforced flex-connect SSD⁴

DISPLAY

- 10.1" XGA sunlight-viewable LED 1024 x 768 dual touch
 - TransfectivePlus and Panasonic CircuLumin™ technology
 - 1-6000 nit (depending on lighting conditions and settings)⁵
 - Anti-reflective, anti-glare screen treatments and circular polarizer
 - Ambient light sensor
- Intel® QM67 video controller, max 1563MB shared VRAM with 32-bit⁶
- External video support up to 1280 x 1024 at 16.7 million colors
- Concealed mode

AUDIO

- Intel® high-definition audio compliant
- Integrated speaker

KEYBOARD & INPUT

- Dual touch LCD (touchscreen and digitizer)
- Integrated stylus holder
- 74-key on-screen keyboard with dedicated Windows® key
- Up to 5 user-defined programmable buttons (varies by model)

INTERFACE

- Docking connector Dedicated 19-pin
- Serial D-sub 9-pin
- USB 2.0 (opt. 2nd USB port)⁷ 4-pin
- 10/100/1000 Ethernet RJ-45

WIRELESS

- Optional integrated 4G LTE mobile broadband
- Optional integrated 3G Gobi™ mobile broadband
- Intel® Centrino® Advanced-N 6205 802.11a/b/g/n
- Bluetooth® v2.1 + EDR (Class 1)
- Security
 - Authentication: LEAP, WPA, 802.1x, EAP-TLS, EAP-FAST, PEAP
 - Encryption: CKIP, TKIP, 128-bit and 64-bit WEP, Hardware AES

POWER SUPPLY

- Twin hot-swappable Li-ion battery packs
 - 7.2V, typical 3400mAh, minimum 3200mAh each battery
- Battery operation: 6.5 hours (with both batteries)⁸
- Battery charging time: 3 hours on⁹
- AC Adapter: AC 100V-240V 50/60Hz, auto sensing/switching worldwide power supply

POWER MANAGEMENT

SECURITY FEATURES

- Suspend/Resume Function, Hibernation, Standby, ACPI BIOS
- Password Security: Supervisor, User, Hard Disk Lock
- Kensington cable lock slot (on optional cradle)
- Trusted platform module (TPM) security chip v.1.2
- Computrace® theft protection agent in BIOS⁹
- Intel® Anti-Theft Technology
- Fingerprint reader
- Insertable SmartCard reader
- Contactless SmartCard reader

WARRANTY

DIMENSIONS & WEIGHT

- 3-year limited warranty, parts and labor
- 10.8"(L) x 10.6"(W) x 2.3"(H)
- 3.5 lbs. (with handle, strap and both batteries)

INTEGRATED OPTIONS¹⁰

- 4G LTE mobile broadband
- 3G Gobi™ mobile broadband (EV-DO Rev. A, HSPA)
- GPS receiver
- 3MP camera with auto focus and LED light
- Barcode reader
- Insertable SmartCard reader
- 13.56MHz Contactless RFID and SmartCard reader
 - ISO 15693 and 14443 A/B compliant
- Fingerprint reader
- 2nd USB port (replaces Ethernet port)
- 128GB solid state drive (SSD)

1.800.662.3537 / panasonic.com/toughbook/H2

Financing options now available from Panasonic Finance Solutions; please call number above for more details.

Panasonic is constantly enhancing product specifications and accessories. Specifications subject to change without notice. Trademarks are property of their respective owners. ©2012 Panasonic Corporation of North America. All rights reserved.



SAFETY CERTIFICATIONS

- IT Equipment Safety (EN:EU, UL:US) EN/IEC 60950-1 UL 60950-1
- Medical Electrical Equipment Safety (EU) EN/IEC 60601-1 (with battery operation) CAN/CSA-C22.2 No.601.1-M90
- Medical Electrical Equipment Safety (Canada) FCC CFR 47 P.15 Sub B-Class B EN 55022/CISPR 22-Class B EN 55024 EN 55011/CISPR 11-Class B FCC CFR 47 P.15 Sub C RSS-210 FCC CFR 47 P.2
- IT Equipment EMI (US)
- IT Equipment EMI (EU)
- IT Equipment EMS (EU)
- Industrial EMI (EU)
- Radio (US)
- Radio (Canada)
- SAR (US)

ACCESSORIES¹⁰

- AC Adapter (3-prong) CF-AA6373AM
- Lithium Ion Battery Pack CF-VZSU53AW
- 4-Bay Battery Charger CF-VGBU11U
- LIND Car Adapter 120W CF-LNDDC120
- LIND Car Adapter 120W Mounting Bracket CF-LNDBRK120
- LIND Car/AC Adapter 90W (with USB port) CF-LNADCDC90
- LIND Car Adapter 90W MIL-STD CF-LNDMLDC90
- LIND Car Adapter 80W CF-LNDDC80
- LIND Shutdown Timer CF-LNDLPT
- InfoCase H2 Shoulder Strap TBCH1SS-BLK-P
- InfoCase H2 Inversion Strap TBCH1SSINV-P
- InfoCase H2 Always-on Sleeve TBCH2SLVE-P
- InfoCase H2 Vinyl Always-on Sleeve TBCH2VNLVSLV-P
- InfoCase U1/H2 Battery Pouch TBCU1BPCH-P
- LaCie External USB Multi Drive TT-DVDRW8XL91U
- Desktop Cradle/Spare 2-Bay Battery Charger CF-VEBH21KU
- Memory Card 4GB DDR3 CF-WMBA1004G
- Magnetic Micro-dock (USB x2, LAN) CF-VEBH12U
- Gamber-Johnson Wall/Cart Mount 7160-0358
- Gamber-Johnson Wall/Cart Mount (no electronics) 7160-0359
- Gamber-Johnson Vehicle Dock (no pass-through) 7160-0348
- Gamber-Johnson Vehicle Dock (no electronics) 7160-0349
- Replacement Stylus CF-VNP011U
- Tether CF-VNT003U
- 10.1" LCD Protector Film CF-VPF13AU

Please consult your reseller or Panasonic representative before purchasing.

¹Tested by a national independent third party lab following MIL-STD-810G Method 516.6 Procedure IV for transit drop test and IEC 60529 Sections 13.4, 13.6.2, 14.2.5 and 14.3 for IP65. Stylus has passed IP65 testing but has not been certified.

²A full set of Windows XP drivers are available at panasonic.com/toughbook/support.

³Total usable memory will be less depending upon actual system configuration.

⁴1GB = 1,000,000,000 bytes.

⁵500 nit without ambient light assistance. Up to 6000 nit in clear, sunny conditions under direct sunlight.

⁶The size of the VRAM cannot be set by the user and varies by operating system as well as size of RAM. Windows 7 64-bit max. VRAM is 1696MB with 4GB of memory.

⁷Replaces Ethernet port.

⁸Battery performance features such as charge time and life span can vary according to the conditions under which the computer and battery are used. Battery operation and recharge times will vary based on many factors, including screen brightness, applications, features, power management, battery conditioning and other customer preferences. Battery testing results from MobileMark 2007.

⁹Requires software and activation to enable theft protection.

¹⁰Accessories and Integrated Options may vary depending on your configuration.