

Epson WorkForce AL-M300DT



The WorkForce AL-M300DT is one of Epson's most hardworking and reliable A4 monochrome laser printers, thanks to its 100,000-page duty cycle - the highest in its class¹. This model has a compact footprint that suits individual desktop users and comes with up to 550-sheet paper capacity as standard.

Aimed at desktop users who are looking for high productivity, this model offers reliable, high-performance printing as well as fast, double-sided printing.

The Workforce AL-M300DT also offers consistently fast printing up to 35ppm², with a first-page-out time of 5.5 seconds, as well as high-quality results up to 1,200dpi resolution. Internal memory can also be increased to 1152Mb, to help process all business printing needs.

High-performance is teamed up with reliable printing, thanks to high-yield toners and a heavy-duty output, which provides an excellent return on investment.

The reliability of the WorkForce AL-M300DT allows businesses to concentrate on their work without the inconvenience of downtime, enhancing productivity and providing greater peace of mind.

DATASHEET



KEY FEATURES

- 100,000-page duty cycle
- 35ppm monochrome printing
- 5.5 second first-page-out time
- Double-sided printing and low CPP
- 550-sheet capacity

PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Resolution	1,200 dpi
Toner System	AcuBrite

PRINT

Printing Speed	35 Pages/min Monochrome single-sided, 21 Pages/min Monochrome double-sided
First Page Out	Monochrome 6 Seconds
Warm Up time	18 s
Max Duty cycle	100,000 Pages per month

CONNECTIVITY

Interfaces	USB 2.0 Type B, IEEE 1284
------------	---------------------------

PAPER / MEDIA HANDLING

Paper Formats	A4, A5, A6, B5, C6 (Envelope), DL (Envelope), LT, HLT, LGL, GLG, GLT, EXE, F4, MON, Custom: Width: 76.2 - 215.9mm / Length: 127 - 355.6mm
Duplex	Yes
Output Tray Capacity	150 Sheets
Number of Paper Trays	3 Trays

GENERAL

Supply Voltage	AC 220 V - 240 V, 50 Hz - 60 Hz
Temperature	Operation 5° C - 32° C, Storage 20° C - 40° C
Humidity	Operation 15% - 85%, Storage 15% - 85%
Safety Standards	IEC60950-1, EN60950-1, IEC60825-1, EN60825-1
Electrical Standards	Energy Star Compliant
EMI Standard	EN55022, EN55024, EN61000-3-3

OTHER FEATURES

Processor Speed	600 MHz
Memory	128 MB included, 1152 MB maximum
Emulations	PCL5c, PCL6, ESC/P, ESC/P2, ESC/Page, PostScript 3, PDF 1.6, FX, I239X

OTHER

Warranty	12 months On site service
LCD screen	Type: Monochrome, 22 characters x 5 Lines

LOGISTICS INFORMATION

SKU	C11CC63011BZ
Barcode	8715946529417

Epson WorkForce AL-M300DT

WHAT'S IN THE BOX

- Initial toner cartridges
- Main unit
- Power cable
- Setup guide
- Software (CD)
- Warranty Documents

SUPPLIES

- 3yrs on-site swap
- 128 MB Additional Memory for C9300N series 7106919
- 256 MB Additional Memory for C9300N series 7106920
- 512 MB Additional Memory for C9300N series 7106921
- 1 GB Additional Memory for C9300N series 7106922
- 3yr CoverPlus Pack 30 LP SESHQ2180
- COVERPLUS-Paket (36 month On-Site-Service)
- Service Pack N° 35
- 3yrs return to base

OPTIONAL ACCESSORIES

- 128 MB Additional Memory for C9300N series 7106919
- 256 MB Additional Memory for C9300N series 7106920
- 512 MB Additional Memory for C9300N series 7106921
- 1 GB Additional Memory for C9300N series 7106922

For more information please contact:

Telephone: 0871 222 6702 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

+ Calls cost 10p per minute plus network extras.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

1. - Comparison made against the top 10 workgroup monochrome laser printers (31ppm to 39ppm) sold in Western Europe in Q4 2012 as tracked by IDC. Duty cycle information as published by manufacturers in January 2013. 2 - Determined in accordance with ISO/IEC 24734 showing the average of ESAT / FSOT from the Office Category Test for default simplex /duplex. For more information visit www.epson.eu/testing

EPSON®