

HSM® SECURIO

P36 professional shredder

Large Volume, High Performance



- Uses Energy Management Control System (EMCS) to deal with energy in a sensible manner by reducing energy consumption up to 90%
- Automatically switches to energy-saving mode in 2 minutes after last use; switches off entirely if not used for 1 hour; temporary mode for small shredding jobs; and permanent mode for large shredding jobs
- Multifunctional control key with reversing function
- Shred bin level indicator
- Folding safety element
- Cutting rollers are V-TEK by HSM with specially hardened steel rollers. This optimum design of all cutting unit components saves valuable energy.
- Continuous duty operation
- Special CD waste container included for separation of shredded material
- Automatic oiler for cross-cut version only
- Awarded the Blue Angel Certification for sustainability
- Equipped with Anti-Jam Technology to easily and quickly reverse out paper in the event the machine is overloaded
- 58 gallon waste bag capacity; Part #HSM2117



HSM part#	HSM1850	HSM1851	HSM1853	HSM1852
Cutting type	Strip cut	Strip cut	Cross cut	Micro cut
Cutting size	1/8"	1/4"	3/16" x 1 1/8"	1/16" x 9/16"
Security level DIN 32757-1	2	2	3	4
Security level DIN 66399	P-2 / O-2 / T-2 / E-2	P-2 / O-2 / T-2 / E-2	P-4 / O-3 / T-4 / E-3 / F-1	P-5 / T-5 / E-4 / F-2
Cutting capacity per run in sheets	37 - 39	47 - 49	29 - 31	18 - 20
Cutting speed	18 ft / min	18 ft / min	18 ft / min	18 ft / min
Throat opening	13"	13"	13"	13"
Motor at max. no. of sheets	1600W	1600W	1600W	1600W
Motor power (horsepower)	2.15	2.15	2.15	2.15
Voltage	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz	115 V / 60 Hz
Dimensions (H x W x D)	36.9" x 22.8" x 21.7"	36.9" x 22.8" x 21.7"	36.9" x 22.8" x 21.7"	36.9" x 22.8" x 21.7"
Weight	141 lbs	141 lbs	150 lbs	150 lbs
Shred-bin volume	38.3 gallons	38.3 gallons	38.3 gallons	38.3 gallons
Cutting capabilities				

All technical specifications are approximate values. Technical and design modifications reserved.

HSM of America, LLC
419 Boot Road
Downingtown, PA 19335
www.hsmofamerica.com
Customer Service: 800.613.2110

Great Products, Great People.

HSM®