

# Product data sheet

Specifications



APC Smart-UPS, Line Interactive, 3kVA, Rackmount 2U, 120V, 6x NEMA 5-15R+NEMA 5-20R outlets, SmartSlot, AVR, LCD, TAA

SMT3000RMUS

## Overview

Lead time Usually Ships within 3 Weeks

## Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Kw Rating	2700 W
Rated power in VA	2880 VA
Product or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	NEMA L5-30P
output connection type	6 NEMA 5-15R 2 NEMA 5-20R
number of rack unit	2U
Cable length	8 ft (2.4 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software Documentation CD Installation guide Rack mounting hardware Rack Mounting support rails Smart UPS signalling RS-232 cable USB cable
Range of Product	Smart-UPS

## Batteries & Runtime

Run Time	<a href="#">View Runtime Graph</a>
Efficiency	<a href="#">View Efficiency Graph</a>
Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery life	3...5 year(s)
Replacement battery	<a href="#">RBC43</a>

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

---

Battery Charge Power (Watts)	188 W rated
------------------------------	-------------

## General

---

Number of power module filled slots	0
Number of power module free slots	0
product web sub-family	TAA compliance
Redundant	No

## Physical

---

color	Black
Height	3.4 in (8.6 cm)
Width	18.9 in (48 cm)
Depth	26.9 in (68.3 cm)
Net Weight	97.62 lb(US) (44.28 kg)
Mounting Location	Front
Mounting preference	Lower
Mounting Mode	Rack-mounted
Two post mountable	0
USB compatible	Yes

## Input

---

Efficiency at full load	75...154 V adjustable 82...144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

## Output

---

Harmonic distortion	Less than 5%
Maximum configurable power in VA	2880 VA
Max Configurable Power (Watts)	2700 W
Transfer Time	4ms typical : 8ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

## Conformance

---

Product Certifications	CSA TAA compliance
Equipment protection policy	Lifetime : \$150000

## Environmental

---

Acoustic level	55 dBA
Online Thermal Dissipation	348 Btu/h
Operating altitude	0...10000 ft

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.0000000000...15240.0000000000 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

## Communications & Management

Control panel	Multi-function LCD status and control console
Free slots	1
Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rating	459 J
---------------------	-------

## Ordering and shipping details

GTIN	731304305637
Country of origin	PH

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	10.0000000000 in (25.4 cm)
Package 1 Width	38.6 in (98 cm)
Package 1 Length	23.6 in (60 cm)
Package 1 Weight	114.0 lb(US) (51.7 kg)

## Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

## Resource performance

Energy Efficient Product

Take-Back Program Available

## Well-being performance

Mercury Free

Rohs Exemption Information [Yes](#)

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

**California Proposition 65** WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)