




Part Number SPFC104-10
 Basic, Surge
 Power Configuration 15A, 120V, 1.4kW
 Physical Configuration 19 in / 483 mm Horizontal



Description	SPFC104-10 is ideal for smaller environments that don't have protective surge suppression at the facility level, or just when additional protection is needed. Parallel circuitry keeps the SPFC104-10 working as a power strip, even if a surge or spike disables surge suppression.
Product Summary	SPFC104-10 - Surge, 15A, 120V, Horizontal, (10) NEMA 5-15R, power switch, breaker, 10 ft power cord with 5-15P, Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input, , Aggregate - Total Unit Monitoring
Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Plug Form	 5-15P
Receptacle	 NEMA 5-15R (Quantity: 10)



SPFC104-10 - Product Specification and Options

Monitoring	Power - Local (A, V, W, PF) Digital RMS Scrolling Power Meter +/- 2% Accuracy with Full Scale 60Hz sine wave input
Monitoring Level 1	Aggregate - Total Unit Monitoring
Quantity Of Inputs	1
Voltage	120V
Current	15A
VA per Input (Load Capacity)	1.4kW
Frequency	50/60 Hz
Over Current Protection	15A Thermal Breaker
Switch	Yes
Indicators - LED(s)	1 - Power ON Green LED
Power Cable Wire Gauge	12/3
Power Cable Length	10ft
Plug Type	NEMA 5-15P
Receptacle/Socket Type #1	NEMA 5-15R
Quantity on Face #1	10
Quantity per Breaker #1	10
Style #1	Duplex
Maximum Output per Receptacle/Socket #1	15A
Voltage per Receptacle/Socket #1	120V
Joule Rating	720
UL 1449 Rating (500A)	330V
Clamping Level	< 315V
Response Time	< 5 nanoseconds
Technology Used	Super MOVs
Surge Indicator Red LED	Yes
Heavy Steel -Black Powder Coat	Yes
Configuration	19in / 435mm Horizontal Rackmount
Adjustable Mount Brackets	Yes
Made in the USA	Yes
Product Warranty	Three Year
Connected Equipment Warranty	Three Year - \$5000
Certification/Agency Approvals	RoHS Compliant
Certification/Agency Approvals	UL & c-UL Listed 60950
Chassis Dimensions (HxWxD)	1.72in x 17in x 4.50in
Shipped Weight	7lbs (3.18kg)

Geist Americas

1821 Yolande Ave
Lincoln, NE 68521 USA
1.800.432.3219 or
1.402.474.3400
www.geistglobal.com

Geist Europe

Unit 1, The Monarch Centre,
Venture Way,
Priorswood, Taunton,
Somerset, TA2 8DE UK
+44 (0) 1823 275100

Geist Asia

China
Tiley Plaza Bldg. A, Unit #2808,
No. 199 Haide 3 Road,
Nanshan Shenzhen,
Guangdong Province, China.

Geist Asia

Hong Kong
Tel: +852 90361927
Email: salesasia@geistglobal.com

www.geisteurope.com

Postal Code: 518000
Tel: +86.755.86639505
www.geistglobal.com