

Cisco Wireless Services Module 2 Controller for Catalyst 6500 Series Switches

<p>MAXIMUM PERFORMANCE AND SCALABILITY</p> <ul style="list-style-type: none"> • Support for up to 500 access points and 10,000 clients • Designed for line-rate performance with Datagram Transport Layer Security (DTLS) encryption and Access Control Lists (ACL) security enabled • 802.11n-optimized for up to nine times the performance of 802.11a/g networks • Enhanced uptime with the ability to simultaneously configure, upgrade and manage 500 access points per controller • Reduced down time with the ability to pre-download access point images during upgrades
<p>REQUIREMENTS</p> <ul style="list-style-type: none"> • Requires Sup720 with -E chassis or a non-E chassis with high speed fan • Requires Sup software 12.2(33)SXJ or higher • Controller software 7.0.116.0 or higher
<p>IMPROVED MOBILITY AND SERVICES</p> <ul style="list-style-type: none"> • Larger mobility domain for more simultaneous client associations • Faster radio resource management updates for uninterrupted network access when roaming • Intelligent RF control plane for self-configuration, self-healing, and self-optimization • Efficient roaming improves application performance such as toll quality voice and consistent streaming video and data backup
<p>LICENSING FLEXIBILITY AND INVESTMENT PROTECTION</p> <ul style="list-style-type: none"> • Additional access point and feature licenses may be added over time
<p>COMPREHENSIVE WIRED AND WIRELESS SECURITY</p> <ul style="list-style-type: none"> • Full Control and Provisioning of Wireless Access Points (CAPWAP) access point to controller encryption • Supports detect of rogue access point and denial-of-service attacks • Management frame protection detects malicious users and alerts network administrators
<p>CISCO OFFICEEXTEND SOLUTION</p> <ul style="list-style-type: none"> • Secure, simple, cost-effective mobile teleworker solution • Up to 500 remote access points per controller • Supports Cisco® Unified Communications wireless phones for reduced cell phone charges
<p>ENTERPRISE WIRELESS MESH</p> <ul style="list-style-type: none"> • Dynamic wireless mesh networks support indoor and outdoor connectivity for areas that are difficult to wire
<p>ENVIRONMENTALLY RESPONSIBLE</p> <ul style="list-style-type: none"> • Support for adaptive power management to turn off access point radios during off-peak hours to reduce power consumption • OfficeExtend solution reduces costs and supports green best practices by reducing commuting time and saving on gas, vehicle mileage, and insurance costs

Cisco Wireless Services Module 2 (WiSM2) for Catalyst 6500 Series Switches

The Cisco® Wireless Service Module 2 (WiSM2) Controller for Catalyst 6500 Series Switches, shown in Figure 1, is a highly scalable and flexible platform that enables systemwide services for mission-critical wireless in medium-sized to large enterprises and campus environments. Designed for [802.11n](#) performance and maximum scalability, the WiSM2 controller supports a higher density of clients and delivers more efficient roaming, with at least nine times the throughput of existing 802.11a/g networks. The WiSM2 controller offers enhanced uptime with the ability to simultaneously manage up to 500 [access points](#); superior performance for reliable streaming video and toll quality voice; and improved fault recovery for a consistent [mobility](#) experience in the most demanding environments.

Figure 1. Cisco Catalyst 6500 Series WiSM2 Controller



Features

As a component of the Cisco Unified Wireless Network, this controller provides realtime communication between [Cisco Aironet® access points](#), the [Cisco Wireless Control System \(WCS\)](#), and the [Cisco Mobility Services Engine](#) to deliver centralized security policies, wireless intrusion prevention system (IPS) capabilities, award-winning RF management, and quality of service (QoS). With CleanAir technology the WiSM2 protects 802.11n performance by providing cross-network access to real-time and historic RF interference information for quick, troubleshooting and resolution. This integrated approach to large-scale wireless networking, customers can realize significant total cost of ownership (TCO) benefits by streamlining support costs and reducing planned and unplanned network downtime.

Software Licensing Flexibility

Cisco WiSM2 Controller software licensing offers the flexibility to add additional access points (up to 500 access points) as business needs grow.

As part of its basic feature set, the Cisco WiSM2 controller supports a variety of business mobility needs, including the Cisco OfficeExtend solution for secure, mobile teleworking and Enterprise Wireless Mesh, which allows access points to dynamically establish wireless connections in locations where it may be difficult or impossible to physically connect to the wired network.

Table 1 lists the features and benefits of the Cisco Wireless Service Module 2 (WiSM2) Controller.

Table 1. Cisco WiSM2 Controller Features and Benefits

Feature	Benefits
Scalability	<ul style="list-style-type: none"> Supports 100, 300, and 500 access points for business-critical wireless services at locations of all sizes
High Performance	<ul style="list-style-type: none"> Wired-network speed, nonblocking performance for 802.11n networks
RF Management	<ul style="list-style-type: none"> Provides both real-time and historical information about RF interference impacting network performance across controllers, via systemwide Cisco CleanAir technology integration
High-Performance Video	<ul style="list-style-type: none"> Integrates Cisco VideoStream technology as part of the Cisco medianet framework to optimize the delivery of video applications across the WLAN
End-to-end Voice	<ul style="list-style-type: none"> Supports Unified Communications for improved collaboration through messaging, presence, and conferencing Supports all Cisco Unified Communications Wireless IP Phones for cost-effective, real-time voice services
Comprehensive End-to-End Security	<ul style="list-style-type: none"> Offers Control and Provisioning of Wireless Access Points (CAPWAP)-compliant Datagram Transport Layer Security (DTLS) encryption to help ensure full-line-rate encryption between access points and controllers across remote WAN/LAN links
OfficeExtend	<ul style="list-style-type: none"> Supports corporate wireless services for mobile and remote workers with secure wired tunnels to the Cisco Aironet® 600, 1130, or 1140, 3500 Series Access Points Extends the corporate network to remote locations with minimal setup and maintenance requirements (zero-touch deployment) Improves productivity and collaboration at remote site locations Separate service set identifier (SSID) tunnels allow both corporate and personal Internet access Reduced carbon dioxide emissions from a decrease in commuting Higher employee job satisfaction from ability to work at home Improves business resiliency by providing continuous, secure connectivity in the event of disasters, pandemics, or inclement weather
Enterprise Wireless Mesh	<ul style="list-style-type: none"> Allows access points to dynamically establish wireless connections without the need for a physical connection to the wired network Available on select Cisco Aironet access points, Enterprise Wireless Mesh is ideal for warehouses, manufacturing floors, shopping centers and any other location where extending a wired connection may prove difficult or aesthetically unappealing
PCI Integration	<ul style="list-style-type: none"> Part of Payment Card Industry (PCI) certified architecture, and well-suited for retail customers who deploy transactional data applications such as scanners and kiosks
Environmentally Responsible	<ul style="list-style-type: none"> Organizations may choose to turn off access point radios to reduce power consumption during off-peak hours

Table 2 lists the product specifications for Cisco WiSM2 Wireless Controller.

Table 2. Product Specifications for Cisco WiSM2 Controller

Item	Specifications
Wireless	<ul style="list-style-type: none"> IEEE 802.11a, 802.11b, 802.11g, 802.11d, WMM/802.11e, 802.11h, 802.11n
Wired/Switching/Routing	<ul style="list-style-type: none"> IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX specification, 1000BASE-T, 1000BASE-SX, 1000BASE-LH,

Item	Specifications
	IEEE 802.1Q Vtagging, and IEEE 802.1AX Link Aggregation
Data Request for Comments (RFC)	<ul style="list-style-type: none"> • RFC 768 UDP • RFC 791 IP • RFC 2460 IPv6 (pass through Bridging mode only) • RFC 792 ICMP • RFC 793 TCP • RFC 826 ARP • RFC 1122 Requirements for Internet Hosts • RFC 1519 CIDR • RFC 1542 BOOTP • RFC 2131 DHCP • RFC 5415 CAPWAP Protocol Specification
Security Standards	<ul style="list-style-type: none"> • WPA • IEEE 802.11i (WPA2, RSN) • RFC 1321 MD5 Message-Digest Algorithm • RFC 1851 The ESP Triple DES Transform • RFC 2104 HMAC: Keyed Hashing for Message Authentication • RFC 2246 TLS Protocol Version 1.0 • RFC 2401 Security Architecture for the Internet Protocol • RFC 2403 HMAC-MD5-96 within ESP and AH • RFC 2404 HMAC-SHA-1-96 within ESP and AH • RFC 2405 ESP DES-CBC Cipher Algorithm with Explicit IV • RFC 2407 Interpretation for ISAKMP • RFC 2408 ISAKMP • RFC 2409 IKE • RFC 2451 ESP CBC-Mode Cipher Algorithms • RFC 3280 Internet X.509 PKI Certificate and CRL Profile • RFC 3602 The AES-CBC Cipher Algorithm and Its Use with IPsec • RFC 3686 Using AES Counter Mode with IPsec ESP • RFC 4347 Datagram Transport Layer Security • RFC 4346 TLS Protocol Version 1.1
Encryption	<ul style="list-style-type: none"> • WEP and TKIP-MIC: RC4 40, 104 and 128 bits (both static and shared keys) • AES: CBC, CCM, CCMP • DES: DES-CBC, 3DES • SSL and TLS: RC4 128-bit and RSA 1024- and 2048-bit • DTLS: AES-CBC • IPsec: DES-CBC, 3DES, AES-CBC
Authentication, Authorization, and Accounting (AAA)	<ul style="list-style-type: none"> • IEEE 802.1X • RFC 2548 Microsoft Vendor-Specific RADIUS Attributes • RFC 2716 PPP EAP-TLS • RFC 2865 RADIUS Authentication • RFC 2866 RADIUS Accounting • RFC 2867 RADIUS Tunnel Accounting • RFC 3576 Dynamic Authorization Extensions to RADIUS • RFC 3579 RADIUS Support for EAP • RFC 3580 IEEE 802.1X RADIUS Guidelines • RFC 3748 Extensible Authentication Protocol • Web-based authentication • TACACS support for management users
Management	<ul style="list-style-type: none"> • SNMP v1, v2c, v3 • RFC 854 Telnet • RFC 1155 Management Information for TCP/IP-Based Internets • RFC 1156 MIB • RFC 1157 SNMP • RFC 1213 SNMP MIB II • RFC 1350 TFTP • RFC 1643 Ethernet MIB • RFC 2030 SNTP

Item	Specifications
	<ul style="list-style-type: none"> • RFC 2616 HTTP • RFC 2665 Ethernet-Like Interface types MIB • RFC 2674 Definitions of Managed Objects for Bridges with Traffic Classes, Multicast Filtering, and Virtual Extensions • RFC 2819 RMON MIB • RFC 2863 Interfaces Group MIB • RFC 3164 Syslog • RFC 3414 User-Based Security Model (USM) for SNMPv3 • RFC 3418 MIB for SNMP • RFC 3636 Definitions of Managed Objects for IEEE 802.3 MAUs • Cisco private MIBs
Management Interfaces	<ul style="list-style-type: none"> • Web-based: HTTP/HTTPS • Command-line interface: Telnet, Secure Shell (SSH) Protocol, serial port • Cisco Wireless Control System (WCS)
Interfaces and Indicators	<ul style="list-style-type: none"> • Service port: 1000 Mbps Ethernet Internal • Redundancy port: 1000 Mbps Ethernet Internal • Console port: RS232 (DB-9 male/RJ-45 connector included), mini-USB • Status indicators: Power, System, Alarm, Console, USB
Physical and Environmental	<ul style="list-style-type: none"> • Dimensions (W x D x H): 1.6 x 15.3 x 16.3 in. (4.0 x 37.9 x 40.3 cm) • Weight: 11 lbs (54.99 kg) • Temperature: Operating temperature: 32 to 104°F (0 to 40°C); Storage temperature: -40 to 167°F (-40 to 75°C) • Humidity: Operating humidity: 10 to 95%, noncondensing; Storage humidity: up to 95% • Input power: 225W maximum; Test conditions: 104°F (40° C), Full Traffic Most deployments and environments would use less power • Heat Dissipation: 768 Btu/h Maximum; Test Conditions: 104°F (40°C), Full Traffic
Regulatory Compliance	<ul style="list-style-type: none"> • CE Mark • Safety: <ul style="list-style-type: none"> • UL 60950-1:2003 • EN 60950:2000 • EMI and susceptibility (Class A): • U.S.: FCC Part 15.107 and 15.109 • Canada: ICES-003 • Japan: VCCI • Europe: EN 55022, EN 55024

Table 3 lists the ordering information for Cisco WiSM2 Controller.

Table 3. Ordering Information for Cisco WiSM2 Controller

Part Number	Description	Cisco SMARTnet® 8x5xNBD Part Number
WS-SVC-WISM2-1-K9(=)	Wireless Services Module:WiSM-2: w/ 100 AP Support License	CON-SNT-WSM2100
WS-SVC-WISM2-3-K9(=)	Wireless Services Module:WiSM-2: w/ 300 AP Support License	CON-SNT-WSM2300
WS-SVC-WISM2-5-K9(=)	Wireless Services Module:WiSM-2: w/ 500 AP Support License	CON-SNT-WSM2500

Additive Capacity Upgrade Licenses

Table 4 shows the additive capacity upgrade licenses are available for the Cisco WiSM2 Controller.

Table 4. Ordering Information for Cisco WiSM2 Wireless Controller Additive Capacity Licenses (e-Delivery Product Authorization Keys [PAKs])

Part Number	Description	Cisco SMARTnet 8x5xNBD Part Number
L-LIC-WISM2-UPG	Primary upgrade SKU: Pick any number or combination of the following options under this SKU to upgrade one or many controllers under one product authorization key	
L-LIC-WISM2-100A	100 AP Adder License for WiSM-2 (e-Delivery)	CON-SNT-LWSM21A
L-LIC-WISM2-200A	200 AP Adder License for WiSM-2 (e-Delivery)	CON-SNT-LWSM22A

Table 5. Ordering Information for Cisco WiSM2 Wireless Controller Additive Capacity Licenses (Paper PAKs)

Part Number	Description	Cisco SMARTnet 8x5xNBD Part Number
LIC-WISM2-UPG	Primary upgrade SKU: Pick any number or combination of the following options under this SKU to upgrade one or many controllers under one product authorization key	
LIC-WISM2-100A	100 AP Adder License for WiSM-2 (e-Delivery)	CON-SNT-LWISM21A
LIC-WISM2-200A	200 AP Adder License for WiSM-2 (e-Delivery)	CON-SNT-LWISM22A

Table 6 shows the Optional Paper PAK license to enable DTLS. Designed for customers who purchase a controller with DTLS disabled due to import restrictions. This optional license will allow you to take advantage of DTLS for OfficeExtend functionality in the future.

Table 6. Optional Paper PAK license to enable DTLS

Part Number	Description
LIC-WISM2-DTLS-K9=	Data DTLS License for WiSM2

Service and Support

Cisco and our specialized partners offer a broad portfolio of end-to-end services to help you improve your organization's productivity and collaboration by assisting with the readiness, deployment, and optimization of your wireless network and mobility services. Our services help you successfully deploy the Cisco 6500 Series Wireless Services Module 2 Controller and integrate mobility solutions effectively to lower the total cost of ownership and secure your wireless network.

To learn more about Cisco Wireless LAN Service offers, visit: <http://www.cisco.com/go/wirelesslanservices>.

For More Information

For more information about Cisco wireless controllers, contact your local account representative or visit: <http://www.cisco.com/en/US/products/ps6366/index.html>.

For more information about the Cisco Unified Wireless Network framework, visit: <http://www.cisco.com/go/unifiedwireless>.



Americas Headquarters
Cisco Systems, Inc.
San Jose, CA

Asia Pacific Headquarters
Cisco Systems (USA) Pte. Ltd.
Singapore

Europe Headquarters
Cisco Systems International BV Amsterdam,
The Netherlands

Cisco has more than 200 offices worldwide. Addresses, phone numbers, and fax numbers are listed on the Cisco Website at www.cisco.com/go/offices.

Cisco and the Cisco Logo are trademarks of Cisco Systems, Inc. and/or its affiliates in the U.S. and other countries. A listing of Cisco's trademarks can be found at www.cisco.com/go/trademarks. Third party trademarks mentioned are the property of their respective owners. The use of the word partner does not imply a partnership relationship between Cisco and any other company. (1005R)