

# Product data sheet

Specifications



## Rack PDU Extender, Basic, 2U, 30A, 200/208V, (4)L6-30



AP7584

### Overview

Lead time Usually in Stock

### Main

Color	Black
Product or Component Type	PDU
PDU Type	Basic
Cord length	28 ft (8.5 m)
Number of cables	1
Provided Equipment	Installation guide Rack Mounting brackets

### Complementary

Input Voltage	200 V 208 V
Height	3.5 in (8.9 cm)
Width	17.2 in (43.7 cm)
Output Voltage	208 V
Depth	3.5 in (8.9 cm)
Net Weight	14.02 lb(US) (6.36 kg)
mounting location	Front Rear
Mounting preference	Lower
Input Plug Type	NEMA L14-30P
Mounting Mode	Rack-mounted
Rack units	2U
Mounting position	Horizontal
Line Rated Current	24 A
Input current limits	30 A
Load Capacity	4992 VA
Input Frequency	50/60 Hz
Outlet type and quantity	4 NEMA L6-30R

### Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

<b>Product Certifications</b>	cUL Listed METI Denan UL Listed
<b>Standards</b>	CSA C22.2 No. 107.1 UL 1778
<b>Ambient Air Temperature for Operation</b>	32.0000000000...113.0000000000 °F (0...45 °C)
<b>Relative Humidity</b>	0...95 %
<b>Operating altitude</b>	0...10000 ft
<b>Ambient Air Temperature for Storage</b>	-13.0000000000...149.0000000000 °F (-25...65 °C)
<b>Storage Relative Humidity</b>	0...95 %
<b>Storage altitude</b>	0...50000 ft (0.0000000000...15240.0000000000 m)

## Ordering and shipping details

<b>GTIN</b>	731304222569
<b>Country of origin</b>	IN

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	6.0 in (15.2 cm)
<b>Package 1 Width</b>	20.5 in (52.1 cm)
<b>Package 1 Length</b>	20.5 in (52.1 cm)
<b>Package 1 Weight</b>	16.03 lb(US) (7.27 kg)

## Contractual warranty

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)




Energy Efficient Take-back Transparency RoHS/REACH

## Resource performance

 Energy Efficient Product

 Take-Back Program Available

## Well-being performance

 Lead Free

## Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

[End of Life Information](#)