

GV-SD220 Indoor Full HD IP Speed Dome



- 1/2.8" Progressive Scan CMOS sensor
- Full HD 1080p at up to 30 fps and 720p at up to 60 fps
- 20x optical zoom and 12x digital zoom
- H.264 and MJPEG video compression
- Dual streams
- IR-cut filter for day and night function
- 4 digital inputs, 1 relay output
- Memory Card Slot
- Auto focus
- Wide Dynamic Range pro (WDR pro)
- Backlight Compensation
- Image noise reduction
- Pan 360° endlessly
- Tilt from 0° up to 180°
- Preset speed at up to 460° /sec
- PTZ movement (Preset, Sequence, Auto Pan, Cruise and Tour)
- PTZ movements by schedule
- Auto and manual PTZ calibration
- Motion detection
- Privacy Mask
- 2-way audio
- Supports iPhone, iPad, Android & 3GPP
- 31 languages on Web interface
- ONVIF conformant


* No memory card slot & local storage function for Argentina

INTRODUCTION

The GV-IP Speed Dome is a network PTZ camera designed for image quality and adaptability in various environments. This camera offers image of 1080p at 30 fps, 720p at 60 fps and 20x optical zoom, capable of showing smooth live view with great detail. In low-light environments, image quality is promised with its image processing tools, such as IR cut filter (ICR), Wide Dynamic Range pro (WDR pro), Backlight Compensation and noise reduction.

Wide surveillance coverage is made possible with 360° endless panning and 180° tilting capacity. Dome movements such as Preset, Sequence, Auto Pan, Cruise and Tour can be programmed and activated by schedule. You can create multiple dome movement modes and have different modes enabled at different time slots. The GV-IP Speed Dome provides variable pan/tilt speeds ranging from a fast patrol of 460° per second to a slow ramble of 0.5° per second with 0.2° pan accuracy for fast and accurate tracking ability.

DIMENSION



SPECIFICATIONS

Camera		
Image Sensor		1/2.8" CMOS
Optical Zoom		20x
Digital Zoom		12x
Effective Pixels		2M
Video Output		Internet
S/N Ratio		50 dB (AGC Off)
Minimum Illumination	Color	0.05 Lux at F/1.6
	B/W	0.005 Lux at F/1.6
Focal Length		4.7 ~ 94 mm
Focus Mode		Auto / Manual
White Balance		Auto / Manual
Iris Control		Auto / Manual
Electronic Shutter		1/1 ~ 1/10000 sec
AGC control		Auto / Manual
Back Light Compensation		On / Off
WDR pro		Yes
Video		
Video Codec		H.264, MJPEG
Video Resolution	16:9	1920 x 1080, 1280 x 720, 640 x 360, 448 x 252
Frame Rate		30/25 fps (60/50 Hz) at 1920 x 1080
		60/50 fps (60/50 Hz) at 1280 x 720
Audio		
Audio input/output		2-way audio, stereo jack, Ø 35 mm
Audio Codec		G.711, AAC (16 kHz / 16 bit)
Network		
Interface		10/100 Base-T Ethernet, RJ-45 connector
Protocol		DHCP, DynDNS, FTP, HTTP, HTTPS, NTP, ONVIF, QoS (DSCP), RTSP, SNMP, SMTP, TCP, UDP, UPnP, 3GPP/ISMA
Mechanical		
Temperature Detector		Yes
Connectors	Power	DC Jack
	Local Storage	SD / SDHC / SDXC memory card slot (for Class 6 or above)
	Digital I/O	I/O wires
Web Interface		
Installation Management		Web-based configuration
Firmware Upgrade		Remote upgrade through Web Browser, IP Device Utility included in the Software CD
Access from Web Browser		live view, video recording, PTZ control, Preset, Sequence, Cruise, Auto Pan, Tour, image quality settings, bandwidth control, image snapshot, I/O control, 2-way audio, Picture-in-Picture (PIP), Picture-and-Picture (PAP), Wide Angle Lens Dewarping (WALD), Text Overlay, image masking
Language		Arabic / Bulgarian / Czech / Danish / Dutch / English / Finnish / French / German / Greek / Hebrew / Hungarian / Indonesian / Italian / Japanese / Lithuanian / Norwegian / Persian / Polish / Portuguese / Romanian / Russian / Serbian / Simplified Chinese / Slovakian / Slovenian / Spanish / Swedish / Thai / Traditional Chinese / Turkish
Operation		
Pan Travel		360° endless
Tilt Travel		0° ~ 180°
Movement Speed		0.5° ~ 460°/s
Calibration		Auto / Manual
Presets	Max. Number	255
	Accuracy	0.2°
Sequence	Max. Number	8
	Max. Presets Allowed	16
Auto Pan		8
Cruise		4
Tour	Max. Number	8
	Max. Number of Preset / Sequence / Auto Pan / Cruise	16

Privacy Mask	8	
Proportional Pan & Tilt	On/Off (Pan and tilt speed proportional to zoom ratio)	
Automatic Function	Preset, Sequence, Auto Pan, Cruise, Tour	
Mechanical Flip	On / Off	
Digital Slow Shutter	On / Off	
Motion Detection	On / Off	
Day/Night: Mechanical IR Cut Filter	On / Off	
Picture Flip	On / Off	
Image Freeze	On / Off	
Digital Noise Reduction	On / Off	
Alarm	Input	4
	Output	1
	Reaction	Preset, Sequence, Auto pan, Cruise, Tour

General	
Operating Temperature	-10°C ~ 50°C / 14°F ~ 122°F
Humidity	20% ~ 90% (non-condensing)
Dimensions	Ø 177 x 221.9 mm / 7 x 8.8 in
Weight	3.2 Kg / 7.1 lb
Power Source	24V AC ± 10%, 3A / 24V DC ± 10%, 3.75A
Power Consumption	30 W
Regulatory	CE, FCC, RoHS

Applications	
Network Storage	GV-NVR, GV-System, GV-Backup Center, GV-Recording Server
Smart Device Access	- GV-Eye for Android smartphone, tablet, iPhone, and iPod Touch- GV-Eye HD for iPad
Live Viewing	IE , GV-MultiView
CMS Server support	GV-Control Center, GV-Center V2, GV-VSM

Note: Specifications are subject to change without notice.

ACCESSORIES

Part Number	Name	Details
GV-Mount907	In-Ceiling Mounting Kit	Dimension: Ø 230 x 153.49 mm / Ø 9.08 x 6.05 in Weight: 0.87 kg / 1.91 lb
		
51-PSD2200-P01U	DC 24V Power Adaptor 100-240VAC US	Dimensions (L x W): 132.75 x 58.6 mm / 5.23 x 2.3 in Weight: 0.39 kg / 0.86 lb Input: 100 to 240V AC 2.5A 50-60Hz Output: 24V DC 3.75 A
51-PSD2200-P01A	DC 24V Power Adaptor 100-240VAC AU	
51-PSD2200-P01B	DC 24V Power Adaptor 100-240VAC AR	
51-PSD2200-P01D	DC 24V Power Adaptor 100-240VAC EU	
51-PSD2200-P01J	DC 24V Power Adaptor 100-240VAC JU	
51-PSD2200-P01C	DC 24V Power Adaptor 100-240VAC UK	
		