

4 Port PCI Express SATA III 6Gbps RAID Controller Card with Heatsink

StarTech ID: PEXSAT34RH



The PEXSAT34RH 4-Port PCI Express SATA III Controller Card adds 4 AHCI SATA III ports to a computer through a PCle slot (x2), delivering multiple internal 6Gbps connections to high-performance hard drives and Solid State Drives (SSDs), all from a single PCle expansion slot.

The PCIe SATA controller card features Port Multiplier (PM) support on each port, which enables multiple SATA drives to be connected through one of the ports over a single cable, for a total of 7 simultaneous drive connections – (Connect up to 4 drives through PM on one port, and a single drive to each of the remaining 3 ports).

Supporting RAID 0, RAID 1 and 1+0 configurations, this versatile PCI Express SATA RAID card includes an onboard heatsink to dissipate heat build-up, to help maintain peak operating performance even at full capacity.

This PCIe SATA 6gbps card is backed by a 2-year StarTech.com warranty and free lifetime technical support.

Applications

- Upgrade an older PCle-based system to SATA 6Gbps capability, to better utilize faster SATA drives
- Add more internal SATA ports to a computer system, to connect additional storage drives and/or optical drives
- Provide optimized off-site back-ups/vaulting, through built-in RAID 1 capability
- Perfect for multi-drive internal RAID storage solutions





Features

- 4 AHCI SATA III (6Gbps) ports through PCI Express x2
- Fully compliant with SATA 3.0 specifications and backward compatible with SATA I/II (1.5/3.0Gbps) drives
- Supports HDDs/SSDs/Optical/Blu-Ray drives
- Compliant with PCI Express 2.0 standards
- Natively supported single chipset design
- Port Multiplier FIS-based and Command-based switching supported
- Supports Native Command Queuing (NCQ) and ATA/ATAPI commands
- Supports hardware RAID 0, 1, and 1+0 modes configured through BIOS
- Onboard heatsink keeps the card running cool
- Includes Low Profile/Half-Height installation bracket
- LED headers for HDD activity LED indicators



Technical Specifications

Warranty 2 Years

Bus Type PCI Express

Card Type Standard Profile (LP bracket incl.)

Chipset ID Marvell 88SE9230 Industry PCI Express 2.0

Standards

Industry Serial ATA 3.0 specification

Standards

Interface SATA

Port Style Integrated on Card

Ports 4

Connector 1 - PCI Express x2 Male

Type(s)

Internal Ports 4 - SATA (7 pin; Data) Plug

Supported JBOD - (Just a Bunch of Disks)

RAID Modes

Supported RAID 1 (Mirrored Disks)

RAID Modes

Supported RAID 0 (Striped Disks)

RAID Modes

Supported RAID 10 (1+0; Striped set of Mirrored Subset)

RAID Modes

LBA support 48-bit

Max Drive Currently tested up to 4TB per drive

Capacity

Port Multiplier Yes

RAID Yes

Type and SATA III (6 Gbps)

Rate

OS Windows XP (32/64-bit)/ Vista (32/64-bit)/ 7 (32/64-bit)/ 8 (32/64-bit)

Compatibility Mac OS 10.6 /10.7 /10.8

Linux

Product 20 mm [0.8 in]

Height

Product 70 mm [2.8 in]

Length

Product 50 g [1.8 oz]





Weight

Product 120 mm [4.7 in]

Width

Humidity 20% ~ 80% RH

5°C ~ 50°C (41°F ~ 122°F) Operating

Temperature

Storage -25°C ~ 70°C (-13°F ~ 158°F)

Temperature

System and Available PCI Express x2 slot (backward compatible with x4, x8, and x16 slots)

Cable

Requirements

Note The maximum throughput of this card is limited by the bus interface. If used with PCI Express Gen

1.0 enabled computers, the max throughput is 2.5 Gbps per lane. If used with PCI Express Gen 2.0

enabled computers, the max throughput is 5 Gbps per lane.

Only one port can use the Port Multiplier feature at a time. Supports up to 4 drives connected via

Port Multiplier, 7 drives total.

Port Multiplier not supported in Mac OS.

Package

1 Quantity

Shipping 145 g [5.1 oz]

(Package) Weight

Included in

1 - PCle SATA Controller Card

Package

Included in 1 - Low Profile Bracket

Package

Included in 1 - Driver CD

Package

1 - Instruction Manual Included in

Package





Certifications, Reports and Compatibility











