

# GRYPHON™ I GFE4400 2D

DATALOGIC



## ADVANCED IMAGING TECHNOLOGY

Using advanced imaging technology, the Gryphon™ GFE4400 2D engine provides a compact and easy-to-use solution for OEM use in self-service kiosks, price verifiers, ticket readers, document handling and medical laboratory applications, as well as vending machines and other automated equipment.


The GFE4400 2D OEM engine features outstanding near-field reading, a wide angle field-of-view, high motion tolerance, snappy reading, and also offers excellent performance on decoding poor or damaged bar codes. The GFE4400 2D OEM engine also offers good-read visual confirmation with Datalogic's patented 'Green Spot' technology.

## RED ILLUMINATING LIGHT AND 4-DOT AIMER

User comfort is maximized with the GFE4400 2D OEM engine's steady, deep red illumination light. Easier on the eyes than competitive products with flicker illumination, the highly visible 4-Dot aimer defines a precise reading zone and reduces accidental reads. The aimer's center cross provides a locator for targeted scanning in a multiple bar code environment.

## 1D AND 2D CAPABILITIES

The GFE4400 2D OEM engine provides snappy reading performance on all common 1D and 2D codes as well as postal, stacked and composite codes like PDF417. For mobile marketing or ticketing applications, this imager also offers excellent performance when reading bar codes from mobile devices.



## FEATURES

- Highly visible 4-Dot aimer with center cross for targeted scanning
- Omnidirectional reading
- Advanced motion tolerance optics
- Image capture and document scanning capabilities
- Reads bar codes down to 4 mils
- Reads 1D, 2D and postal codes plus stacked and composite codes
- Interface options: RS-232 or USB
- Datalogic's patented 'Green Spot' technology for good-read feedback
- Automatic sensing or manual trigger options available
- EASEOFCARE Service Plans offer a wide range of service options to protect your investment, ensuring maximum productivity and ROI

## INDUSTRY-APPLICATIONS

- OEM Applications:
  - Service Kiosks
  - Price Verifiers
  - Ticket Readers
  - Document Handling
  - Medical Laboratories
  - Vending Machines
  - Additional Automated Equipment

# GRYPHON™ I GFE4400 2D



## TECHNICAL SPECIFICATIONS

### DECODING CAPABILITY

1D / LINEAR CODES	Autodiscriminates all standard 1D codes including GS1 DataBar™ linear codes.
2D CODES	Aztec Code; China Han Xin Code; Data Matrix; MaxiCode; Micro QR Code; QR Code
POSTAL CODES	Australian Post; British Post; China Post; IMB; Japanese Post; KIX Post; Korea Post; Planet Code; Postnet; Royal Mail Code (RM4SCC)
STACKED CODES	EAN/JAN Composites; GS1 DataBar Composites; GS1 DataBar Expanded Stacked; GS1 DataBar Stacked; GS1 DataBar Stacked Omnidirectional; MacroPDF; MicroPDF417; PDF417; UPC A/E Composites

### ELECTRICAL

CURRENT	Operating (Typical): < 180 mA Standby/Idle (Typical): Automatic Object Sense Mode: 115 mA Online & Serial OnLine Modes: 65 mA
INPUT VOLTAGE	5 VDC +/- 5%

### ENVIRONMENTAL

AMBIENT LIGHT	0 - 100,000 lux
HUMIDITY (NON-CONDENSING)	5-95%
TEMPERATURE	Operating: -20 to 50 °C / -4 to 122 °F Storage/Transport: -20 to 70 °C / -4 to 158 °F

### INTERFACES

INTERFACES	OEM (IBM) USB; RS-232; USB: USB COM; USB HID Keyboard
------------	--

### PHYSICAL CHARACTERISTICS

DIMENSIONS	2.8 x 4.2 x 4.8 cm / 1.1 x 1.7 x 1.9 in
WEIGHT	USB: 51.2 g / 1.8 oz RS-232: 51.2 g / 1.8 oz

### READING PERFORMANCE

IMAGE CAPTURE	Graphic Formats: BMP, JPEG, TIFF; Greyscale: 256, 16, 2
IMAGER SENSOR	Wide VGA: 752 x 480 pixels
LIGHT SOURCE	Aiming: 650 nm VLD
PRINT CONTRAST RATIO (MINIMUM)	25%
READING ANGLE	Pitch: +/- 40°; Roll (Tilt): 180°; Skew (Yaw): +/- 40°
RESOLUTION (MAXIMUM)	1D Linear: 0.102 mm / 4 mils Data Matrix: 0.178 mm / 7 mils PDF417: 0.102 mm / 4 mils

### READING RANGES

TYPICAL DEPTH OF FIELD	Minimum distance determined by symbol length and scan angle. Printing resolution, contrast, and ambient light dependent.
Code 39: 5 mil: 4.7 to 17.7 cm / 1.8 to 7.0 in	
Code 39: 10 mil: 1.7 to 33.2 cm / 0.7 to 13.1 in	
Data Matrix: 10 mil: 2.7 to 17.1 cm / 1.0 to 6.7 in	
Data Matrix: 15 mil: 1.2 to 24.6 cm / 0.5 to 9.7 in	
EAN: 13 mil: 2.5 to 41.9 cm / 1.0 to 16.5 in	
PDF417: 10 mil: 2.2 to 23.9 cm / 0.9 to 9.4 in	
QR Code: 10 mil: 3.5 to 16.0 cm / 1.4 to 6.3 in	

### SAFETY & REGULATORY

AGENCY APPROVALS	The product meets necessary safety and regulatory approvals for its intended use. The Quick Reference Guide for this product can be referred to for a complete list of certifications.
ENVIRONMENTAL COMPLIANCE LASER CLASSIFICATION	Complies to China RoHS; Complies to EU RoHS Caution Laser Radiation - Do not stare into beam; IEC 60825, Class 2

### UTILITIES

DATALOGIC ALADDIN™	Datalogic Aladdin configuration program is available for download at no charge.
OPOS / JAVPOS	JavaPOS Utilities are available for download at no charge.
REMOTE HOST DOWNLOAD	OPOS Utilities are available for download at no charge. Lowers service costs and improves operations.

### WARRANTY

WARRANTY	18-Month Factory Warranty
----------	---------------------------

